

Technical data sheet

E-Stop button

Part no.: 63000002

ESB200-4KR-C

Contents

- Technical data
- Electrical connection



For illustration purposes only



Technical data

Basic data

Series	ESB200
Type	E-Stop command device, EN ISO 13850, EN 60947-5-5

Functions

Functions	Position-dependent E-Stop command input Protected screw fitting Reset function (via rotary knob or key)
-----------	---

Characteristic parameters

SIL	Up to 3, IEC 61508
Performance Level (PL)	Up to and including e, EN ISO 13849-1
Mission time T_M	20 years, EN ISO 13849-1
Category	Up to incl. 4 (depending on wiring), EN ISO 13849
$B10_d$	600,000 number of cycles
Life expectancy contact	20,000,000 switching cycles

Electrical data

Protective circuit	Short circuit protected
Usage category at DC 13	Ue/Ie: 24 V / 2.5 A, 48 V / 1.3 A, 125 V / 0.6 A, 250 V / 0.3 A, EN 60947-5-1
Usage category at AC 15	Ue/Ie: 24 V / 6 A, 48 V / 6 A, 120 V / 6 A, 250 V / 6 A, 400 V / 3 A, EN 60947-5-1
Contact allocation	2NC + 1NO
Contact opening	Force-fit
Short circuit protected	500 V, 10 A, type gG/gL, IEC 60269-1

Performance data

Rated insulation voltage	600 V AC/DC
Conventional thermal current, max.	10 A

Connection

Number of connections	1 Piece(s)
Number of cable entries	5 Piece(s)

Connection 1

Function	Contact connection
Type of connection	Terminal
No. of pins	6 -pin

Cable properties

Connection cross sections	1 x 0.5 mm ² to 2 x 2.5 mm ² , wire
---------------------------	---

Mechanical data

Dimension (W x H x L)	80 mm x 101.8 mm x 72 mm
Housing material	Plastic
Plastic housing	Glass fiber reinforced (PPS), self-extinguishing
Electrical contact material	Silver alloy
Net weight	240 g
Housing color	Black Yellow, RAL 1023
Type of fastening	Through-hole mounting Wall mounting
Type of cable entry	M16 x 1.5
Installation position	Arbitrary
Switch type	E-Stop command device, EN ISO 13850
Switching principle	Slow-action contact
Mechanical life time	300,000 actuation cycles, IEC 60947-5-1 switching cycles
Actuation frequency, max.	3,600 per hour, IEC 60947-5-1
Type of actuation	E-Stop button, red
Button actuation force	25 N
Sensor material	Plastic

Environmental data

Ambient temperature, operation	-25 ... 80 °C
Degree of contamination	3, EN 60947-1

Certifications

Degree of protection	IP 67 IP 69K
Approvals	c UL US

Classification

Customs tariff number	85369095
ECLASS 5.1.4	27270690
ECLASS 8.0	27371244
ECLASS 9.0	27371244
ECLASS 10.0	27371244
ECLASS 11.0	27371244
ECLASS 12.0	27371244
ECLASS 13.0	27371244
ECLASS 14.0	27371244
ECLASS 15.0	27371244
ECLASS 16.0	27371244
ETIM 5.0	EC002034
ETIM 6.0	EC002034
ETIM 7.0	EC002034
ETIM 8.0	EC002034
ETIM 9.0	EC002034
ETIM 10.0	EC002034
UNSPSC 26.08	39121545

Electrical connection

Connection 1

Function	Contact connection
Type of connection	Terminal
No. of pins	6 -pin

Electrical connection

Terminal	Assignment
1	NC(1)
2	NC(1)
3	NC(2)
4	NC(2)
5	NO(1)
6	NO(1)