

## Technical data sheet

### Reflector

Part no.: 50109828

MTK 20

#### Contents

- Technical data
- Dimensioned drawings



For illustration purposes only

## Technical data

### Mechanical data

|                                          |             |
|------------------------------------------|-------------|
| Design                                   | Round       |
| Triple reflector size                    | 1.2 mm      |
| Mounting dimension, thickness            | 4 mm        |
| Mounting dimension, diameter             | 20 mm       |
| Reflective surface, diameter             | 17 mm       |
| Reflector material                       | Plastic     |
| Material of base material                | Plastic     |
| Polarization-changing                    | Yes         |
| Chemical designation, reflector material | PMMA8N      |
| Structure, active surface                | Mikrotriple |
| Net weight                               | 5 g         |
| Type of fastening                        | Adhesive    |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 65 °C |
|--------------------------------|---------------|

### Certifications

|                      |       |
|----------------------|-------|
| Degree of protection | IP 67 |
|----------------------|-------|

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 90029000 |
| ECLASS 5.1.4          | 27279203 |
| ECLASS 8.0            | 27279203 |
| ECLASS 9.0            | 27273601 |
| ECLASS 10.0           | 27273601 |
| ECLASS 11.0           | 27273601 |
| ECLASS 12.0           | 27273601 |
| ECLASS 13.0           | 27273601 |
| ECLASS 14.0           | 27273601 |
| ECLASS 15.0           | 27273601 |
| ETIM 5.0              | EC002467 |
| ETIM 6.0              | EC002467 |
| ETIM 7.0              | EC002467 |
| ETIM 8.0              | EC002467 |
| ETIM 9.0              | EC002467 |
| ETIM 10.0             | EC002467 |

## Dimensioned drawings

All dimensions in millimeters

