

Technical data sheet

Single beam safety device receiver

Part no.: 50134013

SLE518I-K4/4-M12

Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Notes



Figure can vary



Technical data

Basic data

Series	518
--------	-----

Characteristic parameters

Type	4, IEC/EN 61496, in combination with a suitable test monitoring unit, e.g. MSI-TR1B
SIL	3, IEC 61508, in combination with a suitable test monitoring unit, e.g. MSI-TR1B
SILCL	3, IEC/EN 62061, in combination with a suitable test monitoring unit, e.g. MSI-TR1B
Performance Level (PL)	e, EN ISO 13849-1, In combination with MSI-TRMB safety relay
MTTF _d	1,700 years, EN ISO 13849-1
Mission time T _M	20 years, EN ISO 13849-1
Category	4, EN ISO 13849, In combination with MSI-TRMB safety relay

Electrical data

Protective circuit	Polarity reversal protection Short circuit protected
Performance data	
Supply voltage U _B	24 V, DC, -15 ... 15 %, Incl. residual ripple
Open-circuit current	35 mA
Outputs	
Number of digital switching outputs	1 Piece(s)
Switching outputs	
Voltage type	DC
Switching voltage	high: ≥(U _B -2V) Low: ≤2V
Switching output 1	
Assignment	Connection 1, pin 4
Switching element	Transistor, PNP
Switching principle	Light switching

Timing

Switching frequency	500 Hz
Response time	1 ms
Readiness delay	300 ms

Connection

Number of connections	1 Piece(s)
-----------------------	------------

Connection 1

Function	Signal OUT Voltage supply
Type of connection	Connector
Thread size	M12
Material	Plastic
No. of pins	4 -pin

Mechanical data

Design	Cylindrical
Thread size	M18
Dimension (Ø x L)	22 mm x 91 mm
Housing material	Plastic, ABS, UL 94-V0
Lens cover material	Plastic / PMMA
Net weight	30 g
Housing color	Black
Type of fastening	Mounting bracket

Operation and display

Type of display	LED
Number of LEDs	2 Piece(s)

Environmental data

Ambient temperature, operation	-25 ... 55 °C
Ambient temperature, storage	-25 ... 70 °C

Certifications


Degree of protection	IP 67
Certifications	TÜV Süd UL US
Standards applied	IEC 60947-5-2, IEC/EN 61496

Classification

Customs tariff number	85365019
eCl@ss 8.0	27272701
eCl@ss 9.0	27272701
ETIM 5.0	EC001831
ETIM 6.0	EC001831

Dimensioned drawings

All dimensions in millimeters




- A Green LED
- B Red LED

Electrical connection

Connection 1

Function	Signal OUT
	Voltage supply
Type of connection	Connector
Thread size	M12
Type	Female
Material	Plastic
No. of pins	4 -pin
Encoding	A-coded

Pin	Pin assignment	Conductor color
1	+24V	Brown
2	n.c.	White
3	GND	Blue
4	OUT	Black



Operation and display

LED	Display	Meaning
1	Green, continuous light	Ready
2	Green, continuous light	Function reserve > 30%
	Red, continuous light	Light path free

Notes



Observe intended use!



- ⚡ The product may only be put into operation by competent persons.
- ⚡ Only use the product in accordance with its intended use.

For UL applications:



- ⚡ Only for use in "class 2" circuits

ATTENTION!



- ⚡ The SLS518 K4 safety sensors are a type 4 AOPD only in combination with the MSI-TRM safety relays.
- ⚡ For mounting, electrical connection and operation, the operating instructions of the MSI-TRM safety relays are to be observed.