

# **Technical data sheet Light curtain transmitter**

Part no.: 50119481

CML720i-T05-2640.R-M12



### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Suitable receivers
- Part number code
- Notes
- Accessories





### **Technical data**



### Basic data

Series	720
Operating principle	Throughbeam principle
Device type	Transmitter
Contains	Accessories for the use of the BT-2R1
Application	Object measurement
On a sigl various	

### Special version

Special version	Crossed-beam scanning
	Diagonal-beam scanning
	Parallel-beam scanning

### **Optical data**

Operating range	0.1 3.5 m
Operating range	Guaranteed operating range
Operating range limit	0.1 4.5 m
Operating range limit	Typical operating range
Measurement field length	2,640 mm
Number of beams	528 Piece(s)
Beam spacing	5 mm
Light source	LED, Infrared
Wavelength	940 nm

#### Measurement data

	Minimum ob	ject diameter	10 mr
--	------------	---------------	-------

### **Electrical data** Protective circuit

	Transient protection
Performance data	
Supply voltage U <sub>B</sub>	18 30 V, DC
Residual ripple	0 15 %, From U <sub>B</sub>
Open-circuit current	<ol> <li>435 mA, The specified values refer to the entire package consisting of trans- mitter and receiver.</li> </ol>

Polarity reversal protection Short circuit protected

### **Time behavior**

Readiness delay	450 ms
Cycle time	16.24 ms

### Connection

Number of connections	1 Piece(s)
Plug outlet	Rear side

Connection 1	
Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

### Mechanical data

Design	Cubic
Dimension (W x H x L)	29 mm x 35.4 mm x 2,663 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic
Net weight	2,700 g
Housing color	Silver
Type of fastening	Groove mounting
	Via optional mounting device

### **Operation and display**

Type of display	LED
Number of LEDs	1 Piece(s)

### **Environmental data**

Ambient temperature, operation	-30 60 °C
Ambient temperature, storage	-40 70 °C

#### Certifications

Degree of protection	IP 65
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2

### Classification

Customs tariff number	90314990
ECLASS 5.1.4	27270910
ECLASS 8.0	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ECLASS 13.0	27270910
ECLASS 14.0	27270910
ECLASS 15.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549

# **Dimensioned drawings**



All dimensions in millimeters



- Beam spacing 5 mm
- В Measurement field length 2640 mm
- M6 thread
- Fastening groove
- Profile length 2648 mm
- Transmitter
- Receiver
- 2.5 mm




# **Electrical connection**



### **Connection 1**

Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin	Pin assignment
1	FE/SHIELD
2	V+
3	GND
4	RS 485 Tx+
5	RS 485 Tx-



# **Operation and display**

LED	Display	Meaning
1	Green, continuous light	Continuous mode
	Off	No communication with the receiver / waiting for trigger
	green, flashing in sync with the measurement	Measurement frequency display

### Suitable receivers

	Part no.	Designation	Article	Description
	50119936	CML720i-R05- 2640.R/CN-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: CANopen Connection: Connector, M12, Rear side, 8 -pin
1	50120154	CML720i-R05- 2640.R/CV-M12	Light curtain receiver	Operating range: 0.1 3.5 m Analog outputs: 2 Piece(s), Voltage, Current Connection: Connector, M12, Rear side, 8 -pin
·	50123607	CML720i-R05- 2640.R/D3-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: RS 485 Modbus Connection: Connector, M12, Rear side, 8 -pin
	50120071	CML720i-R05- 2640.R/L-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: IO-Link Connection: Connector, M12, Rear side, 8 -pin

### Suitable receivers



 Part no.	Designation	Article	Description
50122929	CML720i-R05- 2640.R/PB-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: PROFIBUS DP Connection: Connector, M12, Rear side, 8 -pin
50131887	CML720i-R05- 2640.R/PN-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: PROFINET Connection: Connector, M12, Rear side, 8 -pin

### Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle Measuring light curtain					
7XXi	<b>Series</b> 720i: 720i series 730i: 730i series					
Υ	Device type T: transmitter R: receiver					
ZZ	Beam spacing 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm					
AAAA	Measurement field length [mm], dependent on beam spacing					
В	Equipment A: Axial connector outlet R: Rear connector outlet					
ccc	Interface L: IO-Link /CN: CANopen /PB: PROFIBUS /PN: PROFINET /CV: Analog current and voltage output /D3: RS 485 Modbus					
DDD	Special equipment -PS: Power Setting					
EEE	Electrical connection M12: M12 connector					
FFF	-EX: Explosion protection					

### Note



### **Notes**





### Observe intended use!



- \$ This product is not a safety sensor and is not intended as personnel protection.
- \$ The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

### For UL applications:



- 🔖 For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- 🖖 These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

### **Accessories**

# Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
<b>(1)</b>	50129781	KDS DN-M12-5A- M12-5A-P3-050	Interconnection cable	Suitable for interface: DeviceNet, CANopen Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

## Mounting technology - Mounting brackets

Part no.	Designation	Article	Description
50142900	BT 700M.5-2SET	Mounting device set	Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel

# Mounting technology - Swivel mounts

•		0,		
	Part no.	Designation	Article	Description
EE.	429029	BT-2RG	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

### **Accessories**



# Configuration devices

	Part no.	Designation	Article	Description
165	50121098	SET MD12-US2-IL1.1 + Zub.	Diagnostics set	Interface: USB Connections: 2 Piece(s) Degree of protection: IP 20

# Services

	Part no.	Designation	Article	Description
ال ال	S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours.  Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
	S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

### Note



🔖 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.