

Technical data sheet Light curtain transmitter

Part no.: 50119523

CML720i-T40-290.R-M12



Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Suitable receivers
- Part number code
- Notes
- Accessories





Technical data



Basic data

Series	720
Operating principle	Throughbeam principle
Device type	Transmitter
Contains	Accessories for the use of the BT-2R1
Application	Object measurement
Special version	

Special version

Special version	Crossed-beam scanning
	Diagonal-beam scanning
	Parallel-beam scanning

Optical data

Operating range	0.3 7 m
Operating range	Guaranteed operating range
Operating range limit	0.2 9 m
Operating range limit	Typical operating range
Measurement field length	290 mm
Number of beams	8 Piece(s)
Beam spacing	40 mm
Light source	LED, Infrared
Wavelength	940 nm

Measurement data

winimum object diameter 50 mil	Minimum	object diameter	50 mm
--------------------------------	---------	-----------------	-------

Electrical data Protective circuit

	Transient protection
Performance data	
Supply voltage U _B	18 30 V, DC
Residual ripple	0 15 %, From U _B
Open-circuit current	 165 mA, The specified values refer to the entire package consisting of trans- mitter and receiver.

Polarity reversal protection Short circuit protected

Time behavior

Readiness delay	450 ms
Cycle time	1 ms

Connection

Number of connections	1 Piece(s)
Plug outlet	Rear side

Connection 1

Connection 1	
Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Mechanical data

Design	Cubic
Dimension (W x H x L)	29 mm x 35.4 mm x 343 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic
Net weight	550 g
Housing color	Silver
Type of fastening	Groove mounting
	Via optional mounting device

Operation and display

Type of display	LED	
Number of LEDs	1 Piece(s)	

Environmental data

Ambient temperature, operation	-30 60 °C
Ambient temperature, storage	-40 70 °C

Certifications

Degree of protection	IP 65
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2

Classification

Customs tariff number	90314990
ECLASS 5.1.4	27270910
ECLASS 8.0	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ECLASS 13.0	27270910
ECLASS 14.0	27270910
ECLASS 15.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549


Dimensioned drawings



All dimensions in millimeters



- Beam spacing 40 mm
- В Measurement field length 290 mm
- M6 thread
- Fastening groove
- Profile length 328 mm
- Transmitter
- Receiver
- 5 mm




Electrical connection



Connection 1

Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin	Pin assignment
1	FE/SHIELD
2	V+
3	GND
4	RS 485 Tx+
5	RS 485 Tx-



Operation and display

LED	Display	Meaning
1	Green, continuous light	Continuous mode
	Off	No communication with the receiver / waiting for trigger
	green, flashing in sync with the measurement	Measurement frequency display

Suitable receivers

	Part no.	Designation	Article	Description
	50119977	CML720i-R40-290.R/ CN-M12	Light curtain receiver	Operating range: 0.3 7 m Interface: CANopen Connection: Connector, M12, Rear side, 8 -pin
	50120196	CML720i-R40-290.R/ CV-M12	Light curtain receiver	Operating range: 0.3 7 m Analog outputs: 2 Piece(s), Voltage, Current Connection: Connector, M12, Rear side, 8 -pin
·	50123648	CML720i-R40-290.R/ D3-M12	Light curtain receiver	Operating range: 0.3 7 m Interface: RS 485 Modbus Connection: Connector, M12, Rear side, 8 -pin
	50120113	CML720i-R40-290.R/ L-M12	Light curtain receiver	Operating range: 0.3 7 m Interface: IO-Link Connection: Connector, M12, Rear side, 8 -pin

Suitable receivers



	Part no.	Designation	Article	Description
·	50123060	CML720i-R40-290.R/ PB-M12	Light curtain receiver	Operating range: 0.3 7 m Interface: PROFIBUS DP Connection: Connector, M12, Rear side, 8 -pin
	50131999	CML720i-R40-290.R/ PN-M12	Light curtain receiver	Operating range: 0.3 7 m Interface: PROFINET Connection: Connector, M12, Rear side, 8 -pin

Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle Measuring light curtain					
7XXi	Series 720i: 720i series 730i: 730i series					
Υ	Device type T: transmitter R: receiver					
ZZ	Beam spacing 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm					
AAAA	Measurement field length [mm], dependent on beam spacing					
В	Equipment A: Axial connector outlet R: Rear connector outlet					
ccc	Interface L: IO-Link /CN: CANopen /PB: PROFIBUS /PN: PROFINET /CV: Analog current and voltage output /D3: RS 485 Modbus					
DDD	Special equipment -PS: Power Setting					
EEE	Electrical connection M12: M12 connector					
FFF	-EX: Explosion protection					

Note



Notes





Observe intended use!



- \$ This product is not a safety sensor and is not intended as personnel protection.
- \$ The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

For UL applications:



- 🔖 For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- 🖖 These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

Accessories

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50129781	KDS DN-M12-5A- M12-5A-P3-050	Interconnection cable	Suitable for interface: DeviceNet, CANopen Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Mounting technology - Mounting brackets

Part no.	Designation	Article	Description
50142900	BT 700M.5-2SET	Mounting device set	Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel

Mounting technology - Swivel mounts

Leuze electronic GmbH + Co. KG

•				
	Part no.	Designation	Article	Description
EE.	429029	BT-2RG	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

Accessories



Configuration devices

	Part no.	Designation	Article	Description
is.	50121098	SET MD12-US2-IL1.1 + Zub.	Diagnostics set	Interface: USB Connections: 2 Piece(s) Degree of protection: IP 20

Services

	Part no.	Designation	Article	Description
ال ال	S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
	S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

Note



🔖 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.