

Technical data sheet Light curtain transmitter

Part no.: 50119396

CML720i-T05-2320.A-M12



Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Suitable receivers
- Part number code
- Notes
- Accessories





Technical data



Basic data

Series	720
Operating principle	Throughbeam principle
Device type	Transmitter
Contains	2x BT-NC sliding block
Application	Object measurement
Special version	

Crossed-beam scanning Diagonal-beam scanning Parallel-beam scanning

Polarity reversal protection Short circuit protected

Optical data

Special version

Operating range	0.1 3.5 m
Operating range	Guaranteed operating range
Operating range limit	0.1 4.5 m
Operating range limit	Typical operating range
Measurement field length	2,320 mm
Number of beams	464 Piece(s)
Beam spacing	5 mm
Light source	LED, Infrared
Wavelength	940 nm

Measurement data

Minimum object diameter	10 mm
-------------------------	-------

Electrical data Protective circuit

	Transient protection
Performance data	
Supply voltage U _B	18 30 V, DC
Residual ripple	0 15 %, From U _B
Open-circuit current	 435 mA, The specified values refer to the entire package consisting of trans- mitter and receiver.

Time behavior

Readiness delay	450 ms
Cycle time	14.32 ms

Connection

Plug outlet Axial	

Connection 1

Connection 1	
Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Mechanical data

Design	Cubic
Dimension (W x H x L)	29 mm x 35.4 mm x 2,395 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic
Net weight	2,350 g
Housing color	Silver
Type of fastening	Groove mounting
	Via optional mounting device

Operation and display

Type of display	LED
Number of LEDs	1 Piece(s)

Environmental data

Ambient temperature, operation	-30 60 °C
Ambient temperature, storage	-40 70 °C

Certifications

Degree of protection	IP 65
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2


Classification

Customs tariff number	90314990
ECLASS 5.1.4	27270910
ECLASS 8.0	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ECLASS 13.0	27270910
ECLASS 14.0	27270910
ECLASS 15.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549

Dimensioned drawings

Leuze

All dimensions in millimeters



- Beam spacing 5 mm
- В Measurement field length 2320 mm
- M6 thread
- Fastening groove
- Profile length 2328 mm
- Transmitter
- Receiver
- 2.5 mm




Electrical connection



Connection 1

Function	Connection to receiver
	Sync-input
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin	Pin assignment
1	FE/SHIELD
2	V+
3	GND
4	RS 485 Tx+
5	RS 485 Tx-



Operation and display

LED	Display	Meaning
1	Green, continuous light	Continuous mode
	Off	No communication with the receiver / waiting for trigger
	green, flashing in sync with the measurement	Measurement frequency display

Suitable receivers

Part no.	Designation	Article	Description
50119634	CML720i-R05- 2320.A/CN-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: CANopen Connection: Connector, M12, Axial, 8 -pin
50119824	CML720i-R05- 2320.A/CV-M12	Light curtain receiver	Operating range: 0.1 3.5 m Analog outputs: 2 Piece(s), Voltage, Current Connection: Connector, M12, Axial, 8 -pin
50123468	CML720i-R05- 2320.A/D3-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: RS 485 Modbus Connection: Connector, M12, Axial, 8 -pin
50119743	CML720i-R05- 2320.A/L-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: IO-Link Connection: Connector, M12, Axial, 8 -pin

Suitable receivers



Part no.	Designation	Article	Description
50122915	CML720i-R05- 2320.A/PB-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: PROFIBUS DP Connection: Connector, M12, Axial, 8 -pin
50131876	CML720i-R05- 2320.A/PN-M12	Light curtain receiver	Operating range: 0.1 3.5 m Interface: PROFINET Connection: Connector, M12, Axial, 8 -pin

Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle Measuring light curtain				
7XXi	Series 720i: 720i series 730i: 730i series				
Υ	Device type T: transmitter R: receiver				
ZZ	Beam spacing 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm				
AAAA	Measurement field length [mm], dependent on beam spacing				
В	Equipment A: Axial connector outlet R: Rear connector outlet				
ccc	Interface L: IO-Link /CN: CANopen /PB: PROFIBUS /PN: PROFINET /CV: Analog current and voltage output /D3: RS 485 Modbus				
DDD	Special equipment -PS: Power Setting				
EEE	Electrical connection M12: M12 connector				
FFF	-EX: Explosion protection				

info@leuze.com • www.leuze.com

Note



5/7

Notes





Observe intended use!



- \$ This product is not a safety sensor and is not intended as personnel protection.
- \$ The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

For UL applications:



- 🔖 For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- 🖖 These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

Accessories

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50129781	KDS DN-M12-5A- M12-5A-P3-050	Interconnection cable	Suitable for interface: DeviceNet, CANopen Connection 1: Connector, M12, Axial, Female, A-coded, 5-pin Connection 2: Connector, M12, Axial, Male, A-coded, 5-pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Mounting technology - Mounting brackets

Part no.	Designation	Article	Description
50142900	BT 700M.5-2SET	Mounting device set	Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel

Configuration devices

	Part no.	Designation	Article	Description
165	50121098	SET MD12-US2-IL1.1 + Zub.	Diagnostics set	Interface: USB Connections: 2 Piece(s) Degree of protection: IP 20

Leuze electronic GmbH + Co. KG The Sensor People In der Braike 1, D-73277 Owen/Germany Phone: +49 7021 573-0 • Fax: +49 7021 573-199 eng • 2025-04-04

Accessories



Services

Part no.	Designation	Article	Description
S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

Note



♥ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.

Leuze electronic GmbH + Co. KG