

Technical data sheet RFID read/write device

Part no.: 50150660

RDH 142 00 M30

Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Notes
- Further information



For illustration purposes only



Technical data

Basic data

Series	RDH 100
Working frequency	13.56 MHz

Functions

Functions	Configurable operating modes
	I/O
	Reading gate control

Read data

Reading/writing range, max.	60 mm
Transponder, readable	ISO/IEC 14443A
	ISO/IEC 15693
	NFC Types 2, 5

Electrical data

Performance data	
Supply voltage U _B	18 ... 36 V, DC
Power consumption, max.	1 W
Memory access	Read/Write
Inputs	
Number of digital switching inputs	1 Piece(s)
Outputs	
Number of digital switching outputs	1 Piece(s)

Connection

Number of connections	1 Piece(s)
Connection 1	
Function	I/O
	IO-Link
	PWR
Type of connection	Connector
Thread size	M12

Mechanical data

Design	Cylindrical
Length	75 mm
Thread size	M30
Housing material	Metal
	Plastic
Net weight	120 g
Housing color	Red
	Silver
Type of fastening	Mounting thread

Environmental data

Ambient temperature, operation	-32 ... 60 °C
Ambient temperature, storage	-40 ... 85 °C
Relative humidity (non-condensing)	0 ... 90 %

Certifications


Degree of protection	IP 67
Approvals	EU

Classification

Customs tariff number	84719000
ECLASS 5.1.4	27280401
ECLASS 8.0	27280401
ECLASS 9.0	27280401
ECLASS 10.0	27280401
ECLASS 11.0	27280401
ECLASS 12.0	27280401
ECLASS 13.0	27280401
ECLASS 14.0	27280401
ECLASS 15.0	27280401
ETIM 5.0	EC001825
ETIM 6.0	EC002998
ETIM 7.0	EC002998
ETIM 8.0	EC002998
ETIM 9.0	EC002998
ETIM 10.0	EC002998

Dimensioned drawings

All dimensions in millimeters



Electrical connection

Connection 1

Function	I/O
	IO-Link
	PWR
Type of connection	Connector
Thread size	M12
Type	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Operation and display

LED	Display	Meaning
1	Red, continuous light	Reading successful
	Green, continuous light	
	Yellow, flashing, 4 Hz	
	Yellow, continuous light	
	Off	

Notes

**Observe intended use!**



- ⚡ This product is not a safety sensor and is not intended as personnel protection.
- ⚡ The product may only be put into operation by competent persons.
- ⚡ Only use the product in accordance with its intended use.

Further information

- Under certain circumstances, metal in the reading field reduces the operating range considerably.