


## Technical data sheet Interconnection cable

Part no.: 50153687

KDS U-M8-4A-M8-3A-P1-010

### Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



## Technical data

### Basic data

|             |                             |
|-------------|-----------------------------|
| Application | Oil and lubricant resistant |
|-------------|-----------------------------|

### Connection

#### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M8        |
| Type               | Female    |
| No. of pins        | 4 -pin    |
| Version            | Axial     |
| Connector, LED     | No        |

#### Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M8        |
| Type               | Male      |
| No. of pins        | 3 -pin    |
| Version            | Axial     |

#### Cable properties

|                                   |                                                                                                                                                                                                                 |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of conductors              | 3 Piece(s)                                                                                                                                                                                                      |
| Wire cross section                | 0.25 mm <sup>2</sup>                                                                                                                                                                                            |
| AWG                               | 24                                                                                                                                                                                                              |
| Sheathing color                   | Black                                                                                                                                                                                                           |
| Shielded                          | No                                                                                                                                                                                                              |
| Silicone-free                     | Yes                                                                                                                                                                                                             |
| Cable design                      | Interconnection cable                                                                                                                                                                                           |
| Cable diameter (external)         | 4.1 mm                                                                                                                                                                                                          |
| Cable length                      | 1,000 mm                                                                                                                                                                                                        |
| Sheathing material                | PUR                                                                                                                                                                                                             |
| Wire insulation                   | PP                                                                                                                                                                                                              |
| Traverse rate                     | Max. 3m/s with horiz. traverse path of 5m and max. acceleration of 10m/s <sup>2</sup>                                                                                                                           |
| Suitability for drag chains       | Yes                                                                                                                                                                                                             |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable                                                                                            |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |
| Torsion suitability               | ±180° / m (max. 2 mio. cycles with 35 cycles / min)                                                                                                                                                             |

### Mechanical data

|                                         |                          |
|-----------------------------------------|--------------------------|
| Width across flats                      | 9 mm                     |
| Net weight                              | 26.4 g                   |
| Bending cycles                          | 5,000,000 Piece(s)       |
| Bending radius, flexible laying, min.   | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 5 x cable diameter  |

### Operation and display

### Environmental data

|                                                |               |
|------------------------------------------------|---------------|
| Ambient temperature, operation, flexible use   | -25 ... 80 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

### Certifications

|                      |         |
|----------------------|---------|
| Degree of protection | IP 65   |
|                      | IP 66K  |
|                      | IP 67   |
|                      | IP 68   |
| Approvals            | c UL US |
| UL file number       | E366145 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |

## Electrical connection

### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M8        |
| Type               | Female    |
| No. of pins        | 4 -pin    |
| Version            | Axial     |
| Connector, LED     | No        |

Electrical connection

Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M8        |
| Type               | Male      |
| No. of pins        | 3 -pin    |
| Version            | Axial     |

Circuit diagrams

Wiring schematic

