

Technical data sheet


Connection cable

Part no.: 50135244

KD PB-M12-4A-P3-100

Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



Technical data

Basic data

Application	Oil and lubricant resistant
Suitable for interface	PROFIBUS DP

Electrical data

Performance data	
Operating voltage	60 V DC

Connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR
No. of pins	5 -pin
Encoding	B-coded
Version	Axial
Connector, LED	No
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking
Connection 2	
Type of connection	Open end
Cable properties	
Number of conductors	2 Piece(s)
Wire cross section	0.64 mm ²
AWG	19
Sheathing color	Violet
Shielded	Yes
Silicone-free	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	7.7 mm
Cable length	10,000 mm
Sheathing material	PUR
Wire insulation	PE
Suitability for drag chains	Yes
Traversal rate	Max. 3.3 m/s with horiz. traverse path of 5m and max. acceleration of 5m/s ²
Properties of the outer sheathing	Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable
Resistance of the outer sheathing	Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2

Mechanical data

Width across flats	13 mm
Net weight	551 g
Bending cycles	5,000,000 Piece(s)
Bending radius, flexible laying, min.	Min. 12 x cable diameter
Bending radius, stationary laying, min.	Min. 7.5 x cable diameter

Operation and display

Environmental data

Ambient temperature, operation, flexible use	-20 ... 70 °C
Ambient temperature, operation, stationary use	-40 ... 80 °C

Certifications

Degree of protection	IP 65
	IP 67

Classification

Customs tariff number	85444290
ECLASS 5.1.4	27279201
ECLASS 8.0	27279218
ECLASS 9.0	27060311
ECLASS 10.0	27060311
ECLASS 11.0	27060311
ECLASS 12.0	27060311
ECLASS 13.0	27060311
ECLASS 14.0	27060311
ECLASS 15.0	27060311
ECLASS 16.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855
ETIM 7.0	EC001855
ETIM 8.0	EC001855
ETIM 9.0	EC001855
ETIM 10.0	EC001855

Electrical connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
Handle body material	PUR

Electrical connection

Connection 1

No. of pins	5 -pin
Encoding	B-coded
Version	Axial
Connector, LED	No
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Pin	Conductor color
1	n.c.
2	Green
3	n.c.
4	Red
5	n.c.



Connection 2

Type of connection	Open end
--------------------	----------

Circuit diagrams

Wiring schematic

