

## Technical data sheet

### Diffuse sensor with background suppression

Part no.: 50147094

HT36I/NX-M12



For illustration purposes only

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Part number code
- Notes
- Further information
- Accessories



Technical data

Basic data

|                     |                                                           |
|---------------------|-----------------------------------------------------------|
| Series              | 36                                                        |
| Operating principle | Diffuse reflection principle with back-ground suppression |

Optical data

|                             |                                      |
|-----------------------------|--------------------------------------|
| Black-white error           | < 10% up to 800 mm                   |
| Operating range             | Guaranteed operating range           |
| Operating range, white 90%  | 0.01 ... 2.5 m                       |
| Operating range, gray 18%   | 0.05 ... 1.5 m                       |
| Operating range, black 6%   | 0.08 ... 1.1 m                       |
| Operating range limit       | Typical operating range              |
| Operating range limit       | 0.01 ... 2.5 m                       |
| Adjustment range            | 150 ... 2,500 mm                     |
| Beam path                   | Focused                              |
| Light source                | LED, Infrared                        |
| Wavelength                  | 860 nm                               |
| Transmitted-signal shape    | Pulsed                               |
| LED group                   | Exempt group (in acc. with EN 62471) |
| Type of light spot geometry | Rectangular                          |
| Focus                       | Fixed                                |

Electrical data

|                    |                              |
|--------------------|------------------------------|
| Protective circuit | Polarity reversal protection |
|                    | Short circuit protected      |
|                    | Transient protection         |

Performance data

|                               |                                        |
|-------------------------------|----------------------------------------|
| Supply voltage U <sub>B</sub> | 10 ... 30 V, DC, Incl. residual ripple |
| Residual ripple               | 0 ... 15 %, From U <sub>B</sub>        |
| Open-circuit current          | 0 ... 30 mA                            |

Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 1 Piece(s) |
|-------------------------------------|------------|

Switching outputs

|                         |                             |
|-------------------------|-----------------------------|
| Voltage type            | DC                          |
| Switching current, max. | 100 mA                      |
| Switching voltage       | high: ≥(U <sub>B</sub> -2V) |
|                         | low: ≤ 2 V                  |

Switching output 1

|                     |                     |
|---------------------|---------------------|
| Assignment          | Connection 1, pin 4 |
| Switching element   | Transistor, NPN     |
| Switching principle | Dark switching      |

Time behavior

|                     |        |
|---------------------|--------|
| Switching frequency | 250 Hz |
| Response time       | 2 ms   |
| Readiness delay     | 300 ms |

Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Signal OUT     |
|                    | Voltage supply |
| Type of connection | Connector      |
| Thread size        | M12            |
| Type               | Male           |
| Material           | Plastic        |
| No. of pins        | 4 -pin         |
| Encoding           | A-coded        |

Mechanical data

|                       |                              |
|-----------------------|------------------------------|
| Dimension (W x H x L) | 20.5 mm x 76.3 mm x 44 mm    |
| Housing material      | Plastic                      |
| Plastic housing       | PC-PBT                       |
| Lens cover material   | Plastic / PMMA               |
| Net weight            | 60 g                         |
| Housing color         | Black                        |
| Type of fastening     | Through-hole mounting        |
|                       | Via optional mounting device |

Operation and display

|                                     |                         |
|-------------------------------------|-------------------------|
| Type of display                     | LED                     |
| Number of LEDs                      | 2 Piece(s)              |
| Operational controls                | Multiturn potentiometer |
| Function of the operational control | Range adjustment        |

Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 60 °C |
| Ambient temperature, storage   | -40 ... 70 °C |

Certifications


|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
| Protection class     | III           |
| Certifications       | c UL US       |
| Standards applied    | IEC 60947-5-2 |

Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270904 |
| ECLASS 8.0            | 27270904 |
| ECLASS 9.0            | 27270904 |
| ECLASS 10.0           | 27270904 |
| ECLASS 11.0           | 27270904 |
| ECLASS 12.0           | 27270903 |
| ECLASS 13.0           | 27270903 |
| ECLASS 14.0           | 27270903 |
| ETIM 5.0              | EC002719 |
| ETIM 6.0              | EC002719 |
| ETIM 7.0              | EC002719 |
| ETIM 8.0              | EC002719 |
| ETIM 9.0              | EC002719 |

Dimensioned drawings

All dimensions in millimeters




Electrical connection

Connection 1


|                    |                |
|--------------------|----------------|
| Function           | Signal OUT     |
|                    | Voltage supply |
| Type of connection | Connector      |
| Thread size        | M12            |
| Type               | Male           |
| Material           | Plastic        |
| No. of pins        | 4 -pin         |
| Encoding           | A-coded        |

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | n.c.           |
| 3   | GND            |
| 4   | OUT 1          |




Diagrams

Typ. response behavior (focusing distance 800 mm)



Typ. black/white behavior



Operation and display

| LED | Display                  | Meaning               |
|-----|--------------------------|-----------------------|
| 1   | Green, continuous light  | Operational readiness |
| 2   | Yellow, continuous light | Reflection            |

Part number code

Part designation: AAA36 D.E/FG-K

|       |                                                                                                                                                                                                                                                                                            |
|-------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| AAA36 | <b>Operating principle / construction</b><br>HT36: Diffuse reflection sensor with background suppression<br>LS36: Throughbeam photoelectric sensor transmitter<br>LE36: Throughbeam photoelectric sensor receiver<br>PRK36: Retro-reflective photoelectric sensor with polarization filter |
| D     | <b>Light type</b><br>n/a: red light<br>I: infrared light                                                                                                                                                                                                                                   |
| E     | <b>Equipment</b><br>n/a: standard<br>1: 270° potentiometer<br>D: Depolarizing media                                                                                                                                                                                                        |
| FG    | <b>Switching output / Function</b><br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>X: pin not used                                                    |
| K     | <b>Electrical connection</b><br>n/a: cable, standard length 2000 mm, 3-wire<br>200-M8: cable, length 200 mm with M8 connector, 4-pin, axial (plug)<br>200-M12: cable, length 200 mm with M12 connector, 4-pin, axial (plug)<br>M12: M12 connector, 4-pin (plug)                            |

| Note                                                                              |                                                                                                                                      |
|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>A list with all available device types can be found on the Leuze website at <a href="http://www.leuze.com">www.leuze.com</a>.</p> |

Notes

|  Observe intended use! |                                                                                                                                                                                                                                  |
|-----------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                         | <p>This product is not a safety sensor and is not intended as personnel protection.</p> <p>The product may only be put into operation by competent persons.</p> <p>Only use the product in accordance with its intended use.</p> |


| For UL applications:                                                               |                                                                                                                                                                                                                                                                                                                |
|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).</p> <p>These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)</p> |

Further information

- Light source: Average life expectancy 100,000h at an ambient temperature of 25 °C
- Response time: For short decay times, an ohmic load of approx. 5kOhm is recommended

Accessories

Connection technology - Connection cables

|                                                                                   | Part no. | Designation        | Article          | Description                                                                                                                                                                        |
|-----------------------------------------------------------------------------------|----------|--------------------|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50130652 | KD U-M12-4A-V1-050 | Connection cable | Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5.000 mm<br>Sheathing material: PVC  |
|   | 50130690 | KD U-M12-4W-V1-050 | Connection cable | Connection 1: Connector, M12, Angled, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5.000 mm<br>Sheathing material: PVC |

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.