

Technical data sheet

Bar code tape

Part no.: 50144218

BCB G40 SH1 SL

Contents

- Technical data
- Part number code



For illustration purposes only

Technical data

Basic data

| | |
|------|---|
| Type | Configurable bar code tape (special tape, TWIN tape, repair tape) |
|------|---|

Special version

| | |
|-----------------|--------------|
| Special version | Special tape |
|-----------------|--------------|

Mechanical data

| | |
|-----------------------|---------------------------------|
| Grid dimension | 40 mm |
| Tape start value | Individual |
| Tape end value | Individual |
| Tape height | Individually between 20 - 32 mm |
| Net weight | 7 g |
| Manufacturing process | Digital printing |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 48211010 |
| ECLASS 5.1.4 | 27280190 |
| ECLASS 8.0 | 27280190 |
| ECLASS 9.0 | 27280192 |
| ECLASS 10.0 | 27280192 |
| ECLASS 11.0 | 27280192 |
| ECLASS 12.0 | 27280192 |
| ECLASS 13.0 | 27280192 |
| ECLASS 14.0 | 27280192 |
| ECLASS 15.0 | 27280192 |
| ECLASS 16.0 | 27280192 |
| ETIM 5.0 | EC002498 |
| ETIM 6.0 | EC003015 |
| ETIM 7.0 | EC003015 |
| ETIM 8.0 | EC003015 |
| ETIM 9.0 | EC003015 |
| ETIM 10.0 | EC003015 |
| UNSPSC 26.08 | 31242100 |

Part number code

Part designation: **BCB AAA BBB CCCC DDDD E**

BCB Bar code tape

| | |
|-------------|--|
| BCB | Series BCB: Bar code tape |
| AAA | Grid / grid dimension G30: 30 mm G40: 40 mm |
| BBB | Tape height / special height H25: height 25 mm H47: height 47 mm SH1: special height, individually between 20 - 32 mm SH2: special height, individually between 33 - 47 mm SH3: special height, individually between 48 - 70 mm SH4: special height, individually between 71 - 140 mm |
| CCCC | Tape length / special length Lxxx: tape length in mm SL: Special length |

Part number code

BCB Bar code tape

DDDD Options
TWIN: two identical printed tapes
MVS: Measurement Value Switch (color red)
MV0: Measurement Value Zero (color yellow)
ML: Marker label
RW: Reverse Winding (changed winding direction, the smallest position value is inside on the wrapping core)
RK: Repair Kit (repair tape)

E Customer-specific design
A: Code content ML = AA1 color red
B: Code content ML = BB1 color red
C: Code content ML = CC1 color red
D: Code content ML = DD1 color red
E: Code content ML = EE1 color red
F: Code content ML = FF1 color red
G: code content ML = CC1 color red

Note



A list with all available device types can be found on the Leuze website at www.leuze.com.