

## Technical data sheet

### Polarized retro-reflective photoelectric sensor

Part no.: 50122694

PRK328.W3/2N



For illustration purposes only

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Reflectors & reflective tapes
- Part number code
- Notes
- Further information
- Accessories



## Technical data

### Basic data

|                     |                      |
|---------------------|----------------------|
| Series              | 328                  |
| Operating principle | Reflection principle |

### Special version

|                 |                      |
|-----------------|----------------------|
| Special version | 90° - angular optics |
|-----------------|----------------------|

### Optical data

|                          |                                               |
|--------------------------|-----------------------------------------------|
| Operating range          | 0.02 ... 4 m, With reflector TK(S)<br>100x100 |
| Operating range          | Guaranteed operating range                    |
| Operating range limit    | 0.02 ... 5 m, With reflector TK(S)<br>100x100 |
| Operating range limit    | Typical operating range                       |
| Light source             | LED, Red                                      |
| Wavelength               | 620 nm                                        |
| Transmitted-signal shape | Pulsed                                        |
| LED group                | Exempt group (in acc. with EN 62471)          |

### Electrical data

|                    |                                                         |
|--------------------|---------------------------------------------------------|
| Protective circuit | Polarity reversal protection<br>Short circuit protected |
|--------------------|---------------------------------------------------------|

### Performance data

|                      |                                        |
|----------------------|----------------------------------------|
| Supply voltage $U_B$ | 10 ... 30 V, DC, Incl. residual ripple |
| Residual ripple      | 0 ... 15 %, From $U_B$                 |
| Open-circuit current | 0 ... 20 mA                            |

### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 2 Piece(s) |
|-------------------------------------|------------|

### Switching outputs

|                         |                                               |
|-------------------------|-----------------------------------------------|
| Voltage type            | DC                                            |
| Switching current, max. | 100 mA                                        |
| Switching voltage       | high: $\geq(U_B - 2.5V)$<br>low: $\leq 2.5 V$ |

### Switching output 1

|                     |                 |
|---------------------|-----------------|
| Switching element   | Transistor, NPN |
| Switching principle | Light switching |

### Switching output 2

|                     |                 |
|---------------------|-----------------|
| Switching element   | Transistor, NPN |
| Switching principle | Dark switching  |

### Time behavior

|                     |        |
|---------------------|--------|
| Switching frequency | 500 Hz |
| Response time       | 1 ms   |
| Readiness delay     | 300 ms |

### Connection

#### Connection 1

|                      |                              |
|----------------------|------------------------------|
| Function             | Signal OUT<br>Voltage supply |
| Type of connection   | Cable                        |
| Cable length         | 2,000 mm                     |
| Sheathing material   | PUR                          |
| Cable color          | Black                        |
| Number of conductors | 4 -wire                      |
| Wire cross section   | 0.2 mm <sup>2</sup>          |

### Mechanical data

|                         |                            |
|-------------------------|----------------------------|
| Dimension (Ø x L)       | 18 mm x 61 mm              |
| Thread size             | M18 x 1 mm                 |
| Housing material        | Plastic<br>Stainless steel |
| Stainless steel housing | V2A                        |
| Plastic housing         | ABS                        |
| Lens cover material     | Plastic                    |
| Net weight              | 70 g                       |
| Housing color           | Black<br>Silver            |

### Operation and display

|                      |              |
|----------------------|--------------|
| Type of display      | LED          |
| Number of LEDs       | 1 Piece(s)   |
| Operational controls | Teach button |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 60 °C |
| Ambient temperature, storage   | -40 ... 70 °C |

### Certifications


|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
| Protection class     | III           |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270902 |
| ECLASS 8.0            | 27270902 |
| ECLASS 9.0            | 27270902 |
| ECLASS 10.0           | 27270902 |
| ECLASS 11.0           | 27270902 |
| ECLASS 12.0           | 27270902 |
| ECLASS 13.0           | 27270902 |
| ECLASS 14.0           | 27270902 |
| ECLASS 15.0           | 27270902 |
| ETIM 5.0              | EC002717 |
| ETIM 6.0              | EC002717 |
| ETIM 7.0              | EC002717 |
| ETIM 8.0              | EC002717 |
| ETIM 9.0              | EC002717 |
| ETIM 10.0             | EC002717 |

Dimensioned drawings

All dimensions in millimeters



Electrical connection

Connection 1

|                      |                |
|----------------------|----------------|
| Function             | Signal OUT     |
|                      | Voltage supply |
| Type of connection   | Cable          |
| Cable length         | 2,000 mm       |
| Sheathing material   | PUR            |
| Cable color          | Black          |
| Number of conductors | 4 -wire        |
| Wire cross section   | 0.2 mm²        |


Conductor color

Conductor assignment


|       |       |
|-------|-------|
| Brown | V+    |
| White | OUT 2 |
| Blue  | GND   |
| Black | OUT 1 |

Diagrams

Typ. response behavior (TK 100x100)



Typ. function reserve (axial model)



Operation and display

| LED | Display                  | Meaning               |
|-----|--------------------------|-----------------------|
| 1   | Green, continuous light  | Operational readiness |
|     | Yellow, continuous light | Light path free       |
|     | Yellow, flashing         | No function reserve   |

Reflectors & reflective tapes

| Part no. | Designation   | Operating range<br>Operating range<br>limit | Description                                                                                                                                             |
|----------|---------------|---------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| 50108300 | REF 4-A-50x50 | 0.1 ... 1.3 m<br>0.1 ... 1.8 m              | Design: Rectangular<br>Reflective surface: 50 mm x 50 mm<br>Material: Plastic<br>Chemical designation of the material: PMMA<br>Fastening: Self-adhesive |

## Reflectors & reflective tapes

|                                                                                     | Part no. | Designation | Operating range<br>Operating range<br>limit | Description                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------|----------|-------------|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | 50003192 | TK 100x100  | 0.02 ... 4 m<br>0.02 ... 5 m                | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 96 mm x 96 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Rear side can be glued                    |
|    | 50024127 | TK 82.2     | 0.05 ... 3.3 m<br>0.05 ... 4 m              | Design: Round<br>Triple reflector size: 4 mm<br>Reflective surface, diameter: 79 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Rear side can be glued |
|    | 50022816 | TKS 100X100 | 0.02 ... 4 m<br>0.02 ... 5 m                | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 96 mm x 96 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive           |
|   | 50081283 | TKS 20X40   | 0.04 ... 1.5 m<br>0.04 ... 2 m              | Design: Rectangular<br>Triple reflector size: 2.3 mm<br>Reflective surface: 16 mm x 38 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive         |
|  | 50023525 | TKS 30X50   | 0.05 ... 1.6 m<br>0.05 ... 2 m              | Design: Rectangular<br>Triple reflector size: 3 mm<br>Reflective surface: 27 mm x 44 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive           |
|  | 50040820 | TKS 40X60   | 0.02 ... 2.6 m<br>0.02 ... 3.5 m            | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 37 mm x 56 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive           |

## Part number code

Part designation: XXX328BY-AAAF.BB/CC-DDD

|        |                                                                                                                                                                                                                                                                                                |
|--------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| XXX328 | <b>Operating principle</b><br>PRK: Retro-reflective photoelectric sensor with polarization filter<br>ET: energetic diffuse reflection sensor<br>FT: diffuse reflection sensor with fading<br>LE: Throughbeam photoelectric sensor receiver<br>LS: throughbeam photoelectric sensor transmitter |
| Y      | <b>Light type</b><br>n/a: red light<br>I: infrared light                                                                                                                                                                                                                                       |
| AAAF   | <b>Preset range (optional)</b><br>n/a: operating range acc. to data sheet<br>xxxF: Preset range [mm]                                                                                                                                                                                           |

## Part number code

|            |                                                                                                                                                                                                                                                                                                                                                                                                                        |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>BB</b>  | <b>Equipment</b><br>n/a: axial optics<br>W: 90° angular optics<br>3: teach-in via button                                                                                                                                                                                                                                                                                                                               |
| <b>CC</b>  | <b>Switching output / function (OUT1 = pin 4, OUT2 = pin 2):</b><br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>9: input for transmitter deactivation (deactivation with HIGH signal)<br>D: Input for transmitter deactivation (deactivation with LOW signal)<br>X: pin not used |
| <b>DDD</b> | <b>Electrical connection</b><br>n/a: cable, standard length 2000 mm, 4-wire<br>M12: M12 connector, 4-pin (plug)                                                                                                                                                                                                                                                                                                        |

### Note



↪ A list with all available device types can be found on the Leuze website at [www.leuze.com](http://www.leuze.com).

## Notes



### Observe intended use!



- ↪ This product is not a safety sensor and is not intended as personnel protection.
- ↪ The product may only be put into operation by competent persons.
- ↪ Only use the product in accordance with its intended use.

### For UL applications:



- ↪ For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- ↪ These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

## Further information

- Sum of the output currents for both outputs, 50 mA for ambient temperatures > 40 °C

## Accessories

### Mounting technology - Mounting brackets

|                                                                                  | Part no. | Designation | Article          | Description                                                                                                                                                                                                                  |
|----------------------------------------------------------------------------------|----------|-------------|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50113548 | BT D18M.5   | Mounting bracket | Diameter, inner: 18 mm<br>Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Rigid<br>Material: Stainless steel |
|                                                                                  |          |             |                  |                                                                                                                                                                                                                              |

### Mounting technology - Rod mounts

|                                                                                  | Part no. | Designation  | Article         | Description                                                                                                                                                                                                              |
|----------------------------------------------------------------------------------|----------|--------------|-----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50117490 | BTU D18M-D12 | Mounting system | Design of mounting device: Mounting system<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal |
|                                                                                  |          |              |                 |                                                                                                                                                                                                                          |

### Mounting technology - Other

|                                                                                    | Part no. | Designation | Article   | Description                                                                                                                                                                                                                               |
|------------------------------------------------------------------------------------|----------|-------------|-----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50121904 | BT318B-OM   | Fastening | Design of mounting device: Mounting clamp<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Swiveling, Adjustable, Turning<br>Material: Plastic<br>Shock absorber: No |
|                                                                                    |          |             |           |                                                                                                                                                                                                                                           |

### Standard reflectors

|                                                                                     | Part no. | Designation | Article   | Description                                                                                                                                                                                                                            |
|-------------------------------------------------------------------------------------|----------|-------------|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50081283 | TKS 20X40   | Reflector | Design: Rectangular<br>Triple reflector size: 2.3 mm<br>Reflective surface: 16 mm x 38 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive |
|  | 50040820 | TKS 40X60   | Reflector | Design: Rectangular<br>Triple reflector size: 4 mm<br>Reflective surface: 37 mm x 56 mm<br>Material: Plastic<br>Base material: Plastic<br>Chemical designation of the material: PMMA8N<br>Fastening: Through-hole mounting, Adhesive   |

Accessories

Reflective tapes for standard applications

|                                                                                   | Part no. | Designation   | Article         | Description                                                                                                                                             |
|-----------------------------------------------------------------------------------|----------|---------------|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50108300 | REF 4-A-50x50 | Reflective tape | Design: Rectangular<br>Reflective surface: 50 mm x 50 mm<br>Material: Plastic<br>Chemical designation of the material: PMMA<br>Fastening: Self-adhesive |

| Note                                                                             |                                                                                                                           |
|----------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
|  | A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page. |