

Technical data sheet

Tower light element

Part no.: 50130457

E4-MW2

Contents

- Technical data
- Electrical connection
- Notes
- Accessories



For illustration purposes only



Technical data

Basic data

Series	E4
--------	----

Connection

Connection 1

Type of connection	Terminal
Type of terminal	Push-in technology

Mechanical data

Design	Cylindrical
Dimension (Ø x L)	40 mm x 56 mm
Housing material	Plastic
Net weight	132 g
Housing color	Black
Design of mounting device	Bracket mounting
Type of fastening, at system	Screw type / vertical
Lens modules	Max. 10 pieces
Module holder	Two-sided
Number of end caps	2 Piece(s)

Environmental data

Ambient temperature, operation	-30 ... 60 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 66
----------------------	-------

Classification

Customs tariff number	85318070
ECLASS 5.1.4	27371235
ECLASS 8.0	27371235
ECLASS 9.0	27371232
ECLASS 10.0	27371235
ECLASS 11.0	27371235
ECLASS 12.0	27371235
ECLASS 13.0	27371235
ECLASS 14.0	27371235
ECLASS 15.0	27371235
ECLASS 16.0	27371235
ETIM 5.0	EC001154
ETIM 6.0	EC001154
ETIM 7.0	EC001154
ETIM 8.0	EC001154
ETIM 9.0	EC001154
ETIM 10.0	EC001154
UNSPSC 26.08	32151500

Electrical connection

Connection 1

Type of connection	Terminal
Type of terminal	Push-in technology

Notes



Observe intended use!



- ⌘ This product is not a safety sensor and is not intended as personnel protection.
- ⌘ The product may only be put into operation by competent persons.
- ⌘ Only use the product in accordance with its intended use.






For UL applications:



- ⌘ For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).

Accessories

General

	Part no.	Designation	Article	Description
	50130454	E4-V1-BZ1	Tower light element	Signaling: Acoustic Current consumption, max.: 39 mA Design: Cylindrical Fastening: Bayonet system Operational controls: DIP switch Ambient temperature: -30 ... 60 °C Degree of protection: IP 66 Tone type: Continuous or pulse tone Sound pressure: 80 dB Number of tones: 1 Piece(s)
	50130449	E4-V1-DB-R	Tower light element	Signaling: Optical Supply voltage: 24 V, AC/DC Current consumption, max.: 32 mA Design: Cylindrical Fastening: Bayonet system Illuminant: LED/24V Signal image: Flashing light Lens color: Red Angle of radiation: 360° Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130443	E4-V1-DS-R	Tower light element	Signaling: Optical Supply voltage: 24 V, AC/DC Current consumption, max.: 27 mA Design: Cylindrical Fastening: Bayonet system Illuminant: LED/24V Signal image: Continuous light Lens color: Red Angle of radiation: 360° Ambient temperature: -30 ... 60 °C Degree of protection: IP 66

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.