Leuze

Technical data sheet Optical data transmission

Part no.: 50131030 DDLS 508 120.0 L



 Leuze electronic GmbH + Co. KG
 info@leuze.com • www.leuze.com
 changes

 The Sensor People
 In der Braike 1, D-73277 Owen/Germany
 Phone: +49 7021 573-0 • Fax: +49 7021 573-199
 eng • 2024-07-11

Technical data

Encoding

Leuze


Basic data	
Series	DDLS 500
Special version	
Special version	Integrated laser alignment aid
Optical data	
Working range	100 120,000 mm
Light source	Laser
Transmission frequency	F0
Opening angle	1 °
Electrical data	
Performance data	
Supply voltage U _B	18 30 V, DC
Inputs	1 Diago(a)
Number of digital switching inputs	1 Piece(s)
Outputs	
Outputs Number of digital switching outputs	1 Piece(s)
······································	
Interface	
Transmission protocol	EtherNET/IP
	PROFINET IO / RT
	PROFINET IRT
	PROFINET/PROFIsafe
	TCP/IP 100 Mbit
Туре	EtherNet TCP/ IP, PROFINET, PROFIsafe over PROFINET
Ethernet	Transaction
Architecture	Transparent
Address assignment	None
Transmission speed Function	100 Mbit/s Process
Switch functionality	None TCP/IP , UDP
Transmission protocol	
PROFINET	
Function	Process
Conformance class	В
Switch functionality	None
Transmission speed	100 Mbit/s
Connection	
Number of connections	2 Piece(s)
Connection 1	
Type of connection	Connector
Designation on device	POWER
Thread size	M12
Туре	Male
No. of pins	5 -pin


A-coded


Connection 2	
Type of connection	Connector
Designation on device	BUS
Thread size	M12
Туре	Female
No. of pins	4 -pin
Encoding	D-coded
5	
Mechanical data	
Dimension (W x H x L)	100 mm x 156 mm x 99.5 mm
Housing material	Metal
Net weight	1,255 g
Operation and display	
Type of display	Bar graph
	LED
Environmental data	
Ambient temperature, operation	-5 50 °C
Ambient temperature, storage	-35 70 °C
Certifications	
Degree of protection	IP 65
Certifications	c UL US
Test procedure for EMC in accordance	EN 1000-6-4
with standard	EN 61000-6-2
Test procedure for noise in accordance with standard	EN 60068-2-64
Test procedure for oscillation in accordance with standard	EN 60068-2-6
Test procedure for shock in accordance with standard	EN 60068-2-27
accordance with standard	
Classification	
Customs tariff number	84718000
ECLASS 5.1.4	19039001
ECLASS 8.0	19179090
ECLASS 9.0	19179090
ECLASS 10.0	19170506
ECLASS 11.0	19170506
ECLASS 12.0	19170506
ECLASS 13.0	19170506
	10170500
ECLASS 14.0	19170506
ETIM 5.0	EC000515
ETIM 5.0	EC000515
ETIM 5.0 ETIM 6.0	EC000515 EC000515
ETIM 5.0 ETIM 6.0 ETIM 7.0	EC000515 EC000515 EC000515

Dimensioned drawings

All dimensions in millimeters







A Center axis of transmitter and alignment laser

B Center axis of transmitter and receiver

C Center axis of receiver

Leuze

Electrical connection

Connection 1	POWER
Function	Signal IN
	Signal OUT
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin **Pin assignment**

1	VIN	
2	101	
3	GND	3
4	102	
5	FE/SHIELD	

Connection 2

Connection 2	BUS
Function	BUS IN
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded

Pin	Pin assignment
1	TD+
2	RD+
3	TD-
4	RD-

Operation and display

LE	ED	Display	Meaning
1	AUT	Off	Operating mode not active
		Green, continuous light	Operating mode "Automatic"
2	MAN	Off	Operating mode not active
		Green, continuous light	Operating mode "Manual"
3	ADJ	Off	Operating mode not active
		Green, continuous light	Operating mode "Adjust"
4	LAS	Off	Operating mode not active
		Green, continuous light	Operating mode "Alignment-laser mounting support"
5	LLC	Off	Operating mode not active
		Green, continuous light	LLC without interruption
		Red, continuous light	LLC interrupted at least once
6	PWR	Off	No supply voltage
		Green, flashing	Device ok, initialization phase
		Green, continuous light	Data transmission active
		Red, flashing	Data transmission interrupted
		Red, continuous light	Device error
7	TMP	Off	Operating temperature OK
		Orange, continuous light	Operating temperature critical

Leuze

2 Еф



Operation and display



LEI	D	Display	Meaning
7	ТМР	Red, continuous light	Operating temperature exceeded or not met
8	LSR	Off	With function reserve
		Orange, continuous light	Device OK, warning set
9	FRE	Off	Transmission frequency F1 preselected
		Green, continuous light	Transmission frequency F2 preselected (factory setting)
10		Off	Fault
		Green, continuous light	No data transmission
		Orange, continuous light	Data transmission active
11	7 TMP Red, continuous light Operating temperature exceeded 8 LSR Off With function reserve 0range, continuous light Device OK, warning set Device OK, warning set 9 FRE Off Transmission frequency F1 press Green, continuous light Transmission frequency F2 press 10 OLK Off 0 Green, continuous light No data transmission 0 Orange, continuous light No data transmission 0 Orange, continuous light Data transmission active 11 ERL Off No cable-connected link to the operation of the ope	Off	Link OK
		Orange, continuous light	Missing link (Ethernet cable connection) on the second device
		No cable-connected link to the connected device	
12	LINK	Off	No cable-connected link to the connected device
		Green, continuous light	Link OK
		Orange, continuous light	Data transmission active
13		2 red, 2 orange and 4 green	Received signal level

Suitable transmitters

 Part no.	Designation	Article	Description
50131030	DDLS 508 120.0 L	Optical data transmission	Special version: Integrated laser alignment aid Working range: 100 120,000 mm Transmission frequency: F0 Interface: EtherNet TCP/IP, PROFINET Connection: Connector, M12

Part number code

Part designation: DDLS 5XXX YYY.Z A B CC

DDLS	Optical transceiver for digital data transmission
5XXX	Series 508i: without integrated web server for remote diagnostics 508i: with integrated web server for remote diagnostics 538: without integrated web server for remote diagnostics (EtherCAT) 548i: with integrated web server for remote diagnostics
YYY	Range for data transmission in m
Z	Frequency of the transmitter 0: Frequency F0 1: Frequency F1 2: Frequency F2 3: Frequency F3 4: Frequency F4
Α	Option L: integrated laser alignment aid (for transmitter/receiver) n/a: standard
В	Special equipment H: with heating n/a: no special equipment
сс	Special equipment W: transmission optics with larger opening angle (on request) n/a: no special equipment
Note	



A list with all available device types can be found on the Leuze website at www.leuze.com.


Notes

Leuze

Observe intended use!

✤ This product is not a safety sensor and is not intended as personnel protection.

b The product may only be put into operation by competent persons.



Do not expose users of telescopic optics!
The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1M as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.
Do not expose users of telescopic optics! The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1M as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.
Looking into the beam path for extended periods using telescope optics may damage the eye's retina. Never look using telescope optics into the la beam or in the direction of reflecting beams.
 CAUTION! The use of operating and adjusting devices other than those specified here or the carrying out of differing procedures may lead to dang exposure to radiation! The use of optical instruments or devices (e.g., magnifying glasses, binoculars) in combination with the device increases the danger of eye damage
boxerve the applicable statutory and local laser protection regulations.
The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device. Repairs must only be performed by Leuze electronic GmbH + Co. KG.

ATTENTION! LASER RADIATION – CLASS 1 LASER PRODUCT (alignment laser)

The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of **laser class 1** as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.

th The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1 as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.

- ♦ Observe the applicable statutory and local laser protection regulations.
- The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device.

Repairs must only be performed by Leuze electronic GmbH + Co. KG.

Accessories

Leuze

Connection technology - Connection cables

	Part no.	Designation	Article	Description
	50132079	KD U-M12-5A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC
Ŵ	50135074	KS ET-M12-4A-P7- 050	Connection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connector, LED: No Connection 2: Open end Shielded: Yes Cable length: 5.000 mm Sheathing material: PUR

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50137078	KSS ET-M12-4A- M12-4A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: Connector, M12, Axial, Male, D-coded, 4 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR
	50135081	KSS ET-M12-4A- RJ45-A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: RJ45 Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Connection technology - Connectors

	Part no.	Designation	Article	Description
-	50020501	KD 095-5A	Connector	Connection: Connector, M12, Axial, Female, A-coded, 5 -pin
Contraction of the second	50112155	S-M12A-ET	Connector	Suitable for interface: Ethernet Connection: Connector, M12, Axial, Male, D-coded, 4 -pin

Accessories

Leuze

Services

	Part no.	Designation	Article	Description
у. U	S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
	S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

	Note
6	A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.