

Technical data sheet Optical data transmission

Part no.: 50134407 DDLS 508i 200.3 L



Technical data

Encoding

Leuze


Basic data	
Series	DDLS 500
Special version	
Special version	Integrated laser alignment aid
	Not influenced by reflective surfaces
	Operation of parallel light axes
	Remote diagnosis via web server
Optical data	
•	400 000 000
Working range	100 200,000 mm
Light source	Laser
Transmission frequency	F3
Opening angle	1 °
Electrical data	
Derfermenes dete	
Performance data Supply voltage U _B	18 30 V, DC
Cappin rounde oB	
Inputs	
Number of digital switching inputs	1 Piece(s)
Outputs	
Number of digital switching outputs	1 Piece(s)
Interface	
Transmission protocol	TCP/IP 100 Mbit
Туре	EtherNet TCP/IP
Ethernet	
Architecture	Transparent
Address assignment	None
Transmission speed	100 Mbit/s
Function	Process
Switch functionality	None
Transmission protocol	TCP/IP , UDP
Connection	
Number of connections	2 Piece(s)
Connection 1	
Type of connection	Connector
Designation on device	POWER
Thread size	M12
Туре	Male
No. of pins	5 -pin
Encoding	A-coded
Connection 2	
Type of connection	Connector
Designation on device	BUS
Thread size	M12
Type	Female
No. of pins	4 -pin
110. 01 pillo	i Pili


D-coded


Dimension (W x H x L)	100 mm x 156 mm x 99.5 mm
lousing material	Metal
et weight	1,422 g
peration and display	
ype of display	Bar graph
	LED
ype of configuration	Software
	Via web browser
nvironmental data	
nbient temperature, operation	-5 50 °C
mbient temperature, storage	-35 70 °C
ertifications	
egree of protection	IP 65
ertifications	c UL US
est procedure for EMC in accordance	EN 1000-6-4
ith standard	EN 61000-6-2
est procedure for noise in accordance ith standard	EN 60068-2-64
	EN 60068-2-6
ccordance with standard est procedure for shock in	EN 60068-2-6 EN 60068-2-27
ccordance with standard est procedure for shock in	
ccordance with standard est procedure for shock in ccordance with standard	
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number	EN 60068-2-27 84718000
coordance with standard est procedure for shock in coordance with standard estimation e	EN 60068-2-27 84718000 19039001
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number CLASS 5.1.4 CLASS 8.0	EN 60068-2-27 84718000 19039001 19179090
coordance with standard est procedure for shock in coordance with standard lassification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0	EN 60068-2-27 84718000 19039001 19179090 19179090
coordance with standard est procedure for shock in coordance with standard lassification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0	EN 60068-2-27 84718000 19039001 19179090 19179090 19170506
ccordance with standard est procedure for shock in ccordance with standard lassification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0	EN 60068-2-27 84718000 19039001 19179090 19179090 19170506 19170506
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 12.0	EN 60068-2-27 84718000 19039001 19179090 19170506 19170506 19170506
est procedure for oscillation in ccordance with standard est procedure for shock in ccordance with standard classification cLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 12.0 CLASS 12.0 CLASS 13.0 CLASS 14.0	EN 60068-2-27 84718000 19039001 19179090 19170506 19170506 19170506 19170506
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 12.0	EN 60068-2-27 84718000 19039001 19179090 19170506 19170506 19170506
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 12.0 CLASS 13.0 CLASS 14.0 TIM 5.0	EN 60068-2-27 84718000 19039001 19179090 19170506 19170506 19170506 19170506 19170506 19170506
ccordance with standard est procedure for shock in ccordance with standard lassification ustoms tariff number CLASS 5.1.4 CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 9.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 11.0 CLASS 12.0 CLASS 13.0 CLASS 13.0 CLASS 14.0 TIM 5.0 TIM 6.0	EN 60068-2-27 84718000 19039001 19179090 19170506 19170506 19170506 19170506 19170506 19170506 EC000515
ccordance with standard est procedure for shock in ccordance with standard classification ustoms tariff number CLASS 5.1.4 CLASS 8.0 CLASS 9.0 CLASS 10.0 CLASS 11.0 CLASS 12.0 CLASS 13.0 CLASS 14.0	EN 60068-2-27 84718000 19039001 19179090 19179090 19170506 19170506 19170506 19170506 19170506 EC000515 EC000515

Dimensioned drawings

All dimensions in millimeters







- A Center axis of transmitter and alignment laser
- B Center axis of transmitter and receiver
- C Center axis of receiver

Leuze

Electrical connection

Connection 1	POWER
Function	Signal IN
	Signal OUT
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin **Pin assignment**

1	VIN	
2	IO1	
3	GND	3
4	102	
5	FE/SHIELD	4

Connection 2


Connection 2	BUS
Function	BUS IN
Type of connection	Connector
Thread size	M12
Туре	Female
Material	Metal
No. of pins	4 -pin
Encoding	D-coded


Pin	Pin assignment	
1	TD+	
2	RD+	
3	TD-	
4	RD-	

Operation and display

LE	ED	Display	Meaning
1	AUT	Off	Operating mode not active
		Green, continuous light	Operating mode "Automatic"
2	MAN	Off	Operating mode not active
		Green, continuous light	Operating mode "Manual"
3	ADJ	Off	Operating mode not active
		Green, continuous light	Operating mode "Adjust"
4	LAS	Off	Operating mode not active
		Green, continuous light	Operating mode "Alignment-laser mounting support"
5	LLC	Off	Operating mode not active
		Green, continuous light	LLC without interruption
		Red, continuous light	LLC interrupted at least once
6	PWR	Off	No supply voltage
		Green, flashing	Device ok, initialization phase
		Green, continuous light	Data transmission active
		Red, flashing	Data transmission interrupted
		Red, continuous light	Device error
7	TMP	Off	Operating temperature OK
		Orange, continuous light	Operating temperature critical







Operation and display

Leuze

LED)	Display	Meaning
7 1	ТМР	Red, continuous light	Operating temperature exceeded or not met
8 L	LSR	Off	With function reserve
		Orange, continuous light	Device OK, warning set
9 E	BUS	Off	not active for the DDLS 508i
10 0	OLK	Off	Fault
		Green, continuous light	No data transmission
		Orange, continuous light	Data transmission active
11 E	ERL	Off	Link OK
		Orange, continuous light	Missing link (Ethernet cable connection) on the second device
		Red, continuous light	No cable-connected link to the connected device
12 L	LINK	Off	No cable-connected link to the connected device
		Green, continuous light	Link OK
		Orange, continuous light	Data transmission active
	SIGNAL QUALITY	2 red, 2 orange and 4 green	Received signal level

Suitable receivers

 Part no.	Designation	Article	Description
50134408	DDLS 508i 200.4 L	Optical data transmission	Special version: Integrated laser alignment aid, Not influenced by reflective surfaces, Operation of parallel light axes, Remote diagnosis via web server Working range: 100 200.000 mm Transmission frequency: F4 Interface: EtherNet TCP/IP Connection: Connector, M12

Part number code

Part designation: DDLS 5XXX YYY.Z A B CC

DDLS	Optical transceiver for digital data transmission
5XXX	Series 508i: without integrated web server for remote diagnostics 508i: with integrated web server for remote diagnostics 538: without integrated web server for remote diagnostics (EtherCAT) 548i: with integrated web server for remote diagnostics
YYY	Range for data transmission in m
Z	Frequency of the transmitter 0: Frequency F0 1: Frequency F1 2: Frequency F2 3: Frequency F3 4: Frequency F4
A	Option L: integrated laser alignment aid (for transmitter/receiver) n/a: standard
В	Special equipment H: with heating n/a: no special equipment
сс	Special equipment W: transmission optics with larger opening angle (on request) n/a: no special equipment

	Note
1	∜ A list with all available device types can be found on the Leuze website at www.leuze.com.

Notes

Leuze

Observe intended use!

✤ This product is not a safety sensor and is not intended as personnel protection.

b The product may only be put into operation by competent persons.



Do not expose users of telescopic optics! The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1M as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.
* Do not expose users of telescopic optics! The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1M as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.
Scoking into the beam path for extended periods using telescope optics may damage the eye's retina. Never look using telescope optics into the l beam or in the direction of reflecting beams.
 CAUTION! The use of operating and adjusting devices other than those specified here or the carrying out of differing procedures may lead to dan exposure to radiation! The use of optical instruments or devices (e.g., magnifying glasses, binoculars) in combination with the device increases the danger of eye damaged.
by Observe the applicable statutory and local laser protection regulations.
✤ The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device. Repairs must only be performed by Leuze electronic GmbH + Co. KG.

ATTENTION! LASER RADIATION – CLASS 1 LASER PRODUCT (alignment laser)

The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of **laser class 1** as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.

th The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of laser class 1 as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.

- ♦ Observe the applicable statutory and local laser protection regulations.
- ^t The device must not be tampered with and must not be changed in any way. There are no user-serviceable parts inside the device.

Repairs must only be performed by Leuze electronic GmbH + Co. KG.

Accessories

Leuze

Connection technology - Connection cables

	Part no.	Designation	Article	Description
	50132079	KD U-M12-5A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC
Ŵ	50135074	KS ET-M12-4A-P7- 050	Connection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connector, LED: No Connection 2: Open end Shielded: Yes Cable length: 5.000 mm Sheathing material: PUR

Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50137078	KSS ET-M12-4A- M12-4A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: Connector, M12, Axial, Male, D-coded, 4 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR
	50135081	KSS ET-M12-4A- RJ45-A-P7-050	Interconnection cable	Suitable for interface: Ethernet Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin Connection 2: RJ45 Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

Connection technology - Connectors

	Part no.	Designation	Article	Description
-	50020501	KD 095-5A	Connector	Connection: Connector, M12, Axial, Female, A-coded, 5 -pin
Contraction of the second	50112155	S-M12A-ET	Connector	Suitable for interface: Ethernet Connection: Connector, M12, Axial, Male, D-coded, 4 -pin

Accessories

Leuze

Services

 Part no.	Designation	Article	Description
S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours. Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

	Note
6	A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.