


## Technical data sheet Interconnection cable

Part no.: 50130765

KDS U-M12-4A-M12-4A-P1-020-DP

### Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



## Technical data

### Basic data

|             |                             |
|-------------|-----------------------------|
| Application | Oil and lubricant resistant |
|-------------|-----------------------------|

### Connection

#### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Female    |
| No. of pins        | 4 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |
| Connector, LED     | Yes       |

#### Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Male      |
| No. of pins        | 4 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |

#### Cable properties

|                                   |   |
|-----------------------------------|---|
| Number of conductors              | 4 Piece(s)  |
| Wire cross section                | 0.34 mm <sup>2</sup>  |
| AWG                               | 22  |
| Sheathing color                   | Black   |
| Shielded                          | No  |
| Silicone-free                     | Yes   |
| Cable design                      | Interconnection cable   |
| Cable diameter (external)         | 4.7 mm  |
| Cable length                      | 2,000 mm  |
| Sheathing material                | PUR   |
| Wire insulation                   | PP  |
| Traverse rate                     | Max. 3.3 m/s with horiz. traverse path of 5m and max. acceleration of 5m/s <sup>2</sup>   |
| Suitability for drag chains       | Yes   |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable  |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |
| Torsion suitability               | ±180° / m (max. 2 mio. cycles with 35 cycles / min)   |

### Mechanical data

|   |                          |
|---|--------------------------|
| Width across flats                      | 13 mm                    |
| Net weight                              | 100 g                    |
| Bending cycles                          | 5,000,000 Piece(s)       |
| Bending radius, flexible laying, min.   | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 5 x cable diameter  |

### Operation and display

|                |            |
|----------------|------------|
| Number of LEDs | 1 Piece(s) |
|----------------|------------|

### Environmental data

|  |               |
|--|---------------|
| Ambient temperature, operation, flexible use   | -25 ... 80 °C |
| Ambient temperature, operation, stationary use | -40 ... 80 °C |

### Certifications

|                      |                |
|----------------------|----------------|
| Degree of protection | IP 65<br>IP 67 |
| Approvals            | c UL US        |
| UL file number       | E366145        |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |
| UNSPSC 26.08          | 26121604 |

## Electrical connection

### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Female    |
| No. of pins        | 4 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |
| Connector, LED     | Yes       |

# Electrical connection

## Connection 2

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Male      |
| No. of pins        | 4 -pin    |
| Encoding           | A-coded   |
| Version            | Axial     |

## Circuit diagrams

### Wiring schematic

