

## Technical data sheet Interconnection cable

Part no.: 50135081

KSS ET-M12-4A-RJ45-A-P7-050

### Contents

- Technical data
- Electrical connection
- Circuit diagrams



For illustration purposes only



## Technical data

### Basic data

|                        |                             |
|------------------------|-----------------------------|
| Application            | Oil and lubricant resistant |
| Suitable for interface | Ethernet                    |

### Electrical data

#### Performance data

|                   |         |
|-------------------|---------|
| Operating voltage | 60 V DC |
|-------------------|---------|

### Connection

#### Connection 1

|                      |  |
|----------------------|--|
| Type of connection   | Connector  |
| Thread size          | M12  |
| Type                 | Male   |
| Handle body material | PUR  |
| No. of pins          | 4 -pin   |
| Encoding             | D-coded  |
| Version              | Axial  |
| Connector, LED       | No   |
| Lock                 | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

#### Connection 2

|                    |        |
|--------------------|--------|
| Type of connection | RJ45   |
| Type               | Male   |
| No. of pins        | 4 -pin |
| Version            | Axial  |

#### Cable properties

|                                   |   |
|-----------------------------------|---|
| Number of conductors              | 4 Piece(s)  |
| Wire cross section                | 0.34 mm <sup>2</sup>  |
| AWG                               | 22  |
| Sheathing color                   | Green   |
| Shielded                          | Yes   |
| Silicone-free                     | Yes   |
| Cable design                      | Interconnection cable   |
| Cable diameter (external)         | 6.7 mm  |
| Cable length                      | 5,000 mm  |
| Sheathing material                | PUR   |
| Wire insulation                   | PP  |
| Traverse rate                     | Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 2m/s <sup>2</sup>   |
| Suitability for drag chains       | Yes   |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable  |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |

### Mechanical data

|   |                                  |
|---|----------------------------------|
| Width across flats                      | 13 mm                            |
| Net weight                              | 289 g                            |
| Bending cycles                          | 2,000,000 Piece(s)               |
| Bending radius, flexible laying, min.   | One-time min. 5 x cable diameter |
| Bending radius, stationary laying, min. | One-time min. 5 x cable diameter |

### Operation and display

### Environmental data

|  |               |
|--|---------------|
| Ambient temperature, operation, flexible use   | -20 ... 60 °C |
| Ambient temperature, operation, stationary use | -20 ... 60 °C |

### Certifications

|                      |                       |
|----------------------|-----------------------|
| Degree of protection | IP 65                 |
|                      | IP 67, IP 20 for RJ45 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| ECLASS 5.1.4          | 27279201 |
| ECLASS 8.0            | 27279218 |
| ECLASS 9.0            | 27060311 |
| ECLASS 10.0           | 27060311 |
| ECLASS 11.0           | 27060311 |
| ECLASS 12.0           | 27060311 |
| ECLASS 13.0           | 27060311 |
| ECLASS 14.0           | 27060311 |
| ECLASS 15.0           | 27060311 |
| ECLASS 16.0           | 27060311 |
| ETIM 5.0              | EC001855 |
| ETIM 6.0              | EC001855 |
| ETIM 7.0              | EC001855 |
| ETIM 8.0              | EC001855 |
| ETIM 9.0              | EC001855 |
| ETIM 10.0             | EC001855 |
| UNSPSC 26.08          | 26121604 |

## Electrical connection

### Connection 1

|                      |           |
|----------------------|-----------|
| Type of connection   | Connector |
| Thread size          | M12       |
| Type                 | Male      |
| Handle body material | PUR       |

# Electrical connection

## Connection 1

|                |  |
|----------------|--|
| No. of pins    | 4 -pin   |
| Encoding       | D-coded  |
| Version        | Axial  |
| Connector, LED | No   |
| Lock           | Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking |

## Connection 2

|                    |      |
|--------------------|------|
| Type of connection | RJ45 |
|--------------------|------|

# Circuit diagrams

## Wiring schematic

