

# **Technical data sheet Light curtain transmitter**

Part no.: 50118627

CML730i-T10-2720.A-M12



### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Suitable receivers
- Part number code
- Notes
- Accessories



## **Technical data**



### Basic data

Series	730
Operating principle	Throughbeam principle
Device type	Transmitter
Contains	2x BT-NC sliding block
Application	Detection of transparent objects
	Object measurement
Special version	
Special version	Crossed-beam scanning

Diagonal-beam scanning

Parallel-beam scanning

### **Optical data**

Option data	
Operating range	0.3 9.5 m
Operating range	Guaranteed operating range
Operating range, transparent media	0.3 3.5 m
Operating range limit	0.2 12 m
Operating range limit	Typical operating range
Measurement field length	2,720 mm
Number of beams	272 Piece(s)
Beam spacing	10 mm
Light source	LED, Infrared
Wavelength	940 nm

#### Measurement data

Minimum object diameter	20 mm
Electrical data	
Protective circuit	Polarity reversal protection
	Short circuit protected

### Performance data

r en onnance data	
Supply voltage U <sub>B</sub>	18 30 V, DC
Residual ripple	0 15 %, From U <sub>B</sub>
Open-circuit current	0 435 mA, The specified values refer to the entire package consisting of transmitter and receiver.

Transient protection

### **Time behavior**

Readiness delay	450 ms
Cycle time	2.92 ms

## Connection

Number of connections	1 Piece(s)	
Plug outlet	Axial	
Connection 1		
Function	Connection to receiver	

Tunction	Connection to receive
Type of connection	Connector
Thread size	M12
Type	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

### Mechanical data

Design	Cubic
Dimension (W x H x L)	29 mm x 35.4 mm x 2,795 mm
Housing material	Metal
Metal housing	Aluminum
Lens cover material	Plastic
Net weight	2,700 g
Housing color	Silver
Type of fastening	Groove mounting
	Via optional mounting device
	Via optional mounting device

## Operation and display

Type of display	LED	
Number of LEDs	1 Piece(s)	

### **Environmental data**

Ambient temperature, operation	-30 60 °C	
Ambient temperature, storage	-40 70 °C	

#### Certifications

Degree of protection	IP 65
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2

### Classification

Customs tariff number	90314990
ECLASS 5.1.4	27270910
ECLASS 8.0	27270910
ECLASS 9.0	27270910
ECLASS 10.0	27270910
ECLASS 11.0	27270910
ECLASS 12.0	27270910
ECLASS 13.0	27270910
ECLASS 14.0	27270910
ECLASS 15.0	27270910
ETIM 5.0	EC002549
ETIM 6.0	EC002549
ETIM 7.0	EC002549
ETIM 8.0	EC002549
ETIM 9.0	EC002549
ETIM 10.0	EC002549

## **Dimensioned drawings**



All dimensions in millimeters



- Beam spacing 10 mm
- В Measurement field length 2720 mm
- M6 thread
- Fastening groove
- Profile length 2728 mm
- Transmitter
- Receiver
- 5 mm




## **Electrical connection**



### **Connection 1**

Function	Connection to receiver
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Metal
No. of pins	5 -pin
Encoding	A-coded

Pin	Pin assignment
1	FE/SHIELD
2	V+
3	GND
4	RS 485 Tx+
5	RS 485 Tx-



## **Operation and display**

LED	Display	Meaning
1	Green, continuous light	Continuous mode
	Off	No communication with the receiver / waiting for trigger
	green, flashing in sync with the measurement	Measurement frequency display

## Suitable receivers

Part no.	Designation	Article	Description
50118708	CML730i-R10- 2720.A/CN-M12	Light curtain receiver	Operating range: 0.3 9.5 m Interface: CANopen Connection: Connector, M12, Axial, 8 -pin
50118884	CML730i-R10- 2720.A/CV-M12	Light curtain receiver	Operating range: 0.3 9.5 m Analog outputs: 2 Piece(s), Voltage, Current Connection: Connector, M12, Axial, 8 -pin
50123324	CML730i-R10- 2720.A/D3-M12	Light curtain receiver	Operating range: 0.3 9.5 m Interface: RS 485 Modbus Connection: Connector, M12, Axial, 8 -pin
50118790	CML730i-R10- 2720.A/L-M12	Light curtain receiver	Operating range: 0.3 9.5 m Interface: IO-Link Connection: Connector, M12, Axial, 8 -pin

## Suitable receivers



Part no.	Designation	Article	Description
50123168	CML730i-R10- 2720.A/PB-M12	Light curtain receiver	Operating range: 0.3 9.5 m Interface: PROFIBUS DP Connection: Connector, M12, Axial, 8 -pin
50131774	CML730i-R10- 2720.A/PN-M12	Light curtain receiver	Operating range: 0.3 9.5 m Interface: PROFINET Connection: Connector, M12, Axial, 8 -pin

## Part number code

Part designation: CML7XXi-YZZ-AAAA.BCCCDDD-EEEFFF

CML	Operating principle Measuring light curtain				
7XXi	Series 720i: 720i series 730i: 730i series				
Υ	Device type T: transmitter R: receiver				
ZZ	Beam spacing 05: 5 mm 10: 10 mm 20: 20 mm 40: 40 mm				
AAAA	Measurement field length [mm], dependent on beam spacing				
В	Equipment A: Axial connector outlet R: Rear connector outlet				
ccc	Interface L: IO-Link /CN: CANopen /PB: PROFIBUS /PN: PROFINET /CV: Analog current and voltage output /D3: RS 485 Modbus				
DDD	Special equipment -PS: Power Setting				
EEE	Electrical connection M12: M12 connector				
FFF	-EX: Explosion protection				

## Note



### **Notes**





### Observe intended use!



- \$ This product is not a safety sensor and is not intended as personnel protection.
- \$ The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

### For UL applications:



- 🔖 For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).
- \$\text{\text{These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

## **Accessories**

## Connection technology - Interconnection cables

	Part no.	Designation	Article	Description
	50129781	KDS DN-M12-5A- M12-5A-P3-050	Interconnection cable	Suitable for interface: DeviceNet, CANopen Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin Shielded: Yes Cable length: 5,000 mm Sheathing material: PUR

## Mounting technology - Mounting brackets

	Part no.	Designation	Article	Description
	50142900	BT 700M.5-2SET	Mounting device set	Design of mounting device: Bracket mounting Fastening, at system: Through-hole mounting, T slotted hole Mounting bracket, at device: Screw type, Sliding block Type of mounting device: Rigid Material: Steel
P.C.	429393	BT-2HF	Mounting bracket set	Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Turning, 360° Material: Metal, Plastic

## Configuration devices

	Part no.	Designation	Article	Description
IS	50121098	SET MD12-US2-IL1.1 + Zub.	Diagnostics set	Interface: USB Connections: 2 Piece(s) Degree of protection: IP 20

## **Accessories**



## Services

 Part no.	Designation	Article	Description
S981001	CS10-S-110	Start-up support	Details: Performed at location of customer's choosing, duration: max. 10 hours.  Conditions: Devices and connection cables are already mounted, price not including travel costs and, if applicable, accommodation expenses.
S981005	CS10-T-110	Product training	Details: Location and content to be agreed upon, duration: max. 10 hours. Conditions: Price not including travel costs and, if applicable, accommodation expenses.

### Note



♥ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.