

Technical data sheet

Reflector

Part no.: 50116939

TK 10.P

Contents

- Technical data
- Dimensioned drawings



For illustration purposes only



Technical data

Basic data

Area of application	Pharmaceutical
---------------------	----------------

Mechanical data

Design	Round
Triple reflector size	1.5 mm
Mounting dimension, thickness	4 mm
Mounting dimension, diameter	10 mm
Reflective surface, diameter	8.5 mm
Reflector material	Plastic
Material of base material	Plastic
Polarization-changing	Yes
Chemical designation, reflector material	PES
Structure, active surface	Triple
Net weight	1 g
Type of fastening	Rear side can be glued
Compatibility of materials	ECOLAB

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
ECLASS 5.1.4	27279203
ECLASS 8.0	27279203
ECLASS 9.0	27273601
ECLASS 10.0	27273601
ECLASS 11.0	27273601
ECLASS 12.0	27273601
ECLASS 13.0	27273601
ECLASS 14.0	27273601
ECLASS 15.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467
ETIM 8.0	EC002467
ETIM 9.0	EC002467
ETIM 10.0	EC002467

Dimensioned drawings

All dimensions in millimeters

