

## Technical data sheet

### Capacitive sensor

Part no.: 50135754

LCS-1M12M-N08NNC-K020P

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Circuit diagrams
- Operation and display
- Part number code
- Notes
- Accessories



For illustration purposes only



## Technical data

### Basic data

|                            |            |
|----------------------------|------------|
| Series                     | LCS-1      |
| Switching distance $S_n$   | 1 ... 8 mm |
| Assured switching distance | 8 mm       |

### Characteristic parameters

|      |           |
|------|-----------|
| MTTF | 226 years |
|------|-----------|

### Electrical data

|                    |                                                         |
|--------------------|---------------------------------------------------------|
| Protective circuit | Polarity reversal protection<br>Short circuit protected |
|--------------------|---------------------------------------------------------|

#### Performance data

|                                          |                        |
|------------------------------------------|------------------------|
| Supply voltage $U_B$                     | 10 ... 30 V, DC        |
| Residual ripple                          | 0 ... 10 %, From $U_B$ |
| Open-circuit current                     | 15 mA                  |
| Temperature drift, max. (in % of $S_r$ ) | 20 %                   |
| Repeatability, max. (in % of $S_r$ )     | 2 %                    |
| Rated operating current                  | 100 mA                 |

#### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 1 Piece(s) |
|-------------------------------------|------------|

#### Switching outputs

|              |                          |
|--------------|--------------------------|
| Type         | Digital switching output |
| Voltage type | DC                       |

#### Switching output 1

|                     |                           |
|---------------------|---------------------------|
| Assignment          | Connection 1, conductor 2 |
| Switching element   | Transistor, NPN           |
| Switching principle | NC (normally closed)      |

### Time behavior

|                     |        |
|---------------------|--------|
| Switching frequency | 100 Hz |
|---------------------|--------|

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

#### Connection 1

|                      |                              |
|----------------------|------------------------------|
| Function             | Signal OUT<br>Voltage supply |
| Type of connection   | Cable                        |
| Cable length         | 2,000 mm                     |
| Sheathing material   | PUR                          |
| Number of conductors | 3 -wire                      |
| Wire cross section   | 0.14 mm <sup>2</sup>         |

### Mechanical data

|                         |                             |
|-------------------------|-----------------------------|
| Design                  | Cylindrical                 |
| Dimension (Ø x L)       | 12 mm x 61 mm               |
| Thread size             | M12 x 1 mm                  |
| Type of installation    | Non-embedded                |
| Housing material        | Metal<br>Stainless steel    |
| Stainless steel housing | V2A                         |
| Sensing face material   | Plastic, Polybutylene (PBT) |
| Cover material          | Plastic, Polybutylene (PBT) |
| Net weight              | 61 g                        |

### Operation and display

|                                     |                                    |
|-------------------------------------|------------------------------------|
| Type of display                     | LED                                |
| Number of LEDs                      | 2 Piece(s)                         |
| Operational controls                | Multiturn potentiometer (20 turns) |
| Function of the operational control | Sensitivity adjustment             |
| Switching distance, adjustable      | Yes                                |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -25 ... 85 °C |
|--------------------------------|---------------|

### Certifications

|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
| Protection class     | III           |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Correction factors


|                            |               |
|----------------------------|---------------|
| Acetone                    | 0.75          |
| Acrylic resin              | 0.1 ... 0.25  |
| Alcohol                    | 0.85          |
| Ammonia                    | 0.7 ... 0.85  |
| Aniline                    | 0.4           |
| Gasoline                   | 0.1           |
| Celluloid                  | 0.15          |
| Liquid chlorine            | 0.1           |
| Ebonite                    | 0.15          |
| Epoxy resin                | 0.15 ... 0.35 |
| Crude oil                  | 0.05          |
| Ethanol                    | 0.85          |
| Ethylene glycol            | 0.93          |
| Freon R22 and 502 (liquid) | 0.35          |
| Grain                      | 0.15 ... 0.3  |
| Glass                      | 0.2 ... 0.55  |
| Glycerin                   | 0.98          |
| Rubber                     | 0.15 ... 0.9  |
| Wood, wet                  | 0.6 ... 0.85  |
| Wood, dry                  | 0.1 ... 0.4   |
| Carbon dioxide             | 0             |
| Air                        | 0             |
| Marble                     | 0.5           |
| Flour                      | 0.05          |
| Melamine resin             | 0.25 ... 0.55 |
| Milk powder                | 0.2           |
| Nylon                      | 0.2 ... 0.3   |
| Oil-containing paper       | 0.25          |
| Paper                      | 0.1           |
| Polyamide                  | 0.3           |
| Polyester resin            | 0.15 ... 0.5  |
| Pressboard                 | 0.1 ... 0.3   |
| PTFE                       | 0.1           |
| Quartz glass               | 0.2           |
| Salt                       | 0.35          |
| Sand                       | 0.15 ... 0.3  |
| Water                      | 1             |
| Cement dust                | 0.25          |
| Sugar                      | 0.15          |

Technical data

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270102 |
| ECLASS 8.0            | 27270102 |
| ECLASS 9.0            | 27270102 |
| ECLASS 10.0           | 27270102 |
| ECLASS 11.0           | 27270102 |
| ECLASS 12.0           | 27274201 |
| ECLASS 13.0           | 27274201 |
| ECLASS 14.0           | 27274201 |
| ECLASS 15.0           | 27274201 |
| ETIM 5.0              | EC002715 |
| ETIM 6.0              | EC002715 |
| ETIM 7.0              | EC002715 |
| ETIM 8.0              | EC002715 |
| ETIM 9.0              | EC002715 |
| ETIM 10.0             | EC002715 |

Dimensioned drawings

All dimensions in millimeters



Electrical connection


Connection 1

|                      |                |
|----------------------|----------------|
| Function             | Signal OUT     |
|                      | Voltage supply |
| Type of connection   | Cable          |
| Cable length         | 2,000 mm       |
| Sheathing material   | PUR            |
| Number of conductors | 3 -wire        |
| Wire cross section   | 0.14 mm²       |

Electrical connection

| Conductor color | Conductor assignment |
|-----------------|----------------------|
| Brown           | 10 - 30 V DC         |
| Black           | OUT                  |
| Blue            | GND                  |

Circuit diagrams



Operation and display

| LED | Display                  | Meaning                          |
|-----|--------------------------|----------------------------------|
| 1   | Green, continuous light  | Ready                            |
| 2   | Yellow, continuous light | Switching output/switching state |

Part number code

Part designation: LCS-ABBBC-DDDEFF-GHHHIJJJ KK

|     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| LCS | <b>Operating principle</b><br>LCS: capacitive sensor                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| A   | <b>Series</b><br>1: series 1 "Extended"<br>2: series 2 "Advanced"                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| BBB | <b>Design</b><br>M12: series with M12 x 1 external thread<br>M18: series with M18 x 1 external thread<br>M30: series with M30 x 1.5 external thread<br>Q40: series in cubic design, length 40 mm<br>Q54: series in cubic design, length 54 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| C   | <b>Housing material</b><br>B: Brass<br>M: metal<br>P: plastic/PBT<br>T: PTFE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| DDD | <b>Measurement range / type of installation</b><br>F03: typ. range limit 3.0 mm / embedded installation<br>F04: typ. range limit 4.0 mm / embedded installation<br>F05: typ. range limit 5.0 mm / embedded installation<br>F06: typ. range limit 6.0 mm / embedded installation<br>F08: typ. range limit 8.0 mm / embedded installation<br>F10: typ. range limit 10.0 mm / embedded installation<br>F15: typ. range limit 15.0 mm / embedded installation<br>F20: typ. range limit 20.0 mm / embedded installation<br>N06: typ. range limit 6.0 mm / non-embedded installation<br>N08: typ. range limit 8.0 mm / non-embedded installation<br>N15: typ. range limit 15.0 mm / non-embedded installation<br>N25: typ. range limit 25.0 mm / non-embedded installation<br>N30: typ. range limit 30.0 mm / non-embedded installation |
| E   | <b>Output function</b><br>B: NC and NO contact<br>N: NPN<br>P: PNP                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |

## Part number code

|     |                                                                                                  |
|-----|--------------------------------------------------------------------------------------------------|
| FF  | <b>Switching</b><br>NC: Normally closed contact<br>NO: normally open contact<br>NP: programmable |
| G   | <b>Connection cable</b><br>K: Cable<br>n/a: no cable                                             |
| HHH | <b>Cable length</b><br>020: length 2,000 mm<br>003: length 300 mm<br>n/a: no cable               |
| I   | <b>Cable material</b><br>P: PUR<br>T: PTFE<br>V: PVC                                             |
| JJJ | <b>Electrical connection</b><br>M08: M8 connector, 3-pin<br>M12: M12 connector, 4-pin (plug)     |
| KK  | <b>Special equipment</b><br>L: IO-Link interface<br>T: teach-in<br>n/a: no special equipment     |

## Note



A list with all available device types can be found on the Leuze website at [www.leuze.com](http://www.leuze.com).

## Notes



## Observe intended use!



- This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

## Accessories

## Mounting technology - Other

|                                                                                    | Part no. | Designation | Article | Description                                                                                                                                                                                                         |
|------------------------------------------------------------------------------------|----------|-------------|---------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50111499 | MC 012K     | Clamp   | Diameter, inner: 12 mm<br>Design of mounting device: Mounting clamp<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Clampable<br>Type of mounting device: Rigid<br>Material: Plastic |

## Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.