

## Technical data sheet

### Dynamic reference diffuse sensor


Part no.: 50150299

DRT35C.3/LT-200-M12



#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Part number code
- Notes
- Further information
- Accessories



## Technical data

### Basic data

|                     |                               |
|---------------------|-------------------------------|
| Series              | 35C                           |
| Operating principle | Reference teach on background |

### Special version

|                 |             |
|-----------------|-------------|
| Special version | Teach input |
|-----------------|-------------|

### Optical data

|                          |   |
|--------------------------|---|
| Operating range          | 0.05 ... 0.15 m, Max. distance to reference surface |
| Adjustment range         | 50 ... 150 mm                                       |
| Light source             | LED, Red  |
| Wavelength               | 640 nm  |
| Transmitted-signal shape | Pulsed  |
| LED group                | Exempt group (in acc. with EN 62471)                |

### Electrical data

|                    |   |
|--------------------|---|
| Protective circuit | Polarity reversal protection<br>Short circuit protected |
|--------------------|---|

#### Performance data

|                      |  |
|----------------------|--|
| Supply voltage $U_B$ | 12 ... 30 V, DC, Incl. residual ripple |
| Residual ripple      | 0 ... 15 %, From $U_B$                 |
| Open-circuit current | 0 ... 40 mA                            |

#### Inputs

|                        |            |
|------------------------|------------|
| Number of teach inputs | 1 Piece(s) |
|------------------------|------------|

#### Teach inputs

|                   |                                     |
|-------------------|-------------------------------------|
| Type              | Teach input                         |
| Voltage type      | DC                                  |
| Switching voltage | high: $\geq 10V$<br>low: $\leq 2 V$ |
| Input resistance  | 22,000 $\Omega$                     |

#### Teach input 1

|                        |  |
|------------------------|--|
| Assignment             | Connection 1, pin 2                          |
| Function               | Keyboard lockout<br>Setting the teach levels |
| Active switching state | High   |

#### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 1 Piece(s) |
|-------------------------------------|------------|

#### Switching outputs

|                         |  |
|-------------------------|--|
| Type                    | Digital switching output                       |
| Voltage type            | DC   |
| Switching current, max. | 100 mA   |
| Switching voltage       | high: $\geq (U_B - 2.5V)$<br>low: $\leq 2.5 V$ |

#### Switching output 1

|                     |  |
|---------------------|--|
| Assignment          | Connection 1, pin 4                                  |
| Switching element   | Transistor, Push-pull                                |
| Switching principle | IO-Link / light switching (PNP)/dark switching (NPN) |

### Time behavior

|                     |                                 |
|---------------------|---------------------------------|
| Switching frequency | 750 Hz, (Teach level 1: 500 Hz) |
| Response time       | 0.66 ms                         |
| Readiness delay     | 300 ms                          |

### Interface

|                  |                      |
|------------------|----------------------|
| Type             | IO-Link              |
| <b>IO-Link</b>   |                      |
| COM mode         | COM3                 |
| Profile          | Smart sensor profile |
| Min. cycle time  | COM3 = 0.4 ms        |
| Frame type       | 2.5                  |
| Specification    | V1.1                 |
| Device ID        | 2143                 |
| SIO-mode support | Yes                  |
| Process data IN  | 8 bit                |
| Process data OUT | 8 bit                |

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

#### Connection 1

|                    |   |
|--------------------|---|
| Function           | Signal IN<br>Signal OUT<br>Voltage supply |
| Type of connection | Cable with connector                      |
| Cable length       | 200 mm                                    |
| Sheathing material | PVC                                       |
| Cable color        | Black                                     |
| Wire cross section | 0.2 mm <sup>2</sup>                       |
| Thread size        | M12                                       |
| Type               | Male                                      |
| Material           | Stainless steel                           |
| No. of pins        | 4 -pin                                    |
| Encoding           | A-coded                                   |

### Mechanical data

|                                 |  |
|---------------------------------|--|
| Dimension (W x H x L)           | 18.8 mm x 55.3 mm x 32.4 mm  |
| Housing material                | Stainless steel  |
| Material of operational control | Plastic (POM Hostaform C9021, copoly-ester Tritan TX1001), non-diffusive |
| Housing roughness               | Ra $\leq 0,8$ , Typical value for the stainless steel housing            |
| Stainless steel housing         | AISI 316L, DIN X2CrNiMo17132, W. No1.4404                                |
| Lens cover material             | Plastic (PMMA+) with scratch-resistant Indium protective coating         |
| Net weight                      | 120 g  |
| Housing color                   | Silver   |
| Type of fastening               | Through-hole mounting<br>Via optional mounting device                    |
| Compatibility of materials      | CleanProof+<br>ECOLAB<br>Johnson Diversey                                |

### Operation and display

|                                     |                               |
|-------------------------------------|-------------------------------|
| Type of display                     | LED                           |
| Number of LEDs                      | 2 Piece(s)                    |
| Operational controls                | Teach button                  |
| Function of the operational control | Teach-in on reference surface |

### Environmental data

|                                |                                      |
|--------------------------------|--------------------------------------|
| Ambient temperature, operation | -40 ... 60 °C, (70 °C $\leq 15$ min) |
| Ambient temperature, storage   | -40 ... 70 °C                        |

## Technical data

### Certifications

|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
|                      | IP 68         |
|                      | IP 69K        |
| Protection class     | III           |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270903 |
| ECLASS 8.0            | 27270903 |
| ECLASS 9.0            | 27270903 |
| ECLASS 10.0           | 27270903 |
| ECLASS 11.0           | 27270903 |
| ECLASS 12.0           | 27270903 |
| ECLASS 13.0           | 27270903 |
| ECLASS 14.0           | 27270903 |
| ECLASS 15.0           | 27270903 |
| ETIM 5.0              | EC001821 |
| ETIM 6.0              | EC001821 |
| ETIM 7.0              | EC001821 |
| ETIM 8.0              | EC001821 |
| ETIM 9.0              | EC001821 |
| ETIM 10.0             | EC001821 |

# Dimensioned drawings

All dimensions in millimeters



- A Green LED
- B Yellow LED
- C1 Optical axis (receiver)
- C2 Optical axis (transmitter)
- D Range adjustment

## Electrical connection

### Connection 1

|                    |                      |
|--------------------|----------------------|
| Function           | Signal IN            |
|                    | Signal OUT           |
|                    | Voltage supply       |
| Type of connection | Cable with connector |
| Cable length       | 200 mm               |
| Sheathing material | PVC                  |
| Cable color        | Black                |

## Electrical connection

### Connection 1

|                    |                     |
|--------------------|---------------------|
| Wire cross section | 0.2 mm <sup>2</sup> |
| Thread size        | M12                 |
| Type               | Male                |
| Material           | Stainless steel     |
| No. of pins        | 4 -pin              |
| Encoding           | A-coded             |

| Pin | Pin assignment  |
|-----|-----------------|
| 1   | V+              |
| 2   | Teach-in        |
| 3   | GND             |
| 4   | IO-Link / OUT 1 |



## Operation and display

| LED | Display                  | Meaning               |
|-----|--------------------------|-----------------------|
| 1   | Green, continuous light  | Operational readiness |
| 2   | Yellow, continuous light | Object detected       |

## Part number code

Part designation: **AAA35C d EE.GGH/IJ-K**

|               |   |
|---------------|---|
| <b>AAA35C</b> | <b>Operating principle</b><br>LS35C: Throughbeam photoelectric sensor transmitter<br>LE35C: Throughbeam photoelectric sensor receiver<br>PRK35C: Retro-reflective photoelectric sensor with polarization filter<br>HT35C: Diffuse reflection sensor with background suppression<br>DRT35C: Dynamic reference diffuse sensor   |
| <b>d</b>      | <b>Light type</b><br>n/a: red light<br>I: infrared light  |
| <b>EE</b>     | <b>Light source</b><br>n/a: LED<br>PP: Power PinPoint® LED<br>L1: laser class 1   |
| <b>GG</b>     | <b>Equipment</b><br>A: Autocollimation principle (single lens)<br>D: Detection of stretch-wrapped objects<br>X: extended model<br>XL: Extra long light spot<br>TT: autocollimation principle (single lens) for highly transparent bottles with tracking<br>R: greater operating range<br>XXR: super power transmitter   |
| <b>H</b>      | <b>Operating range adjustment</b><br>1: 270° potentiometer<br>2: multiturn potentiometer<br>3: teach-in via button  |
| <b>i</b>      | <b>Switching output/function OUT 1/IN: Pin 4 or black conductor</b><br>X: pin not used<br>8: activation input (activation with high signal)<br>L: IO-Link interface (SIO mode: PNP light switching, NPN dark switching)<br>4: PNP transistor output, light switching<br>6: push-pull switching output, PNP light switching, NPN dark switching<br>1: IO-Link / light switching (NPN) / dark switching (PNP) |

## Part number code

|          |   |
|----------|---|
| <b>J</b> | <b>Switching output / function OUT 2/IN: pin 2 or white conductor</b><br>T: teach-in via cable<br>G: Push-pull switching output, PNP dark switching, NPN light switching<br>X: pin not used<br>P: PNP transistor output, dark switching<br>6: push-pull switching output, PNP light switching, NPN dark switching |
|----------|---|

|          |  |
|----------|--|
| <b>K</b> | <b>Electrical connection</b><br>n/a: cable, standard length 2000 mm, 4-wire<br>200-M12: cable, length 200 mm with M12 connector, 4-pin, axial (plug)<br>M12: M12 connector, 4-pin (plug) |
|----------|--|

| Note |  |
|------|--|
|      | ⓘ A list with all available device types can be found on the Leuze website at <a href="http://www.leuze.com">www.leuze.com</a> . |

## Notes

| ⚠ Observe intended use! |   |
|-------------------------|---|
|                         | ⓘ This product is not a safety sensor and is not intended as personnel protection.<br>ⓘ The product may only be put into operation by competent persons.<br>ⓘ Only use the product in accordance with its intended use. |

## Further information

- Ambient temperature, operation: +70 °C permissible only briefly (≤ 15min)
- IP 69K only in combination with connector
- Light source: Average life expectancy 100,000h at an ambient temperature of 25 °C




## Accessories

### Connection technology - Connection unit


|  | Part no. | Designation           | Article        | Description   |
|--|----------|-----------------------|----------------|---|
|  | 50144900 | MD 798i-11-82/L5-2222 | IO-Link master | Current consumption, max.: 11,000 mA<br>Interface: IO-Link, Automatic protocol detection, EtherNet IP, Modbus TCP, PROFINET<br>Connections: 12 Piece(s)<br>Sensor connections: 8 Piece(s)<br>Degree of protection: IP 67, IP 65, IP 69K |

## Accessories



### Connection technology - Connection cables

|   | Part no. | Designation            | Article          | Description  |
|---|----------|------------------------|------------------|--|
|  | 50130657 | KD U-M12-4A-P1-050     | Connection cable | Application: Oil and lubricant resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PUR                |
|  | 50148349 | KD U-M12-4A-T0-020 F+B | Connection cable | Application: Hygienic and wet areas, Chemical resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 2,000 mm<br>Sheathing material: TPE |
|  | 50148350 | KD U-M12-4A-T0-050 F+B | Connection cable | Application: Chemical resistant, Hygienic and wet areas<br>Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: TPE |

### Mounting technology - Mounting brackets

|   | Part no. | Designation | Article          | Description   |
|---|----------|-------------|------------------|---|
|  | 50118543 | BT 300M.5   | Mounting bracket | Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type, Suited for M4 screws<br>Type of mounting device: Adjustable<br>Material: Stainless steel |

### Mounting technology - Rod mounts

|   | Part no. | Designation    | Article         | Description   |
|---|----------|----------------|-----------------|---|
|  | 50117252 | BTU 300M-D12   | Mounting system | Contains: 2x M4 x 25 screw, 2x M4 x 20 screw, 4x position washers<br>Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod, Sheet-metal mounting<br>Mounting bracket, at device: Screw type, Suited for M4 screws<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal                               |
|  | 50120425 | BTU 300M.5-D12 | Mounting system | Contains: 2x M4 x 25 screw, 2x M4 mounting nut, 2x M4 x 20 screw, 2x position washers<br>Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod, Sheet-metal mounting<br>Mounting bracket, at device: Screw type, Suited for M4 screws<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Stainless steel |

## Accessories

### Note



🔗 A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.