

## Technical data sheet

### Contour measurement system

Part no.: 50143556  
CMS748i-ENC1-0480-0960

#### Contents

- Set consists of
- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Notes
- Accessories



For illustration purposes only



## Set consists of

|                                                                                   | Quantity | Part no. | Designation                 | Article                   | Description                                                                                                                                                                                                                                                                                                                    |
|-----------------------------------------------------------------------------------|----------|----------|-----------------------------|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 2        | 424417   | BT-P40                      | Mounting bracket set      | Contains: BT-P40 clamp bracket, 2x<br>Bore hole 1: M6<br>Bore hole 2: M6<br>Design of mounting device: Mounting clamp<br>Fastening, at system: Groove mounting<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Clampable, Suitable for mounting in UDC-S2, DC-S2 device columns<br>Material: Metal |
|                                                                                   | 1        | 50118742 | CML730i-R05-480.A/L-M12     | Light curtain receiver    | Operating range: 0.1 ... 4.5 m<br>Interface: IO-Link<br>Connection: Connector, M12, Axial, 8 -pin                                                                                                                                                                                                                              |
|                                                                                   | 1        | 50118748 | CML730i-R05-960.A/L-M12     | Light curtain receiver    | Operating range: 0.1 ... 4.5 m<br>Interface: IO-Link<br>Connection: Connector, M12, Axial, 8 -pin                                                                                                                                                                                                                              |
|                                                                                   | 1        | 50118581 | CML730i-T05-480.A-M12       | Light curtain transmitter | Operating range: 0.1 ... 4 m<br>Connection: Connector, M12, Axial, 5 -pin                                                                                                                                                                                                                                                      |
|                                                                                   | 1        | 50118587 | CML730i-T05-960.A-M12       | Light curtain transmitter | Operating range: 0.1 ... 4 m<br>Connection: Connector, M12, Axial, 5 -pin                                                                                                                                                                                                                                                      |
|                                                                                   | 2        | 50129781 | KDS DN-M12-5A-M12-5A-P3-050 | Interconnection cable     | Application: Oil and lubricant resistant<br>Suitable for interface: DeviceNet, CANopen<br>Connection 1: Connector, M12, Axial, Female, A-coded, 5 -pin<br>Connection 2: Connector, M12, Axial, Male, A-coded, 5 -pin<br>Shielded: Yes<br>Cable length: 5,000 mm<br>Sheathing material: PUR                                     |
|                                                                                   | 3        | 50135146 | KDS S-M12-8A-M12-8A-P1-050  | Interconnection cable     | Application: Oil and lubricant resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 8 -pin<br>Connection 2: Connector, M12, Axial, Male, A-coded, 8 -pin<br>Shielded: Yes<br>Cable length: 5,000 mm<br>Sheathing material: PUR                                                                                   |
|                                                                                   | 1        | 50144568 | LMSMA35500024KH 10M16       | Rotary encoder            |                                                                                                                                                                                                                                                                                                                                |

## Set consists of

|                                                                                  | Quantity | Part no. | Designation    | Article        | Description                                                                                                                    |
|----------------------------------------------------------------------------------|----------|----------|----------------|----------------|--------------------------------------------------------------------------------------------------------------------------------|
|  | 1        | 50142931 | LSC748-ENC-100 | Switch cabinet | Supply voltage: 100 ... 263 V, AC<br>Switching inputs: 4 Piece(s)<br>Switching outputs: 4 Piece(s)<br>Connections: 13 Piece(s) |

## Technical data

## Basic data

|             |                                       |
|-------------|---------------------------------------|
| Series      | CMS 7xxi                              |
| Contains    | 1x dongle CMS700<br>1x rotary encoder |
| Order guide | Additional models on request          |

## Functions

|           |                                         |
|-----------|-----------------------------------------|
| Functions | For a minimum object height $\geq 5$ mm |
|-----------|-----------------------------------------|

## Optical data

|                                    |                |
|------------------------------------|----------------|
| Operating range                    | 0.1 ... 4.5 m  |
| Operating range, transparent media | 0.1 ... 1.75 m |
| Operating range limit              | 0.1 ... 6 m    |
| Measurement field length 1         | 480 mm         |
| Measurement field length 2         | 960 mm         |
| Beam spacing                       | 5 mm           |

## Electrical data

|                                                      |                                                                                 |
|------------------------------------------------------|---------------------------------------------------------------------------------|
| Protective circuit                                   | Polarity reversal protection<br>Short circuit protected<br>Transient protection |
| Output current, continuous current per channel, max. | 100 mA                                                                          |

## Performance data

|                      |               |
|----------------------|---------------|
| Supply voltage $U_B$ | 100 ... 263 V |
| Open-circuit current | 250 mA        |

## Inputs

|                                    |            |
|------------------------------------|------------|
| Number of digital switching inputs | 4 Piece(s) |
|------------------------------------|------------|

## Switching inputs

|                   |                         |
|-------------------|-------------------------|
| Type              | Digital switching input |
| Voltage type      | DC                      |
| Switching voltage | 24 V, VIN               |

## Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 4 Piece(s) |
|-------------------------------------|------------|

## Switching outputs

|                   |                          |
|-------------------|--------------------------|
| Type              | Digital switching output |
| Voltage type      | AC                       |
| Switching voltage | 24 V, VIN                |

## Interface

|      |                           |
|------|---------------------------|
| Type | EtherNet TCP/IP, PROFINET |
|------|---------------------------|

## Ethernet

|          |                              |
|----------|------------------------------|
| Function | Configuration / process data |
|----------|------------------------------|

## PROFINET

|          |                              |
|----------|------------------------------|
| Function | Configuration / process data |
|----------|------------------------------|

## Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 8 Piece(s) |
|-----------------------|------------|

## Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Earthing       |
| Type of connection | Earthing strap |
| Material           | Metal          |

## Connection 2

|                    |                   |
|--------------------|-------------------|
| Function           | Voltage supply    |
| Type of connection | Harting connector |
| Material           | Metal             |

## Connection 3

|                    |                                          |
|--------------------|------------------------------------------|
| Function           | Width measuring light curtain connection |
| Type of connection | Connector                                |
| Thread size        | M12                                      |
| Type               | Male                                     |
| Material           | Metal                                    |
| No. of pins        | 8 -pin                                   |
| Encoding           | A-coded                                  |

## Connection 4

|                    |                                           |
|--------------------|-------------------------------------------|
| Function           | Height measuring light curtain connection |
| Type of connection | Connector                                 |
| Thread size        | M12                                       |
| Type               | Male                                      |
| Material           | Metal                                     |
| No. of pins        | 8 -pin                                    |
| Encoding           | A-coded                                   |

## Connection 5

|                    |                                                                                    |
|--------------------|------------------------------------------------------------------------------------|
| Function           | Rotary encoder connection (not in combination with length measuring light curtain) |
| Type of connection | Connector                                                                          |
| Thread size        | M12                                                                                |
| Type               | Male                                                                               |
| Material           | Metal                                                                              |
| No. of pins        | 8 -pin                                                                             |
| Encoding           | A-coded                                                                            |

## Technical data

### Connection 6

|                    |                                     |
|--------------------|-------------------------------------|
| Function           | External Ethernet TCP/IP connection |
| Type of connection | Connector                           |
| Thread size        | M12                                 |
| Type               | Male                                |
| Material           | Metal                               |
| No. of pins        | 4 -pin                              |
| Encoding           | A-coded                             |

### Connection 7

|                    |                                   |
|--------------------|-----------------------------------|
| Function           | PROFINET IN connection (optional) |
| Type of connection | Connector                         |
| Thread size        | M12                               |
| Type               | Male                              |
| Material           | Metal                             |
| No. of pins        | 4 -pin                            |
| Encoding           | A-coded                           |

### Connection 8

|                    |                                    |
|--------------------|------------------------------------|
| Function           | PROFINET OUT connection (optional) |
| Type of connection | Connector                          |
| Thread size        | M12                                |
| Type               | Male                               |
| Material           | Metal                              |
| No. of pins        | 4 -pin                             |
| Encoding           | A-coded                            |

### Mechanical data

|                     |          |
|---------------------|----------|
| Design              | Cubic    |
| Housing material    | Metal    |
| Metal housing       | Aluminum |
| Lens cover material | Plastic  |
| Net weight          | 12,750 g |
| Housing color       | Gray     |
|                     | Red      |

**Note** Dimensions of individual set items, see dimensioned drawings

### Operation and display

|                       |                         |
|-----------------------|-------------------------|
| Type of display       | LED                     |
| Number of LEDs        | 3 Piece(s)              |
| Type of configuration | performed via webConfig |
| Operational controls  | Rotary switch           |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | 0 ... 45 °C   |
| Ambient temperature, storage   | -20 ... 70 °C |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 90314990 |
| ECLASS 5.1.4          | 27270910 |
| ECLASS 8.0            | 27270910 |
| ECLASS 9.0            | 27270910 |
| ECLASS 10.0           | 27270910 |
| ECLASS 11.0           | 27270910 |
| ECLASS 12.0           | 27270910 |
| ECLASS 13.0           | 27270910 |
| ECLASS 14.0           | 27270910 |
| ECLASS 15.0           | 27270910 |
| ETIM 5.0              | EC002549 |
| ETIM 6.0              | EC002549 |
| ETIM 7.0              | EC002549 |
| ETIM 8.0              | EC002549 |
| ETIM 9.0              | EC002549 |
| ETIM 10.0             | EC002549 |

All dimensions in millimeters

- |   |                                     |   |                           |
|---|-------------------------------------|---|---------------------------|
| A | Beam spacing 5 mm                   | L |                           |
| B |                                     |   | Profile length 1 = 488 mm |
|   | Measurement field length 1 = 480 mm |   | Profile length 2 = 968 mm |
|   | Measurement field length 2 = 960 mm | T | Transmitter               |
| F | M6 thread                           | R | Receiver                  |
| G | Fastening groove                    | Y | 2.5 mm                    |

## Dimensioned drawings

### Switch cabinet



## Dimensioned drawings

### Rotary encoders



Dimensioned drawings

Mounting bracket



Electrical connection

Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Earthing       |
| Type of connection | Earthing strap |
| Material           | Metal          |

Connection 2

XS1000

|                    |                   |
|--------------------|-------------------|
| Function           | Voltage supply    |
| Type of connection | Harting connector |
| Material           | Metal             |

Connection 3

XS1301

|                    |                                          |
|--------------------|------------------------------------------|
| Function           | Width measuring light curtain connection |
| Type of connection | Connector                                |
| Thread size        | M12                                      |
| Type               | Male                                     |
| Material           | Metal                                    |
| No. of pins        | 8 -pin                                   |
| Encoding           | A-coded                                  |

Electrical connection

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | IO1            |
| 3   | GND            |
| 4   | IO-Link        |
| 5   | IO2            |
| 6   | IO3            |
| 7   | IO4            |
| 8   | GND            |



| Connection 4       | XS1302                                    |
|--------------------|-------------------------------------------|
| Function           | Height measuring light curtain connection |
| Type of connection | Connector                                 |
| Thread size        | M12                                       |
| Type               | Male                                      |
| Material           | Metal                                     |
| No. of pins        | 8 -pin                                    |
| Encoding           | A-coded                                   |

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | IO1            |
| 3   | GND            |
| 4   | IO-Link        |
| 5   | IO2            |
| 6   | IO3            |
| 7   | IO4            |
| 8   | GND            |



| Connection 5       | XS1400                                                                             |
|--------------------|------------------------------------------------------------------------------------|
| Function           | Rotary encoder connection (not in combination with length measuring light curtain) |
| Type of connection | Connector                                                                          |
| Thread size        | M12                                                                                |
| Type               | Male                                                                               |
| Material           | Metal                                                                              |
| No. of pins        | 8 -pin                                                                             |
| Encoding           | A-coded                                                                            |

| Pin | Pin assignment |
|-----|----------------|
| 1   | U-             |
| 2   | U+             |
| 3   | A              |
| 4   | B              |
| 5   | N              |
| 6   | A inv.         |
| 7   | B inv.         |
| 8   | N inv.         |
| 9   | Shield         |



## Electrical connection

### Connection 6

### XETH1

|                    |                                     |
|--------------------|-------------------------------------|
| Function           | External Ethernet TCP/IP connection |
| Type of connection | Connector                           |
| Thread size        | M12                                 |
| Type               | Male                                |
| Material           | Metal                               |
| No. of pins        | 4 -pin                              |
| Encoding           | A-coded                             |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |



### Connection 7

### XS1100

|                    |                                   |
|--------------------|-----------------------------------|
| Function           | PROFINET IN connection (optional) |
| Type of connection | Connector                         |
| Thread size        | M12                               |
| Type               | Male                              |
| Material           | Metal                             |
| No. of pins        | 4 -pin                            |
| Encoding           | A-coded                           |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |



### Connection 8

### XS1101

|                    |                                    |
|--------------------|------------------------------------|
| Function           | PROFINET OUT connection (optional) |
| Type of connection | Connector                          |
| Thread size        | M12                                |
| Type               | Male                               |
| Material           | Metal                              |
| No. of pins        | 4 -pin                             |
| Encoding           | A-coded                            |

#### Pin Pin assignment

|   |     |
|---|-----|
| 1 | TD+ |
| 2 | RD+ |
| 3 | TD- |
| 4 | RD- |



Diagrams



x Total measuring length from width and height measuring light curtain [mm]  
y Max. conveyor speed [m/s]

Notes

**Observe intended use!**

- This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.

Accessories

Connection technology - Interconnection cables

|  | Part no. | Designation                 | Article               | Description                                                                                                                                                                                                                             |
|--|----------|-----------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50135082 | KSS ET-M12-4A-RJ45-A-P7-100 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 10,000 mm<br>Sheathing material: PUR |

## Accessories

|                                                                                                                                                                                                                                                                                                                                       | Part no. | Designation                 | Article               | Description                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|-----------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|     | 50135083 | KSS ET-M12-4A-RJ45-A-P7-150 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 15,000 mm<br>Sheathing material: PUR |
|                                                                                                                                                                                                                                                                                                                                       | 50135084 | KSS ET-M12-4A-RJ45-A-P7-300 | Interconnection cable | Application: Oil and lubricant resistant<br>Suitable for interface: Ethernet<br>Connection 1: Connector, M12, Axial, Male, D-coded, 4 -pin<br>Connection 2: RJ45<br>Shielded: Yes<br>Cable length: 30,000 mm<br>Sheathing material: PUR |

## Mounting technology - Other

|                                                                                                                                                                                                                                                                                                                                               | Part no. | Designation   | Article             | Description                                                                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|---------------|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|     | 50143670 | BT 708M-MRSET | Mounting device set | Contains: Mounting material, Mounting profiles<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|                                                                                                                                                                                                                                                                                                                                               | 50143671 | BT 70EM-MRSET | Mounting device set | Contains: Mounting material, Mounting profiles<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|                                                                                                                                                                                                                                                                                                                                               | 50143669 | BT 710M-MRSET | Mounting device set | Contains: Mounting profiles, Mounting material<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |
|                                                                                                                                                                                                                                                                                                                                               | 50142039 | BT 712M-MRSET | Mounting device set | Contains: Mounting profiles, Mounting material<br>Design of mounting device: Profile kit<br>Fastening, at system: Screw type / vertical<br>Mounting bracket, at device: Groove mounting<br>Type of mounting device: Rigid<br>Material: Aluminum<br>Shock absorber: No |

### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.