

## Technical data sheet

### Light curtain transmitter

Part no.: 50131409  
CSL505-T50-1550-M8

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Operation and display
- Suitable receivers
- Part number code
- Accessories



For illustration purposes only



## Technical data

### Basic data

|                     |                          |
|---------------------|--------------------------|
| Series              | 505                      |
| Operating principle | Throughbeam principle    |
| Device type         | Transmitter              |
| Application         | Precise object detection |

### Special version

|                 |                        |
|-----------------|------------------------|
| Special version | Crossed-beam scanning  |
|                 | Diagonal-beam scanning |
|                 | Parallel-beam scanning |

### Optical data

|                          |               |
|--------------------------|---------------|
| Operating range          | 0.3 ... 5 m   |
| Measurement field length | 1,550 mm      |
| Number of beams          | 32 Piece(s)   |
| Beam spacing             | 50 mm         |
| Light source             | LED, Infrared |
| Wavelength               | 860 nm        |
| Transmitted-signal shape | Pulsed        |

### Measurement data

|                         |         |
|-------------------------|---------|
| Minimum object diameter | 52.5 mm |
|-------------------------|---------|

### Electrical data

|                    |                              |
|--------------------|------------------------------|
| Protective circuit | Inductive protection         |
|                    | Polarity reversal protection |
|                    | Short circuit protected      |

### Performance data

|                               |                 |
|-------------------------------|-----------------|
| Supply voltage U <sub>B</sub> | 18 ... 30 V, DC |
|-------------------------------|-----------------|

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

### Connection 1

|                    |                    |
|--------------------|--------------------|
| Function           | Deactivation input |
|                    | Voltage supply     |
| Type of connection | Connector          |
| Thread size        | M8                 |
| Type               | Male               |
| Material           | Metal              |
| No. of pins        | 4 -pin             |
| Encoding           | A-coded            |

### Mechanical data

|                       |                          |
|-----------------------|--------------------------|
| Design                | Cubic                    |
| Dimension (W x H x L) | 10 mm x 27 mm x 1,630 mm |
| Housing material      | Metal                    |
| Metal housing         | Aluminum                 |
| Lens cover material   | Plastic                  |
| Net weight            | 383 g                    |
| Housing color         | Silver                   |
| Type of fastening     | Through-hole mounting    |

### Operation and display

|                       |                    |
|-----------------------|--------------------|
| Type of display       | LED                |
| Number of LEDs        | 1 Piece(s)         |
| Type of configuration | Software           |
|                       | Via pin assignment |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -30 ... 50 °C |
| Ambient temperature, storage   | -40 ... 65 °C |

### Certifications

|                      |       |
|----------------------|-------|
| Degree of protection | IP 65 |
| Protection class     | III   |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 90314990 |
| ECLASS 5.1.4          | 27270910 |
| ECLASS 8.0            | 27270910 |
| ECLASS 9.0            | 27270910 |
| ECLASS 10.0           | 27270910 |
| ECLASS 11.0           | 27270910 |
| ECLASS 12.0           | 27270910 |
| ECLASS 13.0           | 27270910 |
| ECLASS 14.0           | 27270910 |
| ECLASS 15.0           | 27270910 |
| ECLASS 16.0           | 27270910 |
| ETIM 5.0              | EC002549 |
| ETIM 6.0              | EC002549 |
| ETIM 7.0              | EC002549 |
| ETIM 8.0              | EC002549 |
| ETIM 9.0              | EC002549 |
| ETIM 10.0             | EC002549 |

Dimensioned drawings

All dimensions in millimeters



"Observe the exact dimensions in the chapter "Technical data, dimensioned drawings" in the operating instructions.

Electrical connection

Connection 1

|                    |                    |
|--------------------|--------------------|
| Function           | Deactivation input |
|                    | Voltage supply     |
| Type of connection | Connector          |
| Thread size        | M8                 |
| Type               | Male               |
| Material           | Metal              |
| No. of pins        | 4 -pin             |
| Encoding           | A-coded            |

| Pin | Pin assignment |
|-----|----------------|
| 1   | V+             |
| 2   | n.c.           |
| 3   | GND            |
| 4   | IN 1           |



Operation and display

| LED | Display | Meaning |
|-----|---------|---------|
| 1   | Off     | Off     |

## Operation and display

| LED | Display                                | Meaning                        |
|-----|----------------------------------------|--------------------------------|
| 1   | Red, continuous light<br>Red, flashing | Operational readiness<br>Error |

## Suitable receivers

| Part no. | Designation        | Operating range<br>Operating range<br>limit | Description                                                                                                                                                                                                                                                                                                  |
|----------|--------------------|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 50131353 | CSL505-R50-1550-M8 | 0.3 ... 5 m                                 | Application: Precise object detection<br>Special version: Parallel-beam scanning, Crossed-beam scanning, Diagonal-beam scanning, Teach input, Warning output<br>Digital switching outputs: 2 Piece(s)<br>Switching output: Transistor, Push-pull, Light/dark switchable<br>Connection: Connector, M8, 4 -pin |

## Part number code

Part designation: **CSL505-XXXX-ZZZZ-AA-BBB**

|             |                                                                                             |
|-------------|---------------------------------------------------------------------------------------------|
| <b>X</b>    | <b>Operating principle</b><br>T: transmitter<br>R: receiver                                 |
| <b>YYY</b>  | <b>Beam spacing</b><br>05: 5 mm<br>12.5: 12.5 mm<br>25: 25 mm<br>50: 50 mm<br>100: 100 mm   |
| <b>ZZZZ</b> | <b>Measurement field length</b><br>Measurement field length [mm], dependent on beam spacing |
| <b>AA</b>   | <b>Electrical connection</b><br>M8: M8 connector, 4-pin (plug)                              |

### Note



A list with all available device types can be found on the Leuze website at [www.leuze.com](http://www.leuze.com).

## Accessories

### Connection technology - Connection cables

| Part no. | Designation       | Article          | Description                                                                                                                                                                                                |
|----------|-------------------|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 50130850 | KD U-M8-4A-V1-050 | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M8, Axial, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC |



Accessories

|                                                                                  | Part no. | Designation       | Article          | Description                                                                                                                                                                                                 |
|----------------------------------------------------------------------------------|----------|-------------------|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | 50130871 | KD U-M8-4W-V1-050 | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M8, Angled, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC |

Configuration devices

|                                                                                  | Part no. | Designation      | Article | Description                                                   |
|----------------------------------------------------------------------------------|----------|------------------|---------|---------------------------------------------------------------|
|  | 50132069 | CSL505-Interface | Module  | Functions: Configuration and test device<br>Connection: Sub-D |

Note

|                                                                                  |                                                                                                                                  |
|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
|  | <p>A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.</p> |
|----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|