

Technical data sheet Throughbeam photoelectric sensor transmitter Part no.: 50116853 LS318B/9D-M12



 Leuze electronic GmbH + Co. KG
 info@leuze.com • www.leuze.com
 changes

 The Sensor People
 In der Braike 1, D-73277 Owen/Germany
 Phone: +49 7021 573-0 • Fax: +49 7021 573-199
 eng • 2025-07-23

We reserve the right to make technical changes

318B

Transmitter

Throughbeam principle

Deactivation input

Technical data

Leuze

Basic data

Series Operating principle Device type

Special version

Special version

Optical data

Operating range	0 10 m (guaranteed operating range)
Operating range limit	0 15 m (typical operating range)
Light source	LED, Red
Wavelength	620 nm
Transmitted-signal shape	Pulsed
LED group	Exempt group (in acc. with EN 62471)

Electrical data

Туре

Material

No. of pins

Encoding

Protective circuit	Polarity reversal protection
	Short circuit protected
Performance data	
Supply voltage U _B	10 30 V, DC, Incl. residual ripple
Residual ripple	0 15 %, From U _B
Open-circuit current	0 15 mA
Inputs	
Number of deactivation inputs	2 Piece(s)
Deactivation inputs	
Туре	Deactivation input
Deactivation input 1	
Active switching state	Low
Deactivation input 2	1.0.1
Active switching state	High
Time behavior	
Readiness delay	300 ms
Connection	
Number of connections	1 Piece(s)
Connection 1	
Function	Signal IN
	Voltage supply
Type of connection	Connector
Thread size	M12

Male

Plastic

4 -pin

A-coded


Mechanical data

Dimension (Ø x L)	18 mm x 46 mm
Thread size	M18 x 1 mm
Housing material	Plastic
Plastic housing	ABS
Lens cover material	Plastic
Net weight	20 g
Housing color	Black
	Red
Operation and display	
Type of display	LED
Number of LEDs	1 Piece(s)
Environmental data	
Ambient temperature, operation	-40 60 °C
Ambient temperature, storage	-40 70 °C
Certifications	
Degree of protection	IP 67
Protection class	III
Approvals	c UL US
Standards applied	IEC 60947-5-2
Classification	
Customs tariff number	85365019
ECLASS 5.1.4	27270901
ECLASS 8.0	27270901
ECLASS 9.0	27270901
ECLASS 10.0	27270901
ECLASS 11.0	27270901
ECLASS 12.0	27270901
ECLASS 13.0	27270901
ECLASS 14.0	27270901
ECLASS 15.0	27270901
ETIM 5.0	EC002716
ETIM 6.0	EC002716
ETIM 7.0	EC002716
ETIM 8.0	EC002716
ETIM 9.0	EC002716
ETIM 10.0	EC002716

Dimensioned drawings



All dimensions in millimeters



Electrical connection

Connection 1

Function	Signal IN
	Voltage supply
Type of connection	Connector
Thread size	M12
Туре	Male
Material	Plastic
No. of pins	4 -pin
Encoding	A-coded

Optical axis Indicator diode

Pin Pin assignment


1	V+
2	IN2
3	GND
4	IN1



Diagrams

Leuze

Typ. response behavior



Operation and display

LED	Display	Meaning
1	Green, continuous light	Operational readiness
	Yellow, continuous light	Transmitted beam active

Suitable receivers

	Part no.	Designation	Operating range Operating range limit	Description
\$	50116845	LE318B/2N-M12	0 10 m 0 15 m	Supply voltage: DC Digital switching outputs: 2 Piece(s) Switching output 1: Transistor, NPN, Light switching Switching output 2: Transistor, NPN, Dark switching Switching frequency: 500 Hz Connection: Connector, M12, Plastic, 4 -pin
\$\$\$	50116847	LE318B/4P-M12	0 10 m 0 15 m	Supply voltage: DC Digital switching outputs: 2 Piece(s) Switching output 1: Transistor, PNP, Light switching Switching output 2: Transistor, PNP, Dark switching Switching frequency: 500 Hz Connection: Connector, M12, Plastic, 4 -pin
\$	50122549	LE318B/PX-M12	0 10 m 0 15 m	Operating range limit: 0 15 m Supply voltage: DC Digital switching outputs: 1 Piece(s) Switching output 1: Transistor, PNP, Dark switching Switching frequency: 500 Hz Connection: Connector, M12, Plastic, 4 -pin

Part number code



Part designation: XXX318BY-AAAF.BB/CC-DDD

XXX318B	Operating principle PRK: Retro-reflective photoelectric sensor with polarization filter ET: energetic diffuse reflection sensor FT: diffuse reflection sensor with fading LE: Throughbeam photoelectric sensor receiver LS: throughbeam photoelectric sensor transmitter
Y	Light type n/a: red light I: infrared light
AAAF	Preset range (optional) n/a: operating range acc. to data sheet xxxF: Preset range [mm]
BB	Equipment n/a: axial optics W: 90° angular optics 3: teach-in via button X: reinforced fading
cc	Switching output / function (OUT1 = pin 4, OUT2 = pin 2): 4: PNP transistor output, light switching P: PNP transistor output, dark switching 2: NPN transistor output, light switching N: NPN transistor output, dark switching 9: input for transmitter deactivation (deactivation with HIGH signal) D: Input for transmitter deactivation (deactivation with LOW signal) X: pin not used
DDD	Electrical connection n/a: cable, standard length 2000mm, 4-wire M12: M12 connector, 4-pin (plug) 5000: cable, standard length 5000mm, 4-wire 200-M12: cable, length 200mm with M12 connector, 4-pin, axial (plug)
No	te
R	A list with all available device types can be found on the Leuze website at www.leuze.com.

Notes

 Observe intended use!

 Image: Serve intended use intended as personnel protection.

 Image: Serve intended use into operation by competent persons.

 Image: Serve intended use into operation by competent persons.

 Image: Serve intended use into operation by competent persons.

 Image: Serve intended use into operation by competent persons.

 Image: Serve intended use into operation by competent persons.

 Image: Serve intended use into operation in accordance with its intended use.



For UL applications:

b For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).

These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)

Further information

- Sum of the output currents for both outputs, 50 mA for ambient temperatures > 40 $^\circ\text{C}$

Accessories

Connection technology - Connection cables

	Part no.	Designation	Article	Description
W	50130652	KD U-M12-4A-V1- 050	Connection cable	Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC
Ŵ	50130690	KD U-M12-4W-V1- 050	Connection cable	Connection 1: Connector, M12, Angled, Female, A-coded, 4 -pin Connector, LED: No Connection 2: Open end Shielded: No Cable length: 5.000 mm Sheathing material: PVC

Mounting technology - Mounting brackets

	Part no.	Designation	Article	Description
C	50113548	BT D18M.5	Mounting bracket	Diameter, inner: 18 mm Design of mounting device: Angle, L-shape Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Rigid Material: Stainless steel

Mounting technology - Rod mounts

 Part no.	Designation	Article	Description
50117490	BTU D18M-D12	Mounting system	Design of mounting device: Mounting system Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Clampable, Adjustable, Turning, 360° Material: Metal

Mounting technology - Other

	Part no.	Designation	Article	Description
Ţ	50117258	BT 318P-LS	Fastening	Design of mounting device: Mounting clamp Fastening, at system: Through-hole mounting Mounting bracket, at device: Clampable Type of mounting device: Rigid Material: Plastic Shock absorber: No
80	50121904 **	BT318B-OM	Fastening	Design of mounting device: Mounting clamp Fastening, at system: Through-hole mounting Mounting bracket, at device: Screw type Type of mounting device: Swiveling, Adjustable, Turning Material: Plastic Shock absorber: No

** Included in delivery contents

Leuze

Accessories





♦ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.