

Karta danych technicznych Element mocujący

Nr art.: 50121433

BT 300 W

Treść

- Dane techniczne
- Rysunki wymiarowe



Ilustracja może się różnić od stanu rzeczywistego

Dane techniczne

Dane podstawowe

zawarty	2 szt. śruby M6 x 10
	4 szt. śruby M3 x 8
	4 szt. śruby M4 x 10
Odpowiednie dla grupy produktów	Stacjonarne czytniki kodów kreskowych
Przeznaczony dla	Czytniki kodów kreskowych serii BCL 2xxi Lustra odbijające
	Czytniki kodów kreskowych serii BCL 3xxi
	Czytniki kodów kreskowych serii BCL 3xxi Lustra odbijające
	IVS 1000i & DCR 1000i
	LCAM 308

Dane mechaniczne

Oznaczenie standardowe elementu mocującego z metalu	Stal, ocynkowana
Masa netto	213 g
Wersja elementu mocującego	Kątowniki kształt L
Rodzaj mocowania, po stronie instalacji	Mocowanie przelotowe
Rodzaj mocowania, po stronie urządzenia	przykręcany
Rodzaj elementu mocującego	regulowany
Materiał elementu mocującego	Metal

Klasyfikacja

Numer taryfy celnej	73182900
ECLASS 5.1.4	27279202
ECLASS 8.0	27279202
ECLASS 9.0	27273701
ECLASS 10.0	27273701
ECLASS 11.0	27273701
ECLASS 12.0	27273701
ECLASS 13.0	27273701
ECLASS 14.0	27273701
ECLASS 15.0	27273701
ECLASS 16.0	27273701
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015
ETIM 10.0	EC003015
UNSPSC 26.08	31242100

Technical drawing of a rectangular plate, showing two views: a front view (top) and a top view (bottom).

Front View (Top):

- Overall dimensions: 58 (width) x 100 (height).
- Internal dimensions: 42 (width of central area), 42 (height of central area), 38 (width of bottom flange), 4 (height of bottom flange), 4.4 (height of top flange), 16 (height of top flange).
- Corner radius: R42.
- Angles: 25° (indicated for the top and bottom corners of the central area).
- Holes:
 - Four small holes (Ø 4.2) arranged in a square pattern.
 - Four medium holes (Ø 6.2) arranged in a square pattern.
 - Four small holes (Ø 3.2) arranged in a square pattern.
- Slots: Two elongated slots, each with a width of 4.2 and a height of 6.2.

Top View (Bottom):

- Overall dimensions: 48 (width) x 27.5 (height).
- Angles: 30° (indicated for the slots).
- Holes:
 - Four small holes (Ø 6.2) arranged in a square pattern.
 - Four medium holes (Ø 2.9) arranged in a square pattern.
- Slots: Four elongated slots, each with a width of 4.2 and a height of 6.2.