

## Technical data sheet

### Alignment aid

Part no.: 50139665

PRK25CL1/XX-M12

#### Contents

- Technical data
- Electrical connection
- Notes
- Further information
- Accessories



CDRH

UK  
CA

For illustration purposes only

## Technical data

### Basic data

|              |                    |
|--------------|--------------------|
| Series       | 25C                |
| Suitable for | 25C series sensors |

### Optical data

|                                      |                        |
|--------------------------------------|------------------------|
| Light source                         | Laser, Red             |
| Laser class                          | 1                      |
| Light spot size [at sensor distance] | 3 mm x 5 mm [1,000 mm] |
| Type of light spot geometry          | elliptic               |

### Electrical data

#### Performance data

|                      |                           |
|----------------------|---------------------------|
| Supply voltage $U_B$ | DC, Incl. residual ripple |
| Residual ripple      | 0 ... 15 %, From $U_B$    |

### Connection

#### Connection 1

|                    |           |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size        | M12       |
| Type               | Male      |
| No. of pins        | 4 -pin    |
| Encoding           | A-coded   |

### Mechanical data

|                            |                                      |
|----------------------------|--------------------------------------|
| Dimension (W x H x L)      | 15 mm x 42.7 mm x 30 mm              |
| Housing material           | Metal                                |
|                            | Plastic                              |
| Plastic housing            | ABS                                  |
| Lens cover material        | Plastic                              |
| Net weight                 | 22 g                                 |
| Housing color              | Red                                  |
| Type of fastening          | Through-hole mounting with M4 thread |
|                            | Via optional mounting device         |
| Compatibility of materials | ECOLAB                               |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 60 °C |
| Ambient temperature, storage   | -40 ... 70 °C |

### Certifications

|                      |        |
|----------------------|--------|
| Degree of protection | IP 67  |
|                      | IP 69K |
| Protection class     | III    |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27279210 |
| ECLASS 8.0            | 27279210 |
| ECLASS 9.0            | 27273607 |
| ECLASS 10.0           | 27273607 |
| ECLASS 11.0           | 27273607 |
| ECLASS 12.0           | 27273607 |
| ECLASS 13.0           | 27273607 |
| ECLASS 14.0           | 27273607 |
| ECLASS 15.0           | 27273607 |
| ECLASS 16.0           | 27273607 |
| ETIM 5.0              | EC002498 |
| ETIM 6.0              | EC003015 |
| ETIM 7.0              | EC003015 |
| ETIM 8.0              | EC003015 |
| ETIM 9.0              | EC003015 |
| ETIM 10.0             | EC003015 |

## Electrical connection


### Connection 1

|                    |                |
|--------------------|----------------|
| Function           | Signal OUT     |
|                    | Voltage supply |
| Type of connection | Connector      |
| Thread size        | M12            |
| Type               | Male           |
| Material           | PUR            |
| No. of pins        | 4 -pin         |
| Encoding           | A-coded        |

### Pin

### Pin assignment

|   |      |
|---|------|
| 1 | V+   |
| 2 | n.c. |
| 3 | GND  |
| 4 | n.c. |



## Notes

|   |   |
|---|---|
|  | <b>Observe intended use!</b>  |
|   | <ul style="list-style-type: none"> <li>↳ This product is not a safety sensor and is not intended as personnel protection.</li> <li>↳ The product may only be put into operation by competent persons.</li> <li>↳ Only use the product in accordance with its intended use.</li> </ul> |

|  |  |
|--|--|
|  | <b>For UL applications:</b>  |
|  | <ul style="list-style-type: none"> <li>↳ Only for use in "class 2" circuits</li> <li>↳ These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV7 or PVVA/PVVA7)</li> </ul> |

|   |   |
|---|---|
|  | <b>WARNING! LASER RADIATION – CLASS 1 LASER PRODUCT</b>   |
|   | <p>The device satisfies the requirements of IEC 60825-1:2007 (EN 60825-1:2007) safety regulations for a product of <b>laser class 1</b> as well as the U.S. 21 CFR 1040.10 regulations with deviations corresponding to Laser Notice No. 50 from June 24, 2007.</p> <ul style="list-style-type: none"> <li>↳ Observe the applicable statutory and local laser protection regulations.</li> <li>↳ The device must not be tampered with and must not be changed in any way.<br/>There are no user-serviceable parts inside the device.<br/>Repairs must only be performed by Leuze electronic GmbH + Co. KG.</li> </ul> |

## Further information

### Accessories

#### Connection technology - Connection cables

| Part no.  | Designation | Article            | Description   |
|---|-------------|--------------------|---|
|  | 50130652    | KD U-M12-4A-V1-050 | Connection cable<br>Application: Chemical resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC  |
|  | 50130690    | KD U-M12-4W-V1-050 | Connection cable<br>Application: Chemical resistant<br>Connection 1: Connector, M12, Angled, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC |

## Accessories

### Mounting technology - Mounting brackets

| Part no.  | Designation | Article   | Description   |
|---|-------------|-----------|---|
|  | 50118543    | BT 300M.5 | Mounting bracket<br>Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type, Suited for M4 screws<br>Type of mounting device: Adjustable<br>Material: Stainless steel |

### Mounting technology - Rod mounts

| Part no.  | Designation | Article      | Description  |
|---|-------------|--------------|--|
|  | 50117252    | BTU 300M-D12 | Mounting system<br>Contains: 2x M4 x 25 screw, 2x M4 x 20 screw, 4x position washers<br>Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod, Sheet-metal mounting<br>Mounting bracket, at device: Screw type, Suited for M4 screws<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal |

**Note**

↳ A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.