



### Technical data

#### Optical data

Typ. maximum range (white 90%) <sup>1)</sup> Infrared light  
 0 ... 2,500 mm  
 Operating range <sup>2)</sup> See tables  
 Adjustment range 120 ... 2500 mm  
 Light source <sup>3)</sup> LED (modulated light)  
 Wavelength 850 nm

#### Time behavior

Switching frequency 200 Hz  
 Response time 2.5 ms  
 Readiness delay ≤ 100 ms

#### Electrical data

##### With transistor switching outputs

Operating voltage  $U_B$  10 ... 30 VDC (incl. residual ripple)  
 Residual ripple ≤ 15% of  $U_B$   
 Open-circuit current ≤ 30 mA  
 Switching output .../66. ... 2 push-pull switching outputs <sup>4)</sup>  
 Pin 2: PNP dark switching, NPN light switching  
 Pin 4: PNP light switching, NPN dark switching  
 PNP switching output, pin 4: PNP light switching  
 .../4. ... ≥ ( $U_B - 2V$ ) / ≤ 2V  
 Max. 50 mA

Signal voltage high/low  
 Output current

#### Indicators

Green LED Ready  
 Yellow LED Reflection  
 Yellow LED, flashing Reflection, no function reserve

#### Mechanical data

Housing / lens cover Plastic / plastic  
 Weight 50 g (with connector) / 65 g (with cable and conn.)  
 Connection type Cable with M12 connector, cable length: 200 mm

#### Environmental data

Ambient temp. (operation/storage) -20°C ... +50°C / -30°C ... +70°C  
 Protective circuit <sup>5)</sup> 2, 3  
 VDE protection class <sup>6)</sup> II, all-insulated  
 Degree of protection IP 67, IP 69K  
 Light source Exempt group (in acc. with EN 62471)  
 Standards applied IEC 60947-5-2

#### Explosion protection

Certification ATEX:  $\text{Ex}$  II 3G Ex ec IIB T4 Gc X  
 Certification IECEx:  $\text{Ex}$  II 3D Ex tc IIIC T70°C Dc X  
 Ex ec IIB T4 Gc  
 Ex tc IIIC T70°C Dc

#### Additional functions

Warning output autoControl warn PNP transistor, counting principle  
 Signal voltage high/low ≥ ( $U_B - 2V$ ) / ≤ 2V  
 Output current Max. 50 mA

- 1) Typ. max. range: max. achievable range for light objects (white 90%)
- 2) Operating range: recommended range for objects with different diffuse reflection
- 3) Average life expectancy 100,000 h at an ambient temperature of 25°C
- 4) The push-pull switching outputs must not be connected in parallel
- 5) 2=polarity reversal protection, 3=short circuit protection for all outputs
- 6) Rating voltage 50 VAC

### Order guide

Connection diagram no.

Designation

Part no.



**Cable with M12 connector, length: 200 mm**

#### Antivalent push-pull switching output

Housing model S (standard) 1 HRT 46B/66, 200-S12 S-Ex n 50108587

#### PNP switching output light switching, warning output

Housing model S (standard) 3 IHRT 46B/4, 200-S12 S-Ex n 50108943

#### PNP switching output light switching, warning output + operating range adjustment

Housing model S (standard) 3 IHRT 46B/4.01, 200-S12 S-Ex n 50112802




### Tables

1	0	2,500
2	5	1,800
3	10	1,200


1	White 90%
2	Gray 18%
3	Black 6%

Operating range [mm]

### Diagrams



- A White 90%
- B Gray 18%
- C Black 6%



### Notes

#### Observe intended use!

- ⚠ This product is not a safety sensor and is not intended as personnel protection.
- ⚠ The product may only be put into operation by competent persons.
- ⚠ Only use the product in accordance with its intended use.


- With the set detection range, a tolerance of the upper scanning range limit is possible depending on the reflection properties of the material surface.

## Ex devices

### Notices for the safe use of sensors in potentially explosive areas

This document is valid for devices with the following classifications:

Device group	Device category	Equipment protection level	Zone
II	3G	Gc	Zone 2
II	3D	Dc	Zone 22

⚠ ATTENTION!	
	<ul style="list-style-type: none"> <li>● Check whether the equipment classification corresponds to the requirements of the application.</li> <li>● The devices are not suited for the protection of persons and may not be used for emergency shutdown purposes.</li> <li>● A safe operation is only possible if the equipment is used properly and for its intended purpose.</li> <li>● Electrical equipment may endanger humans and (where applicable) animal health, and may threaten the safety of goods if used incorrectly or under unfavorable conditions in potentially explosive areas.</li> <li>● The applicable national regulations (e.g. EN 60079-14) for the configuration and installation of explosion-proof systems must be observed without fail.</li> </ul>

#### Installation and Commissioning (see also Special conditions)

- The devices must only be installed and commissioned by trained electricians. They must be aware of the regulations and operation of explosion-proof equipment.
- The connector of series 46B sensors must be equipped with a safeguard or a mechanical interlocking guard (e.g. K-VM 12-Ex, part no. 50109217) to prevent unintentional separation under voltage. An additional warning sign "WARNING – DO NOT SEPARATE WHEN ENERGIZED" that is supplied with the device must be attached to the sensor or its mounting bracket so that it is clearly visible. This notice must be attached to the device before it is taken into operation.
- Connection cables and connectors must be protected from excessive or unintended pulling or pushing strain.
- Prevent dust deposits from forming on the devices.

#### Maintenance

- No changes may be made to explosion-proof devices.
- Repairs may only be performed by a person trained for such work or by the manufacturer.
- Defective devices must be replaced immediately.
- Cyclical maintenance is generally not necessary.
- Depending on the environmental conditions, it may occasionally be necessary to clean the optical surfaces of the sensors. This cleaning must only be performed by persons trained for performing this task. We recommend the use of a soft and damp cloth. Cleaning agents containing solvents must not be used.

#### Chemical resistance

- The sensors demonstrate good resistance against diluted (weak) acids and bases.
- Exposure to organic solvents is possible only under certain circumstances and only for short periods of time.
- Resistance to chemicals must be examined on a case by case basis.

#### Special conditions

- The devices must be installed in such a way that they are protected from direct exposure to UV rays (sunlight).
- The metallic cage has to be integrated into the potential equalization before usage to prevent electrostatic charge.
- The light barriers must not be installed in areas where processes with high static charges occur.
- The light barriers may only be used if high or repeated electrostatic processes are surely excluded by installation.
- The metallic cage is screwed together with two torx-screws.
- The connector of series 46B sensors must be equipped with a safeguard or a mechanical interlocking guard to prevent unintentional separation under voltage.
- The connector provided by the user in the final application shall be in accordance with all applicable clauses of IEC 60079-0, IEC 60079-7 and IEC 60079-31. A minimum of IP54 according to IEC 60529 shall be ensured.