

Technical data sheet Signaling column element

Part no.: 50130444

E4-V1-DS-C

Contents

- Technical data
- Notes
- Accessories



Figure can vary



Technical data

Basic data

Series	E4
Suitable for	Signaling column elements of the E4 series
Type of signaling	Optical

Electrical data

Life expectancy	> 100,000 h
Performance data	
Supply voltage U _B	24 V, AC/DC, 10 %
Current consumption, max.	27 mA

Mechanical data

Design	Cylindrical
Dimension (Ø x L)	40 mm x 62 mm
Housing material	Plastic
Net weight	45 g
Type of fastening	Bayonet system
Type of illuminant	LED/24V
Signal image	Continuous light
Lens color	Clear
Angle of radiation	360°

Environmental data

Ambient temperature, operation	-30 ... 60 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 66
Certifications	c UL US

Classification

Customs tariff number	85318070
eCl@ss 5.1.4	27371220
eCl@ss 8.0	27371220
eCl@ss 9.0	27371220
eCl@ss 10.0	27371220
eCl@ss 11.0	27371220
ETIM 5.0	EC000232
ETIM 6.0	EC000232
ETIM 7.0	EC000232

Notes

⚠ Observe intended use!

This product is not a safety sensor and is not intended as personnel protection.

The product may only be put into operation by competent persons.

Only use the product in accordance with its intended use.

⚠ For UL applications:

For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).

Accessories

Mounting

	Part no.	Designation	Article	Description
	50130455	E4-MH1	Signaling column element	Connection: Terminal, Push-in technology Design: Cylindrical Diameter: 40 mm Version: Horizontal mounting Fastening, at system: Screw type / horizontal Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66

Accessories

	Part no.	Designation	Article	Description
	50130458	E4-MP1-100	Signaling column element	Connection: Terminal, Push-in technology Design: Cylindrical Diameter: 40 mm Version: Base mounting Fastening, at system: Screw type / horizontal Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130456	E4-MW1	Signaling column element	Connection: Terminal, Push-in technology Design: Cylindrical Diameter: 40 mm Version: Bracket mounting Fastening, at system: Screw type / vertical Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130457	E4-MW2	Signaling column element	Connection: Terminal, Push-in technology Design: Cylindrical Diameter: 40 mm Version: Bracket mounting Fastening, at system: Screw type / vertical Lens modules: Max. 10 pieces Module holder: Two-sided Ambient temperature: -30 ... 60 °C Degree of protection: IP 66

Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.