

## Technical data sheet

### Throughbeam photoelectric sensor receiver

Part no.: 50145233

LE5B/4X-200-M12

#### Contents

- Technical data
- Dimensioned drawings
- Electrical connection
- Diagrams
- Operation and display
- Suitable transmitters
- Part number code
- Notes
- Accessories



For illustration purposes only



## Technical data

### Basic data

|                     |                       |
|---------------------|-----------------------|
| Series              | 5B                    |
| Operating principle | Throughbeam principle |
| Device type         | Receiver              |

### Optical data

|                 |                 |
|-----------------|-----------------|
| Operating range | see transmitter |
|-----------------|-----------------|

### Electrical data

|                    |                              |
|--------------------|------------------------------|
| Protective circuit | Polarity reversal protection |
|                    | Short circuit protected      |

### Performance data

|                      |  |
|----------------------|--|
| Supply voltage $U_B$ | 10 ... 30 V, DC, Incl. residual ripple |
| Residual ripple      | 0 ... 15 %, From $U_B$                 |
| Open-circuit current | 0 ... 20 mA                            |

### Outputs

|                                     |            |
|-------------------------------------|------------|
| Number of digital switching outputs | 1 Piece(s) |
|-------------------------------------|------------|

### Switching outputs

|                         |                          |
|-------------------------|--------------------------|
| Type                    | Digital switching output |
| Voltage type            | DC                       |
| Switching current, max. | 50 mA                    |
| Switching voltage       | high: $\geq(U_B - 2.5V)$ |
|                         | low: $\leq 2.5 V$        |

### Switching output 1

|                     |   |
|---------------------|---|
| Switching element   | Transistor, PNP   |
| Switching principle | Light switching<br>(dark switching by reversing polarity of $U_B$ ) |

### Time behavior

|                     |         |
|---------------------|---------|
| Switching frequency | 900 Hz  |
| Response time       | 0.56 ms |
| Readiness delay     | 300 ms  |

### Connection

|                       |            |
|-----------------------|------------|
| Number of connections | 1 Piece(s) |
|-----------------------|------------|

### Connection 1

|                      |                      |
|----------------------|----------------------|
| Function             | Signal OUT           |
|                      | Voltage supply       |
| Type of connection   | Cable with connector |
| Cable length         | 200 mm               |
| Sheathing material   | PVC                  |
| Cable color          | Black                |
| Number of conductors | 3 -wire              |
| Wire cross section   | 0.14 mm <sup>2</sup> |
| Thread size          | M12                  |
| Type                 | Male                 |
| Material             | Plastic              |
| No. of pins          | 4 -pin               |
| Encoding             | A-coded              |

### Mechanical data

|  |                              |
|--|------------------------------|
| Dimension (W x H x L)                          | 11 mm x 32.4 mm x 20 mm      |
| Housing material                               | Plastic                      |
| Plastic housing                                | PC-ABS                       |
| Lens cover material                            | Plastic                      |
| Net weight                                     | 40 g                         |
| Housing color                                  | Black                        |
|  | Red                          |
| Type of fastening                              | Two M3 threaded sleeves      |
|  | Via optional mounting device |
| Recommended tightening torque for M3 fastening | 0.9 N·m                      |
| Compatibility of materials                     | ECOLAB                       |

### Operation and display

|                 |            |
|-----------------|------------|
| Type of display | LED        |
| Number of LEDs  | 2 Piece(s) |

### Environmental data

|                                |               |
|--------------------------------|---------------|
| Ambient temperature, operation | -40 ... 60 °C |
| Ambient temperature, storage   | -40 ... 70 °C |

### Certifications

|                      |               |
|----------------------|---------------|
| Degree of protection | IP 67         |
| Protection class     | III           |
| Approvals            | c UL US       |
| Standards applied    | IEC 60947-5-2 |

### Classification

|                       |          |
|-----------------------|----------|
| Customs tariff number | 85365019 |
| ECLASS 5.1.4          | 27270901 |
| ECLASS 8.0            | 27270901 |
| ECLASS 9.0            | 27270901 |
| ECLASS 10.0           | 27270901 |
| ECLASS 11.0           | 27270901 |
| ECLASS 12.0           | 27270901 |
| ECLASS 13.0           | 27270901 |
| ECLASS 14.0           | 27270901 |
| ECLASS 15.0           | 27270901 |
| ECLASS 16.0           | 27270901 |
| ETIM 5.0              | EC002716 |
| ETIM 6.0              | EC002716 |
| ETIM 7.0              | EC002716 |
| ETIM 8.0              | EC002716 |
| ETIM 9.0              | EC002716 |
| ETIM 10.0             | EC002716 |
| UNSPSC 26.08          | 39121528 |

# Dimensioned drawings

All dimensions in millimeters



- A Green LED
- B Yellow LED
- C1 Receiver
- C2 Transmitter
- E Threaded sleeve


## Electrical connection

### Connection 1

|                      |                      |
|----------------------|----------------------|
| Function             | Signal OUT           |
|                      | Voltage supply       |
| Type of connection   | Cable with connector |
| Cable length         | 200 mm               |
| Sheathing material   | PVC                  |
| Cable color          | Black                |
| Number of conductors | 3 -wire              |
| Wire cross section   | 0.14 mm <sup>2</sup> |
| Thread size          | M12                  |
| Type                 | Male                 |
| Material             | Plastic              |
| No. of pins          | 4 -pin               |
| Encoding             | A-coded              |


### Pin Pin assignment

|   |       |
|---|-------|
| 1 | V+    |
| 2 | n.c.  |
| 3 | GND   |
| 4 | OUT 1 |




# Diagrams

## Typ. response behavior



## Typ. function reserve





## Operation and display

| LED | Display                  | Meaning                              |
|-----|--------------------------|--------------------------------------|
| 1   | Yellow, continuous light | Light path free                      |
|     | Yellow, flashing         | Light path free, no function reserve |
| 2   | Green, continuous light  | Operational readiness                |

## Suitable transmitters

|  | Part no. | Designation     | Operating range<br>Operating range<br>limit | Description  |
|--|----------|-----------------|---|--|
|  | 50145240 | LS5B/9X-200-M12 | 0 ... 10 m<br>0 ... 15 m                    | Special version: Deactivation input<br>Operating range limit: 0 ... 15 m<br>Light source: LED, Red<br>Supply voltage: DC<br>Deactivation inputs: 1 Piece(s)<br>Connection: Cable with connector, 200 mm, M12, Plastic, 3 -wire, 4 -pin |

## Suitable transmitters

|  | Part no. | Designation       | Operating range<br>Operating range<br>limit | Description  |
|--|----------|-------------------|---|--|
|  | 50149741 | LS5B/XX-200-M12   | 0 ... 10 m<br>0 ... 15 m                    | Operating range limit: 0 ... 15 m<br>Light source: LED, Red<br>Supply voltage: DC<br>Connection: Cable with connector, 200 mm, M12, Plastic, 3 -wire, 4 -pin                   |
|  | 50153000 | LS5BPP/XX-200-M12 | 0 ... 12.5 m<br>0 ... 17.5 m                | Operating range limit: 0 ... 17.5 m<br>Light source: Power PinPoint® LED, Red<br>Supply voltage: DC<br>Connection: Cable with connector, 200 mm, M12, Plastic, 3 -wire, 4 -pin |

## Part number code

Part designation: AAA5B D-E.FF/GG.HH-JJ

|              |  |
|--------------|--|
| <b>AAA5B</b> | <b>Operating principle / construction</b><br>LS5B: Throughbeam photoelectric sensor transmitter<br>LE5B: Throughbeam photoelectric sensor receiver<br>PRK5B: Retro-reflective photoelectric sensor with polarization filter<br>HT5B: Diffuse reflection sensor with background suppression<br>ET5B: Energetic diffuse reflection sensor  |
| <b>D</b>     | <b>Light type</b><br>n/a: red light<br>I: infrared light<br>PP: Power PinPoint® LED  |
| <b>E</b>     | <b>Preset range (optional)</b><br>n/a: operating range acc. to data sheet<br>xxxF: Preset range [mm]   |
| <b>FF</b>    | <b>Equipment</b><br>1: 270° potentiometer<br>D: Detection of stretch-wrapped objects<br>M: Detection of semi-transparent media and transparent films<br>XL: Extra long light spot<br>n/a with retro-reflective photoelectric sensors (PRK): operating range not adjustable<br>n/a with ET / HT: range adjustable via 8-turn potentiometer  |
| <b>GG</b>    | <b>Switching output / Function</b><br>2: NPN transistor output, light switching<br>N: NPN transistor output, dark switching<br>4: PNP transistor output, light switching<br>P: PNP transistor output, dark switching<br>9: deactivation input (deactivation with high signal)<br>X: pin not used   |
| <b>HH</b>    | <b>Electrical connection</b><br>n/a: cable, standard length 2000 mm, 3-wire<br>M8: M8 connector, 4-pin (plug)<br>200-M12: cable, length 200 mm with M12 connector, 4-pin, axial (plug)<br>200-M8: cable, length 200 mm with M8 connector, 4-pin, axial (plug)<br>200-M8.3: cable, length 200 mm with M8 connector, 3-pin, axial (plug)<br>200-M8.1: Cable, length 200 mm with snap-in M8 connector, 4-pin (plug)<br>M8.3: M8 connector, 3-pin (plug) |
| <b>JJ</b>    | <b>Version</b><br>Y1: mounting holes without threaded sleeve   |

### Note



A list with all available device types can be found on the Leuze website at [www.leuze.com](http://www.leuze.com).

## Notes



### Observe intended use!



- ⌘ This product is not a safety sensor and is not intended as personnel protection.
- ⌘ The product may only be put into operation by competent persons.
- ⌘ Only use the product in accordance with its intended use.

### For UL applications:



- ⌘ Only for use in "class 2" circuits
- ⌘ These proximity switches shall be used with UL Listed Cable assemblies rated 30V, 0.5A min, in the field installation, or equivalent (categories: CYJV/ CYJV7 or PVVA/PVVA7)



## Accessories

### Connection technology - Connection cables



|  | Part no. | Designation        | Article          | Description   |
|--|----------|--------------------|------------------|---|
|  | 50130652 | KD U-M12-4A-V1-050 | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M12, Axial, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC  |
|  | 50130690 | KD U-M12-4W-V1-050 | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M12, Angled, Female, A-coded, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC |
|  | 50130850 | KD U-M8-4A-V1-050  | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M8, Axial, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC            |
|  | 50130871 | KD U-M8-4W-V1-050  | Connection cable | Application: Chemical resistant<br>Connection 1: Connector, M8, Angled, Female, 4 -pin<br>Connector, LED: No<br>Connection 2: Open end<br>Shielded: No<br>Cable length: 5,000 mm<br>Sheathing material: PVC           |

## Accessories

### Mounting technology - Mounting brackets

|   | Part no. | Designation   | Article             | Description   |
|---|----------|---------------|---------------------|---|
|  | 50118542 | BT 200M.5     | Mounting bracket    | Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type, Suited for M3 screws<br>Type of mounting device: Adjustable<br>Material: Stainless steel |
|   | 50124651 | BT 205M-10SET | Mounting device set | Contains: 10x<br>Design of mounting device: Angle, L-shape<br>Fastening, at system: Through-hole mounting<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Rigid<br>Material: Metal                     |

### Mounting technology - Rod mounts

|   | Part no. | Designation  | Article         | Description   |
|---|----------|--------------|-----------------|---|
|   | 50117829 | BTP 200M-D12 | Mounting system | Design of mounting device: Protection hood<br>Fastening, at system: For 12 mm rod<br>Mounting bracket, at device: Screw type<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal  |
|  | 50117255 | BTU 200M-D12 | Mounting system | Contains: 2x M3 x 16 screw, 2 M3 x 20 screws, 2x position washers<br>Design of mounting device: Mounting system<br>Fastening, at system: For 12 mm rod, Sheet-metal mounting<br>Mounting bracket, at device: Screw type, Suited for M3 screws<br>Type of mounting device: Clampable, Adjustable, Turning, 360°<br>Material: Metal |

#### Note



A list with all available accessories can be found on the Leuze website in the Download tab of the article detailed page.