

기술 데이터 시트

엔코더 시리즈 정보

품목 번호: 90000470

EI30-P 100 HI

내용

- 기술 데이터
- 제품 키워드



그림과 차이가 날 수 있습니다

인코더_시리즈	EI 100 HI
인코더_기본 원리	증분형
인코더_작동 원리	광학 보간
인코더_플랜지 직경	Ø 100mm
인코더_플랜지 유형	절연 중공축
인코더_실축/중공축	중공축
인코더_축 직경	Ø 25mm
	Ø 30mm
	Ø 32mm
	Ø 38mm
	Ø 40mm
	Ø 42mm
인코더_공급전압	10 ~ 30 V DC
	4.75 ... 5.5 V DC
	5 ~ 30V DC
인코더_출력 회로	HTL
	TTL
	TTL, RS422 호환
	반전 1 Vss Sin/Cos
	반전 HTL
인코더_펄스 수	10240I/U
	16384I/U
	20480I/U
	4096I/U
	8192I/U

기술 데이터

Encoder EI30 P 100 HI

Resolution

Pulses per revolution PPR up to 20480 PPR

Mechanical Data

Flange	hollow shaft (through-bored)
Flange material	aluminum
Housing material	aluminum, powder coated
Torque supports	incl. 1 torque support
- 1. Spring plate compensation	axial: ± 0.8 mm [0.0315"], radial: ± 0.2 mm [0.0079"]
Flange diameter	$\varnothing$ 100 mm [$\varnothing$ 3.543"]

Shaft(s)

Shaft material	stainless steel
Starting torque	approx. 1.5 Ncm [2.124 in-ozf] at ambient temperature
Fixing	2 x M4, DIN 913; Starting torque: 2,5 Nm

Shaft	$\varnothing$ 25 mm [$\varnothing$ 0.984"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 28 mm [$\varnothing$ 1.102"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 30 mm [$\varnothing$ 1.181"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 32 mm [$\varnothing$ 1.26"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 38 mm [$\varnothing$ 1.496"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]

Max. Permissible shaft loading axial 100 N [10.197 kp]

Shaft	$\varnothing$ 40 mm [$\varnothing$ 1.575"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 42 mm [$\varnothing$ 1.654"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Shaft	$\varnothing$ 45 mm [$\varnothing$ 1.772"]
Shaft length	L: 42 mm [1.654"]
Insertion depth min.	52 mm [2.047"]
Max. Permissible shaft loading radial	200 N [20.394 kp]
Max. Permissible shaft loading axial	100 N [10.197 kp]

Bearings

Bearings type	2 precision ball bearings
Nominale service life	3 x 10 ¹⁰ revs. at 100 % rated shaft load 1 x 10 ¹¹ revs. at 40 % rated shaft load 1 x 10 ¹² revs. at 20 % rated shaft load
Max. operating speed	3500 rpm

Machinery Directive: basic data safety integrity level

MTTF _d	200 a
Mission time (TM)	25 a
Nominale service life (L10h)	1 x 10 ¹² revs. at 20 % rated shaft load and 3500 rpm
Diagnostic coverage (DC)	0 %

Electrical Data

Power supply/Current consumption	4.75 VDC up to 30 VDC: typ. 70 mA (100 mA only C3, D3)
Power supply/Current consumption	5 VDC up to 30 VDC: typ. 70 mA
Power supply/Current consumption	10 VDC up to 30 VDC: typ. 70 mA (100 mA only C2, C4, D4)
Operating principle	optical
Output circuit	TTL TTL, RS422 compatible, inv. HTL HTL, inv. 1 Vpp sin/cos
Pulse frequency	TTL $\leq$ 5000 ppr: max. 200 kHz HTL $\leq$ 5000 ppr: max. 200 kHz TTL more than 1200 ppr: max. 2 MHz HTL more than 1200 ppr: max. 600 kHz 1 Vpp sin/cos: max. 100 kHz

기술 데이터

Encoder EI30 P 100 HI

Electrical Data

Channels	B N and inverted signals
Load	max. 40 mA / channel @ 1 Vpp sin/cos: min. 120 Ohm
Circuit protection	circuit type C6 and D6 only

Accuracy

Phase offset	90° ± max. 7.5 % of the period duration
pulse-/pause-ratio	≤5000 ppr: 50 % ± max. 7 % Output circuits C2, C3, C4, D3, D4: 50 % ± max. 10 %

Environmental data

ESD (DIN EN 61000-4-2):	8 kV
Burst (DIN EN 61000-4-4):	2 kV
includes EMC:	DIN EN 61000-6-2 DIN EN 61000-6-3
Vibration: (DIN EN 60068-2-6)	50 m/s ² (10 Hz up to 2000 Hz)
Shock: (DIN EN 60068-2-27)	1000 m/s ² (6 ms)
Electrical Safety:	according DIN VDE 0160


Duty information

Customs tariff number:	90318020
Country of origin:	Germany

General Data

Weight	approx. 720 g [25.397 oz]
Connections	cable or connector, radial
Protection rating (EN 60529)	IP54
Operating temperature	-20 °C up to +80 °C [-4 °F up to +176 °F] 1 Vpp: -10 °C up to +70 °C [+14 °F up to +158 °F]
Storage temperature	-30 °C up to +80 °C [-22 °F up to 176 °F]

Cable connection R-N, R-C radial with 2 m cable



All dimensions in mm

- A Plug-in connexctor for functional ground connection
(flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support

Description

N inv. poss.

R-N	radial, shield not connected	•
R-C	radial, shield connected to encoder housing	•

Assignments

	R-N, R-C	R-N, R-C	R-C
Circuit	C3, C4, C5, C6, C7	C1, C2, D3, D4, D5, D6, D7	D8
GND	WH	WH	WH
(+) Vcc	BN	BN	BN
A	GN	GN	GN


기술 데이터

Encoder EI30 P 100 HI

Assignments

B	YE	YE	GY
N	GY	GY	BK
	–	–	–
A inv.	–	RD	YE
B inv.	–	BK, (BU at LT)	PK
N inv.	–	VT	–
Shield	flex	flex	flex

Connector (M16x0.75) R, radial, 5-, 6-, 8-, 12-pin



All dimensions in mm

- A Plug-in connector for functional ground connection
(flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support

Description

N inv. poss.

R5	radial, 5-pin, Connector connected to encoder housing	–
R6	radial, 6-pin, Connector connected to encoder housing	–
R8	radial, 8-pin, Connector connected to encoder housing	•
R12	radial, 12-pin, Connector connected to encoder housing	•

Assignments

	R5 5-pin	R6 6-pin	R8 8-pin	R8 8-pin	R12 12-pin	R12 12-pin
Circuit	C3, C4, C5, C6, C7	C3, C4, C5, C6, C7	C1, C2, D3, D4, D5, D6, D7	D8	C1, C2, D3, D4, D5, D6, D7	D8
GND	1	6	1	1	K, L	K, L
(+) Vcc	2	1	2	2	M, B	M, B
A	3	2	3	3	E	E
B	4	4	4	4	H	H
N	5	3	5	5	C	C
–	–	–	–	–	–	–
A inv.	–	–	6	6	F	F
B inv.	–	–	7	7	A	A


기술 데이터

Encoder EI30 P 100 HI

Assignments

N inv.	-	-	8	8	D	D
n. c.	-	5	-	-	G, J	G, J
Shield	-	-	-	-	-	-

Connector (M16x0.75) R7, radial, 7-pin



All dimensions in mm

- A Plug-in connexctor for functional ground connection (flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support

Description

N inv. poss.


R7 radial, 7-pin, Connector connected to encoder housing

-

Assignments

R7

7-pin




Circuit	C3, C4, C5, C6, C7
GND	1
(+) Vcc	2
A	3
B	4
N	5
-	-
A inv.	-
B inv.	-
N inv.	-
n. c.	6, 7
Shield	-

기술 데이터

Encoder EI30 P 100 HI

Connector (M23) R12M, radial, 12-pin



All dimensions in mm

- A Plug-in connexctor for functional ground connection (flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support


Description		N inv. poss.
R12M	radial, 12-pin, Connector connected to encoder housing	•

Assignments			
	R12M 12-pin	R12M 12-pin	R12M 12-pin
Circuit	C3, C4, C5, C6, C7	C1, C2, D3, D4, D5, D6, D7	D8
GND	10	10	10
(+) Vcc	12	12	12
A	5	5	5
B	8	8	8
N	3	3	3
–	–	–	–
A inv.	–	6	6
B inv.	–	1	1
N inv.	–	4	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11	2, 7, 9, 11
Shield	–	–	–

기술 데이터

Encoder EI30 P 100 HI

Connector (M23) RC12, radial, 12-pin (clockwise)



All dimensions in mm

- A Plug-in connexctor for functional ground connection (flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support

Description	N inv. poss.
RC12 radial, 12-pin, Connector connected to encoder housing	•


	RC12 12-pin	RC12 12-pin	RC12 12-pin
Circuit	C3, C4, C5, C6, C7	C1, C2, D3, D4, D5, D6, D7	D8
GND	10	10	10
(+) Vcc	12	12	12
A	5	5	5
B	8	8	8
N	3	3	3
—	—	—	—
A inv.	—	6	6
B inv.	—	1	1
N inv.	—	4	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11	2, 7, 9, 11
Shield	—	—	—

Hier waren die falschen Bilder drin: es fehlte unten rechts das R

기술 데이터

Encoder EI30 P 100 HI

Sensor-connector (M12x1) RS, radial, 4-, 5-, 8-, 12-pin



All dimensions in mm

- A Plug-in connexctor for functional ground connection (flat pin 6.3 x 0.8 according to DIN 46244)
- B 2x threaded pin M4
- C 6x M4x0.7-6H - 6 deep
- D Spring plate as torque support

Description

N inv. poss.

RS4	radial, 4-pin, Connector connected to encoder housing	—
RS5	radial, 5-pin, Connector connected to encoder housing	—
RS8	radial, 8-pin, Connector connected to encoder housing	•
RS12	radial, 12-pin, Connector connected to encoder housing	•

Assignments

	RS4 4-pin	RS5 5-pin	RS8 8-pin	RS8 8-pin	RS12 12-pin
Circuit	C3, C4, C5, C6, C7	C3, C4, C5, C6, C7	C1, C2, D3, D4, D5, D6, D7	D8	C1, C2, D3, D4, D5, D6, D7
GND	3	3	1	1	3
(+) Vcc	1	1	2	2	1
A	2	4	3	3	4
B	4	2	4	5	6
N	—	5	5	—	8
—	—	—	—	—	—
A inv.	—	—	6	4	9
B inv.	—	—	7	6	7
N inv.	—	—	8	—	10
n. c.	—	—	—	7, 8	2, 5, 11, 12
Shield	—	—	—	—	—

기술 데이터

Encoder EI30 P 100 HI

Options

Low temperature	Order key										
The encoder EI30 P 100 HI with the output circuit types C4, C6, D4, D6, C3, C5, D3, D5, C1, C2 is also available with the extended temperature range -40 °C up to +85 °C [-40 °F up to +185 °F] (measured at the flange).	LT										
Pressure equalising membrane	Order key										
The EI30 P 100 HI shaft encoder is also optionally available with a pressure equalising membrane. This prevents water from penetrating into the encoder housing in the case of high air humidity. The IP67 protection level, temperature range and salt spray resistance are maintained. Resistant to chemicals and solvents in accordance with DIN EN ISO 2812-1. <table><tr><td>Max. RPM:</td><td>1500 rpm</td></tr><tr><td>Permitted Shaft-Loading, axial:</td><td>100 N [10.197 kp]</td></tr><tr><td>Permitted Shaft-Loading, radial:</td><td>120 N [12.236 kp]</td></tr><tr><td>Max. PPR:</td><td>20480 ppr</td></tr><tr><td>Starting-torque:</td><td>approx. 5 Ncm [7.081 in-ozf] at ambient temperature</td></tr></table>	Max. RPM:	1500 rpm	Permitted Shaft-Loading, axial:	100 N [10.197 kp]	Permitted Shaft-Loading, radial:	120 N [12.236 kp]	Max. PPR:	20480 ppr	Starting-torque:	approx. 5 Ncm [7.081 in-ozf] at ambient temperature	PE
Max. RPM:	1500 rpm										
Permitted Shaft-Loading, axial:	100 N [10.197 kp]										
Permitted Shaft-Loading, radial:	120 N [12.236 kp]										
Max. PPR:	20480 ppr										
Starting-torque:	approx. 5 Ncm [7.081 in-ozf] at ambient temperature										
Cable length	Order key										
The encoder EI30 P 100 HI can be supplied with more than 2 m cable. The maximum cable length depends on the supply voltage and the frequency. Please extend the standard order code with a three figure number, specifying the cable length in decimetres. Example: 5 m cable = 050	XXX = Decimeter										

기술 데이터

Encoder EI30 P 100 HI

Example Order No.	Type				
EI30 P 100 HI	EI30 P 100 HI	EI30 P 100 HI			
Shaft					
25	25; 28; 30; 32; 38; 40; 42; 45				
Pulses per revolution PPR:					
1024	512, 1024, 2048, 2500, 3600, 4096, 4500, 5000, 8192, 10240, 16384, 20480 1 Vpp Sin/Cos only 1024, 2048 Other PPRs on request				
Channels:					
N	B, N				
Output circuit					
C6	Resolution PPR	Power supply VDC	Output circuit	—	Order key
	up to 2500	5 - 30	HTL (TTL at 5 VDC)	—	C7
		5 - 30	HTL, inv. (TTL/RS422 comp. at 5 VDC)	—	D7
	up to 5000	4.75 - 5.5	TTL	—	C5
		4.75 - 5.5	TTL, RS422 comp., inverted	—	D5
		10 - 30	HTL	—	C6
		10 - 30	HTL inverted	—	D6
		10 - 30	TTL, RS422 comp., inverted	—	C1
	(higher frequency) 1200	4.75 - 5.5	TTL	—	C3
		4.75 - 5.5	TTL, RS422 comp., inverted	—	D3
	up to 25000	10 - 30	HTL	—	C4
		10 - 30	HTL inverted	—	D4
		10 - 30	TTL, RS422 comp., inverted	—	C2
	1024, 2048	4.75 - 5.5	1 Vpp sin/cos	—	D8

기술 데이터

Encoder EI30 P 100 HI

Electrical connections

Description		N inv. poss.	Order key
Cable: length (2 m standard)			
R-N	radial, shield not connected	•	R-N
	radial, shield connected to encoder housing	•	R-C
	Connector: (shield connected to encoder housing)		
	connector, M16x0.75, 5-pin, radial	–	R5
	connector, M16x0.75, 6-pin, radial	–	R6
	connector, M16x0.75, 8-pin, radial	•	R8
	connector, M16x0.75, 12-pin, radial	•	R12
	connector, M16x0.75, 7-pin, radial	–	R7
	connector, M23, 12-pin, radial	•	R12M
	connector, clockwise pin count, M23, 12-pin, radial	•	RC12
	sensor-connector, M12x1, 4-pin, radial	–	RS4
	sensor-connector, M12x1, 5-pin, radial	–	RS5
	sensor-connector, M12x1, 8-pin, radial	•	RS8
	sensor-connector, M12x1, 12-pin, radial	•	RS12

Options

Description		Order key
Low temperature		LT
IP55		PE
Without option		Empty
Cable length		XXX = Decimeter

Example Order No.:	EI30 P 100 HI	25	1024	N	C6	R-N	EI30 P 100 HI	Your encoder
--------------------	---------------	----	------	---	----	-----	---------------	--------------

제품 키워드

제품 명칭: EABB CCCDDEE FFFFFFF GHJJKK LLMNNOPPP RR

A	회전 센서 유형 I: 증분형 S: 절대형, 싱글턴 M: 절대형, 멀티턴
BB	시리즈 10: Entry 30: 기본 50: 확장형 70: Advanced
CCC	플랜지 직경 024: 24mm 036: 36mm 058: 58mm 063: 63mm 067: 67mm 070: 70mm 080: 80mm 100: 100 mm 115: 115 mm
DD	플랜지 유형 BB: 막힌 구멍 보어가 있는 중공축 CC: 클램핑 플랜지(컴팩트형) CF: 클램핑 플랜지(식품 및 음료용) CH: 클램핑 플랜지(중하중형) CL: 클램핑 플랜지 HI: 중공축(절연) HO: 중공축 HT: 중공축(특수 토크 지지대) RC: 원형 플랜지(36/40 클램핑 플랜지, 58은 6 mm 축 적용) RE: 원형 플랜지(확장 홀) RN: 원형 플랜지 SC: 스테이터 커플링 SF: 나사식 플랜지(53 클램핑 플랜지, 58 식품 및 음료용) SI: 서보 플랜지(증가된 축 하중 및 IP 보호) SQ: 스퀘어 플랜지 SR: 나사식 플랜지(36/40 클램핑 플랜지, 58 내식형) SY: 싱크로(증분형), 서보(36), 싱크로(58)(절대형) TM: 타코(115, 1mm 축, 58 모터 피드백) TS: 타코(10mm 축)
EE	축/보어 직경 06: 6mm 07: 7mm 08: 8mm 08: 8mm 10: 10mm 11: 11mm 12: 12mm 14: 14mm 15: 15 mm 06-72: 중공축/막힌 구멍 보어(6 ~ 72mm)
FFFFFF	신호/분해능 Axxxxx: A Bxxxxx: AB Nxxxxx: ABN P16384: 프로그래밍 가능 xx: 싱글턴, 1 ~ 16비트 xx: 멀티턴, 0 ~ 43비트(싱글턴의 경우 00)
G	갈바닉 절연(절대형에 한함) 0: 제외 1: 있음
HH	전원 공급(절대형에 한함) 0: 10 ~ 32V DC/갈바닉 절연 1: 4.75 ~ 5.5V DC 2: 18 ~ 30V DC
J	작동 원리 M: 자기식 O: 광학 방식 P: 광학 보간

제품 키워드

KK	인터페이스 01: RS485 07: SSI 2진 08: SSI Gray 35: CANopen 38: EtherCAT 48: PROFINET 58: EtherNet/IP
LL	전기 연결 M08: 원형 커넥터 M8 M12: 원형 커넥터 M12 M16: 원형 커넥터 M16 M23: 원형 커넥터 M23 M12BC: 버스 커넥터
M	케이블 출구 A: 액시얼 R: 레이디얼 T: 접선형
NN	핀 개수 xx: 핀 개수
O	차폐 연결(2m 케이블)(옵션) C: 연결됨 N: 연결되지 않음
PPP	케이블 길이 xxx: 케이블 길이(단위: dm)

참고

	제공되는 모든 장치 유형 목록은 로이체의 웹 사이트 www.leuze.com 을 참조하십시오.
---	---

