

KFX-ETD-420

Cod. art. 50117757

**Fibra ottica,
a tasteggio**

Dati tecnici

Tipo di fibra ottica	Precisione
Temperatura operativa	-55°C ... +70°C
Raggio di curvatura min.	R15
Diametro esterno fibra ottica	2x Ø1,25mm
Diametro attivo fibra	2x Ø0,5mm
Pezzo più piccolo riconoscibile	Ø0,1mm
Lunghezza totale	2019mm


Caratteristiche

Features



- 1) Impostazione di amplificatore per fibra ottica: max. tempo di reazione, max. amplificazione, min. soglia di commutazione / Adjustment on fiber optics amplifier: max. response time, max. gain, min. switching threshold

Disegno quotato/Dimensioned drawing



Accessori (da ordinare a parte)/Accessories (available separately)

- KL-M04; 50117781

Leuze electronic GmbH + Co. KG
In der Braike 1 D-73277 Owen
www.leuze.com

KFX-ETD-420

Part No. 50117757

**Fiber,
reflective**

Specifications

Fiber type	Precision
Operating temperature	-55°C ... +70°C
Min. bending radius	R15
Fiber jacket diameter	2x Ø1.25mm
Active fiber diameter	2x Ø0.5mm
Smallest detectable object	Ø0.1mm
Total length	2019mm

Portata limite tipica per oggetti chiari (bianco 90%) ¹⁾
Typ. scanning range limit for light objects (white 90%) ¹⁾

LV463LXR	350mm
LV463.XR	175mm
LV463B, LV463.XV	120mm
LV463	70mm
LV462	40mm
LV461	25mm

Tel. +49 (0) 7021 573-0
info@leuze.com