

技術データシート

ステッカー

製品番号: 50142923

Safety Sticker Set

目次

- 仕様書

⚠ Leuze electronic

Regular function test of the protective device by instructed persons (e.g. operators)

The following tests are carried out on a regular basis (e.g.: daily).
Make absolutely certain that no persons are located in the danger zone during the inspection.

Test at least:

- ↳ Are safety sensor and connectors securely mounted and free of obvious signs of damage, changes or tampering?
- ↳ Are possible access points free from obvious signs of modification?
- ↳ Test the effectiveness of the safety sensor:
 1. The OSSD LED on the safety sensor must illuminate green.
 2. Interrupt an active beam or the protective field with a suitable, opaque test object.
 3. Does the OSSD LED illuminate constantly red while the protective field is interrupted?

When possible, test during running operation:

- Protective device with approach function:
during machine operation, the protective field is interrupted with a suitable opaque test object – are the obviously dangerous machine parts stopped without noticeable delay?
- Protective device with presence detection:
the protective field is interrupted with a suitable opaque test object – does this prevent operation of the obviously dangerous machine parts?

If there is any doubt about the correct function of the safety system or if you answer no to one of the points, shutdown the system and inform the person responsible.

More information about regular testing of the safety sensors can be found in the respective operating instructions.

Cleaning:

In the event of visible contamination, the front screens of the AOPDs are to be periodically cleaned with mild detergent. Do not use abrasive, alcohol-containing or aggressive detergents or solvents!

写真と異なる場合があります

仕様書

基本仕様

説明	安全のヒント"保護装置の定期的な機能検査"
詳細	粘着ラベル13枚、ポリ袋入り

機械の仕様

寸法 (幅 x 高さ x 長さ)	100 mm x 210 mm
素材	淡くて永久に保証された銀の隠されたラベル紙

ソフトウェア

言語	イタリア語
	スウェーデン語
	スペイン語
	チェコ語
	ドイツ語
	トルコ語
	フランス語
	ポルトガル語
	ポーランド語
	ロシア語
	中国語 (簡易字)
	英語
	韓国語

分類

関税分類番号	48114190
ECLASS 5.1.4	27279290
ECLASS 8.0	27279290
ECLASS 9.0	27279090
ECLASS 10.0	27273692
ECLASS 11.0	27273692
ECLASS 12.0	27273692
ECLASS 13.0	27273692
ECLASS 14.0	27273692
ETIM 5.0	EC002498
ETIM 6.0	EC003015
ETIM 7.0	EC003015
ETIM 8.0	EC003015
ETIM 9.0	EC003015