

技术数据表

旋转编码器系列信息

配件编号: 90000110

EI30-M 058 CL

内容

- 技术参数
- 产品型号描述



图片可能不同

编码器_系列	EI 058 CL
编码器_基本原理	增量
编码器_工作原理	磁性
编码器_法兰直径	Ø 58 mm
编码器_法兰型号	夹紧法兰
编码器_实心轴/空心轴H	空心轴
编码器_轴直径	Ø 10 mm
	Ø 6 mm
	Ø 8 mm
编码器_供电电压	4.75 ... 30 VDC
编码器_输出电路	HTL (TTL , 当 5 VDC 时)
	HTL , 逆转 (TTL/RS422 兼容 , 当 5 VDC 时)
编码器_脉冲数	1 ... 16384 I/U

技术参数

Encoder EI30 M 058 CL

Resolution

Pulses per revolution PPR	1 PPR up to 16384 PPR
---------------------------	-----------------------

Mechanical Data

Flange	clamping flange
Flange material	aluminum
Housing material	Stainless steel or die cast aluminum, powder coated (only M16 and M23 plugs)
Flange diameter	Ø 58 mm [Ø 2.283"]
Cam mounting	pitch 69 mm [2.717 inches]

Shaft(s)

Shaft material	stainless steel
Starting torque	approx. 1 Ncm [1.416 in-ozf] at ambient temperature

Shaft	Ø 6 mm [Ø 0.236"]
	Attention: No option IP = full IP67 version
Shaft length	L: 12 mm [0.472"]
Max. Permissible shaft loading radial	125 N [12.746 kp]
Max. Permissible shaft loading axial	120 N [12.236 kp]

Shaft	Ø 8 mm [Ø 0.315"]
	Attention: No option IP = full IP67 version
Shaft length	L: 19 mm [0.748"]
Max. Permissible shaft loading radial	125 N [12.746 kp]
Max. Permissible shaft loading axial	120 N [12.236 kp]

Shaft	Ø 9.525 mm [Ø 3/8"] Order No: 4Z
	Attention: No option IP = full IP67 version
Shaft length	L: 20 mm [0.787"]
Max. Permissible shaft loading radial	220 N [22.433 kp]
Max. Permissible shaft loading axial	120 N [12.236 kp]

Shaft	Ø 10 mm [Ø 0.394"]
Shaft length	L: 20 mm [0.787"]
Max. Permissible shaft loading radial	220 N [22.433 kp]
Max. Permissible shaft loading axial	120 N [12.236 kp]

Bearings

Bearings type	2 precision ball bearings
Nominale service life	1 x 10 ⁹ revs. at 100 % rated shaft load 1 x 10 ¹⁰ revs. at 40 % rated shaft load 1 x 10 ¹¹ revs. at 20 % rated shaft load
Max. operating speed	8000 rpm

Machinery Directive: basic data safety integrity level

MTTF _d	2200 a
Mission time (TM)	25 a
Nominale service life (L10h)	1 x 10 ¹¹ revs. at 20 % rated shaft load and 8000 rpm
Diagnostic coverage (DC)	0 %

Electrical Data

Power supply/Current consumption	4.75 VDC up to 30 VDC: typ. 40 mA
Operating principle	magnetic
Output circuit	HTL (TTL at 5 VDC) HTL, inv. (TTL/RS422 comp. at 5 VDC)
Pulse frequency	HTL up to 16384 ppr: max. 600 kHz TTL up to 16384 ppr: max. 1 MHz
Channels	B N and inverted signals
Load	max. 40 mA / channel
Circuit protection	yes

Accuracy

Phase offset	90° ± max. 7.5 % of the period duration
pulse-/pause-ratio	50 % ± max. 7 %

Environmental data

ESD (DIN EN 61000-4-2):	8 kV
Burst (DIN EN 61000-4-4):	2 kV
includes EMC:	DIN EN 61000-6-2 DIN EN 61000-6-3
Vibration: (DIN EN 60068-2-6)	50 m/s ² (10 Hz up to 2000 Hz)
Shock: (DIN EN 60068-2-27)	1000 m/s ² (6 ms)
Electrical Safety:	according DIN VDE 0160

Duty information

Customs tariff number:	90318020
Country of origin:	Germany

General Data

Weight	approx. 250 g [8.818 oz]
Connections	cable or connector outlet
Protection rating (EN 60529)	Housing: IP65, IP67; shaft sealed: IP65
Operating temperature	Connector: -40 °C up to +85 °C, Cable: -20 °C up to +80 °C (Option LT: -40 °C up to +85 °C). Connector: -40 °F up to +185 °F, Cable: -4 °F up to +176 °F, Option LT: -40 °F up to +185 °F
Storage temperature	Connector: -40 °C up to +85 °C, Cable: -30 °C up to +80 °C (Option LT: -40 °C up to +85 °C) Connector: -40 °F up to +185 °F, cable: -22 °F up to +176 °F, (Option LT: -40 °F up to +185 °F)

All dimensions in mm

	R-IP	R-IP
Circuit	D2	D1
GND	WH	WH
(+) Vcc	BN	BN
A	GN	GN
B	YE	YE
N	GY	GY
–	–	
A inv.	–	RD
B inv.	–	BK


技术参数

Encoder EI30 M 058 CL

Assignments

N inv.	–	VT
Shield	flex	flex

Connector (M16x0.75) A, axial, 5-, 6-, 8-, 12-pin



All dimensions in mm



Description


N inv. poss.

A5	axial, 5-pin, Connector connected to encoder housing	–
A6	axial, 6-pin, Connector connected to encoder housing	–
A8	axial, 8-pin, Connector connected to encoder housing	•
A12	axial, 12-pin, Connector connected to encoder housing	•

Assignments

	A5 5-pin	A6 6-pin	A8 8-pin	A8 8-pin	A12 12-pin	A12 12-pin
Circuit	D2	D2	D2	D1	D2	D1
GND	1	6	1	1	K, L	K, L
(+) Vcc	2	1	2	2	M, B	M, B
A	3	2	3	3	E	E
B	4	4	4	4	H	H
N	5	3	5	5	C	C
–	–	–	–	–	–	–
A inv.	–	–	–	6	–	F
B inv.	–	–	–	7	–	A
N inv.	–	–	–	8	–	D
n. c.	–	5	6, 7, 8	–	A, D, F, G, J	G, J
Shield	–	–	–	–	–	–


	R5	R6	R8	R8	R12	R12
	5-pin	6-pin	8-pin	8-pin	12-pin	12-pin
						
Circuit	D2	D2	D2	D1	D2	D1
GND	1	6	1	1	K, L	K, L
(+) Vcc	2	1	2	2	M, B	M, B
A	3	2	3	3	E	E
B	4	4	4	4	H	H
N	5	3	5	5	C	C
—	—	—	—	—	—	—
A inv.	—	—	—	6	—	F
B inv.	—	—	—	7	—	A
N inv.	—	—	—	8	—	D
n. c.	—	5	6, 7, 8	—	A, D, F, G, J	G, J
Shield	—	—	—	—	—	—

A7	
7-pin	
	
Circuit	D2
GND	1
(+) Vcc	2
A	3
B	4
N	5
—	—
A inv.	—
B inv.	—
N inv.	—
n. c.	6, 7
Shield	—

技术参数

Encoder EI30 M 058 CL

Connector (M16x0.75) R7, radial, 7-pin



All dimensions in mm

Description


N inv. poss.

R7 radial, 7-pin, Connector connected to encoder housing

Assignments

R7

7-pin




Circuit	D2
GND	1
(+) Vcc	2
A	3
B	4
N	5
—	—
A inv.	—
B inv.	—
N inv.	—
n. c.	6, 7
Shield	—

技术参数

Encoder EI30 M 058 CL

Connector (M23) A12M, axial, 12-pin



All dimensions in mm

Description N inv. poss.

A12M axial, 12-pin, Connector connected to encoder housing


Assignments

	A12M	A12M
	12-pin	12-pin
Circuit	D2	D1
GND	10	10
(+) Vcc	12	12
A	5	5
B	8	8
N	3	3
—	—	—
A inv.	—	6
B inv.	—	1
N inv.	—	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Connector (M23) R12M, radial, 12-pin



All dimensions in mm

Description

N inv. poss.

R12M radial, 12-pin, Connector connected to encoder housing


Assignments

	R12M	R12M
	12-pin	12-pin
Circuit	D2	D1
GND	10	10
(+) Vcc	12	12
A	5	5
B	8	8
N	3	3
—	—	—
A inv.	—	6
B inv.	—	1
N inv.	—	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Connector (M23) AC12, axial, 12-pin (clockwise)



All dimensions in mm

Description N inv. poss.

AC12 axial, 12-pin, Connector connected to encoder housing


Assignments

	AC12	AC12
	12-pin	12-pin
Circuit	D2	D1
GND	10	10
(+) Vcc	12	12
A	5	5
B	8	8
N	3	3
—	—	—
A inv.	—	6
B inv.	—	1
N inv.	—	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Connector (M23) RC12, radial, 12-pin (clockwise)



All dimensions in mm

Description

N inv. poss.

RC12 radial, 12-pin, Connector connected to encoder housing


Assignments

	RC12	RC12
	12-pin	12-pin
Circuit	D2	D1
GND	10	10
(+) Vcc	12	12
A	5	5
B	8	8
N	3	3
—	—	—
A inv.	—	6
B inv.	—	1
N inv.	—	4
n. c.	1, 2, 4, 6, 7, 9, 11	2, 7, 9, 11
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Sensor-connector (M12x1) AS axial, 5-, 8-pin



All dimensions in mm


Description		N inv. poss.
AS5	axial, 5-pin, Connector connected to encoder housing	—
AS8	axial, 8-pin, Connector connected to encoder housing	•

	RS5	RS8
	5-pin	8-pin
Circuit	D2	D1
GND	3	1
(+) Vcc	1	2
A	4	3
B	2	4
N	5	5
—	—	—
A inv.	—	6
B inv.	—	7
N inv.	—	8
n. c.	—	—
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Sensor-connector (M12x1) RS radial, 5-, 8-pin



D = 6	L1 = 12	d = 5.3	L2 = 10
D = 8	L1 = 19	d = 7.5	L2 = 15
D = 9.525 [3/8"]	L1 = 20	d = 8.302 [0.327"]	L2 = 10
D = 10	L1 = 20	d = 9	L2 = 15

All dimensions in mm

Description

N inv. poss.

RS5	radial, 5-pin, Connector connected to encoder housing	—
RS8	radial, 8-pin, Connector connected to encoder housing	•

Assignments

	RS5	RS8
	5-pin	8-pin
Circuit	D2	D1
GND	3	1
(+) Vcc	1	2
A	4	3
B	2	4
N	5	5
—	—	—
A inv.	—	6
B inv.	—	7
N inv.	—	8
n. c.	—	—
Shield	—	—

技术参数

Encoder EI30 M 058 CL

Options

Low-friction bearings

Order key

The encoder EI30 M 058 CL is also available as a particularly smooth- running low-friction encoder. The starting torque is thereby changed to $\leq 0.5 \text{ Ncm}$ [0.708 in-ozf] and the protection class at the shaft input to IP50.

LB

Shafts sealed to IP67, only with 10 mm [0.394"] shaft

Order key

The encoder EI30 M 058 CL can be supplied in a IP67 version. (full IP67 only connection AS, RS, A-C or R-C version; not cable connection R-IP = IP40).

IP

Max. RPM: 3500 min⁻¹
 Permitted Shaft-Loading: axial 100 N [10.197 kp]; radial 110 N [11.216 kp]
 Starting-torque: approx. 4 Ncm [5.664 in-ozf] at ambient temperature

Low temperature

Order key

The encoder EI30 M 058 CL with the output circuit types D2, D1 is also available with the extended temperature range -40 °C up to +85 °C [-40 °F up to +185 °F] (measured at the flange).

LT

Pressure equalising membrane

Order key

The EI30 M 058 CL shaft encoder is also optionally available with a pressure equalising membrane. This prevents water from penetrating into the encoder housing in the case of high air humidity.

PE

The IP67 protection level, temperature range and salt spray resistance are maintained.
 Resistant to chemicals and solvents in accordance with DIN EN ISO 2812-1.

Cable length

Order key

The encoder EI30 M 058 CL can be supplied with more than 2 m cable.
 The maximum cable length depends on the supply voltage and the frequency.

XXX = Decimeter

Please extend the standard order code with a three figure number, specifying the cable length in decimetres.
 Example: 5 m cable = 050

技术参数

Encoder EI30 M 058 CL

Example Order No.	Type				
EI30 M 058 CL	EI30 M 058 CL	EI30 M 058 CL			
Shaft					
10	06; 08; 4Z; 10				
Pulses per revolution PPR:					
16384	1-16384 Other PPRs on request				
Channels:					
N	B, N				
Output circuit					
D1	Resolution PPR	Power supply VDC	Output circuit	—	Order key
	1-16384	4.75 - 30	HTL (TTL at 5 VDC)	—	D2
		4.75 - 30	HTL, inv. (TTL/RS422 comp. at 5 VDC)	—	D1

技术参数

Encoder EI30 M 058 CL

Electrical connections

Description		N inv. poss.	Order key
A-C	Cable: length (2 m standard)		
	radial, shield not connected (IP40)	•	R-IP
	axial, shield connected to encoder housing	•	A-C
	radial, shield connected to encoder housing	•	R-C
	Connector: (shield connected to encoder housing)		
	connector, M16x0.75, 5-pin, axial	–	A5
	connector, M16x0.75, 5-pin, radial	–	R5
	connector, M16x0.75, 6-pin, axial	–	A6
	connector, M16x0.75, 6-pin, radial	–	R6
	connector, M16x0.75, 8-pin, axial	•	A8
	connector, M16x0.75, 8-pin, radial	•	R8
	connector, M16x0.75, 12-pin, axial	•	A12
	connector, M16x0.75, 12-pin, radial	•	R12
	connector, M16x0.75, 7-pin, axial	–	A7
	connector, M16x0.75, 7-pin, radial	–	R7
	connector, M23, 12-pin, axial	•	A12M
	connector, M23, 12-pin, radial	•	R12M
	connector, clockwise pin count, M23, 12-pin, axial	•	AC12
	connector, clockwise pin count, M23, 12-pin, radial	•	RC12
	sensor-connector, M12x1, 5-pin, axial	–	AS5
	sensor-connector, M12x1, 5-pin, radial	–	RS5
	sensor-connector, M12x1, 8-pin, axial	•	AS8
	sensor-connector, M12x1, 8-pin, radial	•	RS8

Options

Description	Order key
Low-friction bearings	LB
Shafts sealed to IP67, only with 10 mm [0.394"] shaft	IP
Low temperature	LT
Pressure equalising membrane	PE
Without option	Empty
Cable length	XXX = Decimeter

Example Order No.:	EI30 M 058 CL	10	16384	N	D1	A-C	EI30 M 058 CL	Your encoder
--------------------	---------------	----	-------	---	----	-----	---------------	--------------

产品型号描述

产品名称：EABB CCCDDEE FFFFFFF GHHJKK LLMNOPPP RR

A	旋转编码器型号 I：增量 S：绝对，单圈 M：绝对，多圈
BB	系列 10：条目 30：基本型 50：扩展型 70：高级版
CCC	法兰直径 024: 24 mm 036: 36 mm 058: 58 mm 063: 63 mm 067: 67 mm 070: 70 mm 080: 80 mm 100：100 mm 115: 115 mm
DD	法兰型号 BB：带有盲孔钻孔的空心轴 CC：夹紧法兰（紧凑结构形式） CF：夹紧法兰（食品和饮料） CH：夹紧法兰（重负载规格） CL：夹紧法兰 HI：空心轴（绝缘） HO：空心轴 HT：空心轴（特殊扭矩支承） RC：圆形法兰（36/40 夹紧法兰，58 带 6-mm-轴） RE：圆形法兰（扩展钻孔） RN：圆形法兰 SC：定子联轴器 SF：螺栓法兰（53 夹紧法兰，58 食品和饮料） SI：伺服法兰（高级轴负载和 IP 地址） SQ：方形法兰 SR：螺栓法兰（36/40 夹紧法兰，58 耐腐蚀） SY：同步（增量），伺服(36)，同步(58)（绝对） TM：转速计（115 带 1-mm-轴，58 电机反馈） TS：转速计（10-mm-轴）
EE	轴-/钻孔直径 06: 6 mm 07: 7 mm 08: 8 mm 08: 8 mm 10: 10 mm 11: 11 mm 12: 12 mm 14: 14 mm 15: 15 mm 06-72：空心/盲孔钻孔 (6 ... 72 mm)
FFFFFF	信号/分辨率 Axxxxx: A Bxxxxx: AB Nxxxxx: ABN P16384：可编程 xx：单圈，1 ... 16 位 xx：多圈，0 ... 43 位（单圈时为 00）
G	电隔离（仅绝对） 0：无 1：带有
HH	供电电源（仅绝对） 0：10 ... 32 V DC/带电隔离 1: 4.75 ... 5.5 V DC 2: 18 ... 30 V DC
J	工作原理 M：磁性 O：光学 P：光学插值

产品型号描述

KK	接口 01: RS485 07 : SSI 二进制 08: SSI Gray 35: CANopen 38: EtherCAT 48: PROFINET 58: EtherNet/IP
LL	电气连接 M08 : 圆形插头 M8 M12 : 圆形插头 M12 M16 : 圆形插头 M16 M23 : 圆形插头 M23 M12BC : 总线罩插头
M	电缆出口 A : 轴向 R : 径向 T : 正切
NN	引脚数 xx : 引脚数
O	屏蔽接口 (2-m-电缆) (可选) C : 已连接 N : 未连接
PPP	电缆长度 xxx : 电缆长度 (单位为 dm)

注意

	所有可用设备类型列表请查阅劳易测的网站 www.leuze.com 。
---	--

